

NOTES:

1. MATERIAL:

HOUSING: LCP UL94V-0, BLACK

CONTACT: C5210R-EH, T=0.20mm






2. DURABILITY TEST: 100 CYCLES MIN.

3. SPECIFICATION:

DIELECTRIC STRENGTH: AC 300V/MINUTE

INSULATOR RESISTANCE: 500 Mohm MIN

CONTACT RESISTANCE: 40 mohm Max.

OPERATING TEMPERATURE: $-40^{\circ}\sim +85^{\circ}$ RECOMMENDED PCB LAYOUT(TOP VIEW)
(ALL TOLERANCES ARE ± 0.05)RECOMMENDED LAYOUT
MATING PCB SIDE

			GENERAL TOLERANCE		制 图	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO., LTD			
			DIM	TOL	DRAWING				
			X. X	± 0.30	审 核	产品名称 TITLE	SPF (20Pin CONN)	版本 REV.	A
			X. XX	± 0.20	批 准				
			X. XXX	± 0.10	SCALE	产品料号 PART NO.	HC-SFP-20P	单 位 UNITS	mm
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle	$\pm 3.0^{\circ}$	投 影 Projection	材 料 MATERIAL		页 次 SHEET	1/1