











Ordering Information:
A2508WV-XP - *** - *** - *** - ***
1 2 3 4 5

1.Part No.

2.Material:

(Blank) : Nylon 66,UL94V-0
46 : Nylon 46,UL94V-0
9T : Nylon 9T,UL94V-0
GWT : Nylon 66,UL94V-0(Beige),
IEC 60335-1,5th Edition
Glow Wire Capable.

3.Color:



(Blank):Ivory
RD:Red
YL:Yellow
BL:Blue
BK:Black
GN:Green
WH:White
LE:Light Blue
OR:Orange
GY:Gray
PK:Pink
BR:Brown
VI:Violet
LY:Lemon yellow
VY:Vivid yellow

4.Finish:

(Blank):Tin over Nickel
G:Gold over Nickel(Au:1u" all area)
G3:Gold over Nickel(Au:3u" all area)
G5:Gold over Nickel(Au:5u" all area)
G10:Gold over Nickel(Au:10u" all area)
G15:Gold over Nickel(Au:15u" all area)

5.Void position:

(Blank): Full positions
N*.*.*: Void position(select Arbitrary numbers)



SPECIFICATIONS:

Current Rating: 3A AC,DC
Voltage Rating: 250V AC,DC
Temperature Range: -40°C ~ +105°C
Contact Resistance: 10mΩ Max
Insulation Resistance: 1000MΩ Min
Withstanding Voltage: 1000V AC/minute
Pin Material:Brass
Material: Nylon 66,UL94V-0

Ordering Information & Dimensions

Circuits	Dimensions(mm)		Circuits	Press K	
	A	B		R	L
2P	2.50	7.50	2P	---	---
3P	5.00	10.00	3P	P1.P3	P2
4P	7.50	12.50	4P	P1.P4	P2
5P	10.00	15.00	5P	P1.P5	P3
6P	12.50	17.50	6P	P1.P6	P3
7P	15.00	20.00	7P	P1.P7	P4
8P	17.50	22.50	8P	P1.P8	P4
9P	20.00	25.00	9P	P1.P9	P5
10P	22.50	27.50	10P	P1.P10	P5
11P	25.00	30.00	11P	P1.P11	P6
12P	27.50	32.50	12P	P1.P12	P6
13P	30.00	35.00	13P	P1.P13	P7
14P	32.50	37.50	14P	P1.P14	P7
15P	35.00	40.00	15P	P1.P15	P8
16P	37.50	42.50	16P	P1.P16	P8
17P	40.00	45.00	17P	P1.P17	P9
18P	42.50	47.50	18P	P1.P18	P9
19P	45.00	50.00	19P	P1.P19	P10
20P	47.50	52.50	20P	P1.P20	P10


CJTconn

CHANGJIANG CONNECTORS CO.,LTD.




Unit	Scale	Sheet	TITLE		
mm	2:1	1 of 2	2.50mm PITCH VERTICAL WAFER		
DRAWN	CHK'D	APPR			
Chengblao Ye	Diankul Wan	Jack Yin	DRAWING NO. A2508WV-XP		
General Tolerances					REV B1
THIRD ANGLE PROJECTION					
x.x±0.25 x.xx±0.20 x.xxx±0.15 ANGLES ±1°					

B1	CHANGE THE DRAWING	2024.03.20
A5	CHANGE THE DRAWING	2023.02.22
A4	CHANGE THE DRAWING	2022.12.28
A3	CHANGE THE DRAWING	2022.03.25




Style	Circuits	X=Void position													Press K	
		P1	P2	P3	P4	P5	P6	P7	P8	P9	P10	P11	P12	P13	R	L
N2	4P	O	X	O	O										P1.P4	P3
N2.3	4P	O	X	X	O										P1.P4	
N3	4P	O	O	X	O										P1.P4	P2
N2	5P	O	X	O	O	O									P1.P5	P3
N2.3	5P	O	X	X	O	O									P1.P5	P4
N2.3.4	5P	O	X	X	X	O									P1.P5	
N4	5P	O	O	O	X	O									P1.P5	P3
N1.3.5	6P	X	O	X	O	X	O								P2.P6	P4
N2	6P	O	X	O	O	O	O								P1.P6	P3
N2.4	6P	O	X	O	X	O	O								P1.P6	P3
N2.4.6	6P	O	X	O	X	O	X								P1.P5	P3
N3.4	6P	O	O	X	X	O	O								P1.P6	P5
N3.5	6P	O	O	X	O	X	O								P1.P6	P4
N5	6P	O	O	O	O	X	O								P1.P6	P3
N5.6	6P	O	O	O	O	X	X								P1.P4	P3
N2.3	7P	O	X	X	O	O	O	O							P1.P7	P4
N2.4	7P	O	X	O	X	O	O	O							P1.P7	P3
N2.4.5	7P	O	X	O	X	X	O	O							P1.P7	P3
N2.3.5.6	7P	O	X	X	O	X	X	O							P1.P7	P4
N4.6	7P	O	O	O	X	O	X	O							P1.P7	P3
N5.6	7P	O	O	O	O	X	X	O							P1.P7	P4
N6	7P	O	O	O	O	O	X	O							P1.P7	P4
N7	7P	O	O	O	O	O	O	X							P1.P6	P4
N1.6.7	8P	X	O	O	O	O	X	X	O						P2.P8	P4
N2.3.5.6	8P	O	X	X	O	X	X	O	O						P1.P8	P4
N2.3.5.6.8	8P	O	X	X	O	X	X	O	X						P1.P7	P4
N3.5.7	8P	O	O	X	O	X	O	X	O						P1.P8	P4
N3.6	8P	O	O	X	O	O	X	O	O						P1.P8	P4
N5.6	8P	O	O	O	O	X	X	O	O						P1.P8	P4
N6.7	8P	O	O	O	O	O	X	X	O						P1.P8	P4
N8	8P	O	O	O	O	O	O	O	X						P1.P7	P4
N2.3	9P	O	X	X	O	O	O	O	O	O					P1.P9	P5
N4.6.8	9P	O	O	O	X	O	X	O	X	O					P1.P9	P5
N5.6.8	9P	O	O	O	O	X	X	O	X	O					P1.P9	P4
N6.8	9P	O	O	O	O	O	X	O	X	O					P1.P9	P5
N2.3.5.6.8.9	10P	O	X	X	O	X	X	O	X	X	O				P1.P10	P7
N3.4.7.8	10P	O	O	X	X	O	O	X	X	O	O				P1.P10	P5
N6.7.9	10P	O	O	O	O	O	X	X	O	X	O				P1.P10	P5
N7	10P	O	O	O	O	O	O	X	O	O	O				P1.P10	P5
N8.9	10P	O	O	O	O	O	O	O	X	X	O				P1.P10	P5
N10	10P	O	O	O	O	O	O	O	O	O	X				P1.P9	P5
N2.4.6	11P	O	X	O	X	O	X	O	O	O	O	O			P1.P11	P6
N2.3.5.6.8.9	11P	O	X	X	O	X	X	O	X	X	O	O			P1.P11	P7
N3.6.9	12P	O	O	X	O	O	X	O	O	X	O	O	O		P1.P12	P7
N2.3.5.6.8.9.11.12	13P	O	X	X	O	X	X	O	X	X	O	X	X	O	P1.P13	P7





2P13P14P




3P12P15P




4P11P16P


5P10P17P

6P9P18P

7P8P19P



20P



CHANGJIANG CONNECTORS CO.,LTD.

Unit	Scale	Sheet	TITLE
mm	2:1	2 of 2	
DRAWN	CHK'D	APPR	
Chengbiao Ye	Djankui Wan	Jack Yin	
General Tolerances		THIRD ANGLE PROJECTION	DRAWING NO.
A5	CHANGE THE DRAWING	2023.02.22	
A4	CHANGE THE DRAWING	2022.12.28	
A3	CHANGE THE DRAWING	2022.03.25	

x.x±0.25
x.xx±0.20
x.xxx±0.15
ANGLES ±1°



2.50mm PITCH
VERTICAL WAFER

A2508WV-XP

REV B1