


承 認 書  
SPECIFICATION FOR APPROVAL

NO: YF3568LA



| 尺 寸 數 據 (mm) |             |
|--------------|-------------|
| A            | 3.5 ± 0.2   |
| B            | 6.0 ± 0.2   |
| C            | 0.55 ± 0.5  |
| D            | 11.0        |
| E            | 2.0 ± 0.2   |
| F            | 5.0 ± 0.5   |
| G            | 4.0 ± 0.5   |
| H            | 18.5 ± 0.85 |
| J            | 12.5 ± 0.3  |
| W            | 18 ± 0.85   |
| W1           | 10 ± 1.8    |

| DIMENSION<br>尺寸    |      |       | MATERIAL<br>材料 |        |              | TESTING CONDITION<br>測試條件 | CUSTOMER<br>客戶 |
|--------------------|------|-------|----------------|--------|--------------|---------------------------|----------------|
| Measuring unit: mm |      |       | R10            |        |              | 測試儀器: E4991A              |                |
| OD                 | 3.50 | ±0.3  | 30mhz-35 Ω     | 初始磁導率  | 680          | 1-500MHZ                  |                |
| ID                 | 0.80 | ±0.3  | 100mhz-60 Ω    | 比損耗因子  | ≤17 (0.1mhz) | 0.5x0.5TSx100L(mm)        |                |
| HT                 | 6.00 | ± 0.8 |                | 飽和磁通密度 | 280(1600A/m) | DATE: 2025/4/1            |                |