

2		1	
REV	E.C.N NO.	CONTENT	CHK DATE



- 1.Rating voltage/current: 300V/10A
- 2.withstanding voltage: AC2000V/1Min
- 3.Torque value: M3, 4.43Lb.in
- 4.Wire range: 22~14AWG

1. Pollution Degree	3	2	2
Overvoltage Category	III	III	II
Rate Impulse Voltage(KV)	/	/	/
Rate Voltage(V)	/	250V	/
Rate Current(A)	/	15A	/

NOTES2:

NOTES3:

How to order

MX300R - 5.0 - XXP - XXXX - XX - X - X

产品型号 间距 颜色: 极数 01:常规颜色 0:Y一字螺丝
1:S十字螺丝
2:PS平头十字螺丝
A-Z其他定制

灰色:GY 橙色:OE 02-99: 定制颜色
蓝色:BU 红色:RD
黑色:BK 透明色:TT
绿色:GN 黄色:YW
白色:WE

Cu:铜方块
Fe:铁方块

Pitch Range In mm			Nominal Dimension Range In mm					—		
TO 6	Over 6 TO 10	Over 10 TO 24	TO 30	Over 30 TO 60	Over 60 TO 100	Over 100 TO 150	Over 150	0.1/10		
										
±0.15	±0.20	±0.30	±0.30	±0.50	±0.70	±1.00	±1.30	±2°		

ITEM	NAME OF PART		NO. OF PART	Q'TY	MATERIAL		NOTE	
DWG.	CKK	DATE	23.03.13	UNITS	MM	SHEET/OF		1/1
CHK.		DATE		SCALE	1 : 1	A4		
APP.		DATE		NAME	MX300R-5.0-XXP			
 CIXI MAIXU ELECTRONICS CO., LTD. 慈溪市迈旭电子有限公司								
				DWGNO.				