


承認書

SPECIFICATION FOR APPROVAL

NO: CMT56321815



PRODUCTION CORD

CMT56321815

性能測試數據

Core Factor 0.562mm⁻¹

Le (mm⁻¹) 131.2

Ae (mm²) 233.83

Ve (mm³) 30679

DIMENSION 尺寸			MATERIAL 材料			TESTING CONDITION 測試條件	CUSTOMER 客戶名稱
Measuring unit: mm			NT2			測試儀器: TH2826A	
OD	56.00	± 0.5	初始磁導率	10K (100KHZ)	14K (10KHZ)	T=25℃ 1000V 1mA 3sec 1TS	
ID	32.00	± 0.5	比損耗因子	<8x10 ⁻⁶		10KHz	AL:15-25uH 1KHz/0.3V 100Ω
HT	18.00	± 0.3	飽和磁通密度	≥240 (80℃)	≥380 (25℃)	DATE: 2025/4/1	