


承認書

SPECIFICATION FOR APPROVAL

NO: CMT18100706



PRODUCTION CORD

CMT18100706

性能測試數據

Core Factor	3.25mm^{-1}
$L_e (\text{mm}^{-1})$	33.25
$A_e (\text{mm}^2)$	18.67
$V_e (\text{mm}^3)$	485.25

DIMENSION 尺寸			MATERIAL 材料			TESTING CONDITION 測試條件	CUSTOMER 客戶名稱
Measuring unit: mm			NT2			測試儀器: TH2826A	
OD	18.00	± 0.5	初始磁導率		14000 (10KHZ)	T=25℃ 1000V 1mA 3sec 1TS	
ID	10.00	± 0.5	比損耗因子	$<8 \times 10^{-6}$	10KHz	AL:6.0-7.0uH 1KHz/0.1V 100Ω	
HT	7.00	± 0.3	飽和磁通密度	$\geq 240 (80^\circ\text{C})$	$\geq 380 (25^\circ\text{C})$	DATE: 2025/4/1	