






REVISIONS				
ZONE	REV	DESCRIPTION	DATE	APPROVED

NOTE:
1.MATERIAL:
a.HOUSING: PA66+30%GF UL94V-0
b.CONTACT:PHOSPHOR BRONZE

FINISH:
CONTACT: SN100u" MIN. SN ONLY PLATED OVER 50u" MIN.
NICKEL UNDER-PLATING.

SPECIFICATION :
APPLICATION : FOR 3V LITHIUM BATTERY (CR2032).
OPERATION TEMPERATURE : -55°C TO +105°C.
DURABILITY : 50 CYCLES.
CONTACT RESISTANCE : 30mΩ MAX.
Insulation Resistance: 5000 M Ohm Min.
Current Rating: 1 A Max.
Dielectric Withstanding Voltage: 500 VAC for 1 minute.
REFLOW SOLDER CAPABLE TO 265°C ^{+5°}_{-0°} PER TEST SPEC.



PCB HOLE LAYOUT



深圳市连欣科技有限公司
Shenzhen City Lianxin Technology Co. LTD

NAME: BS系列 CR2032-9 卧式插件DIP		PART NO: XDBS-CR2032-9	
SIZE	FSCM NO.	DWG NO.	REV
SCALE		SHEET	

