






Rev	ECN Number	Description	Date	Drawn	Checkd	Approved



- NOTES :
- 1.0. RATING :
 - 1.1. VOLTAGE :60 VAC (R.M.S.)
 - 1.2. NOMINAL CHARACTERISTIC IMPEDANCE: 50 Ohm
 - 1.3. APPLICABLE FREQUENCY: DC ~ 6GHz
 - 1.4. VSWR: 1.3 MAX. (DC~3GHz), 1.5 MAX. (3~6GHz)
 - 1.5. TEMPERATURE : -40° C TO +85° C
 - 1.6. APPLIED TO IR SOLDERING PROCESS
 - 2.0. MATERIAL SEE BILL OF MATERIAL :
 - 2.1. HOUSING: THERMOPLASTIC, UL94V-0,
 - 2.2. CENTER CONTACT : COPPER ALLOY.
 - 2.3. SHELL CONTACT: COPPER ALLOY.

东莞市文章济美电子有限公司 Dongguan wenzhangjimei Electronics Co., LTD	GENERAL TOLERANCE		SCALE: 1:1		SIZE:	DATE:	SWG. NO	TITLE FR01(成品图)	REV
	XX. ±0.40		UNIT: mm		CHECK	DATE:	PARTS NO. (INTENDED USE) 5001-RF00001-03R1-00		SHEET
	X. ±0.25	X.° ±0°				DATE:			
	.X±0.13	.X° ±0°				DATE:			
	.XX±0.05	.XX° ±0.5°	SIZE: A4		APPROVE	DATE:			
A <									