



承認書

SPECIFICATION FOR APPROVAL

CUSTOMER:

DESCRIPTION:

WIRE WOUND CHIP INDUCTOR

PART NO:

MWI0603IF系列

CUST. PART NO:

REV. NO.

A0

DRAWING		
PREPARED	CHECKED	APPROVED
邹声平	卢嘉良	曾凡强
DATE:	2025/5/1	

CUSTOMER APPROVE



东莞市铭易轩电子科技有限公司

DongGuan Ming Yixuan Electronic Technology Co., LTD

地址: 广东省东莞市大朗镇景泰路20号VV大厦

电话: 15970768093 , 13640935893

网址: <http://www.dgmingyixuan.com>




CUSTOMER:		REV. NO.	A0
PART NO:	MWI0603IF系列	PAGE NO:	1/7
CUST. PART NO:		DATE:	2025/5/1

MODIFY RECORD 变更履历


[illegible]

CUSTOMER:		REV. NO.	A0
PART NO:	MWI0603IF系列	PAGE NO:	2/7
CUST. PART NO:		DATE:	2025/5/1

1. SHAPE & DIMENSION (UNIT:mm)


Recommended patterns

L	W	T	E	F	D
1.8 Max.	1.25 Max.	1.1Max.	0.64 Max.	1.02 Typ.	0.64 Typ.

2. SCHEMATIC

3. PART NUMBERING SYSTEM

MWI	0603	IF	2R2	K	S	T	-	HF
1	2	3	4	5	6	7		8

- 1 PRODUCT SYMBOL (产品代号)
- 2 DIMENSIONS (规格尺寸)
- 3 MATERIAL (芯片类型)
- 4 INDUCTANCE (电感量)
- 5 TOLERANCE (公差) : J±5%; K±10%; M±20%
- 6 TERMINAL (端电极材料) : S-锡端头
- 7 PACKAGING (包装方式) : T-编带盘装; B-散装
- 8 E.P. (环保) : LF—Lead Free HF—Halogen Free FP—Red Phosphor Free

APPROVED	CHECKED	PREPARED
曾凡强	卢嘉良	邹声平

CUSTOMER:		REV. NO.	A0
PART NO:	MWI0603IF系列	PAGE NO:	3/7
CUST. PART NO:		DATE:	2025/5/1

4. ELECTRICAL CHARACTERISTICS

No.	Part Number	L	Freq	Q	SRF	Rdc	Irms	Tolerance
		(uH)	(MHz)	(Min.)	(MHz) Typ.	(Ω)Max.	(mA) Typ.	
1	MWI0603IFR12□ST-HF	0.12	7.9	12	1000	0.15	1000	K,M
2	MWI0603IFR15□ST-HF	0.15	7.9	12	950	0.15	1000	K,M
3	MWI0603IFR18□ST-HF	0.18	7.9	12	950	0.2	1000	K,M
4	MWI0603IFR22□ST-HF	0.22	7.9	12	775	0.3	700	K,M
5	MWI0603IFR27□ST-HF	0.27	7.9	12	775	0.3	700	K,M
6	MWI0603IFR33□ST-HF	0.33	7.9	12	725	0.32	600	K,M
7	MWI0603IFR39□ST-HF	0.39	7.9	12	620	0.51	500	K,M
8	MWI0603IFR47□ST-HF	0.47	7.9	12	540	0.43	570	K,M
9	MWI0603IFR56□ST-HF	0.56	7.9	12	600	0.65	400	K,M
10	MWI0603IFR68□ST-HF	0.68	7.9	12	500	1	380	K,M
11	MWI0603IFR82□ST-HF	0.82	7.9	12	500	1.3	350	K,M
12	MWI0603IF1R0□ST-HF	1	7.9	12	400	0.81	330	J,K,M
13	MWI0603IF1R2□ST-HF	1.2	7.9	12	380	1.7	320	J,K,M
14	MWI0603IF1R5□ST-HF	1.5	7.9	12	300	1.3	310	J,K,M
15	MW10603IF1R8□ST-HF	1.8	7.9	12	180	2.2	300	J,K,M
16	MWI0603IF2R2□ST-HF	2.2	7.9	12	180	2.3	280	J,K,M
17	MWI0603IF2R7□ST-HF	2.7	7.9	12	150	2.6	250	J,K,M
18	MWI0603IF3R3□ST-HF	3.3	7.9	12	150	2.9	230	J,K,M
19	MWI0603IF3R9□ST-HF	3.9	7.9	12	100	2	200	J,K,M
20	MWI0603IF4R7□ST-HF	4.7	7.9	12	100	4	200	J,K,M
21	MWI0603IF5R6□ST-HF	5.6	7.9	12	32	2.6	240	J,K,M
22	MWI0603IF6R8□ST-HF	6.8	7.9	12	31	3.9	200	J,K,M
23	MWI0603IF8R2□ST-HF	8.2	7.9	12	26	4.2	190	J,K,M

□:表示产品公差

APPROVED	CHECKED	PREPARED
曾凡强	卢嘉良	邹声平

CUSTOMER:		REV. NO.	A0
PART NO:	MWI0603IF系列	PAGE NO:	4/7
CUST. PART NO:		DATE:	2025/5/1

4. ELECTRICAL CHARACTERISTICS

No.	Part Number	L	Freq	Q	SRF	Rdc	Irms	Tolerance
		(uH)	(MHz)	(Min.)	(MHz) Typ.	(Ω)Max.	(mA) Typ.	
24	MWI0603IF100□ST-HF	10	2.5	12	25	4.8	180	J,K,M
25	MWI0603IF150□ST-HF	15	2.5	10	23	8.5	170	J,K,M
26	MWI0603IF220□ST-HF	22	2.5	10	10	12	100	J,K,M

□:表示产品公差

Test remarks

- (1). All test data is referenced to 25 °C ambient.
- (2). Irms: DC current that causes the temperature rise ($\Delta T \cong 40^{\circ}\text{C}$) from 25°C ambient.

5. GENERAL SPECIFICATION


- (1). Operating temp.: $-40^{\circ}\text{C} \sim +85^{\circ}\text{C}$ (Including self-generated heat).
- (2). Storage temp.: $-10^{\circ}\text{C} \sim +40^{\circ}\text{C}$ R.H.:60% Max.
- (3). Moisture sensitivity level (MSL) 1
- (4). Recommended products should be used within 12 months from the date of delivery
- (5). The part temperature (ambient + temp rise) should not exceed 85 °C under worst case operating conditions. Circuit design, component placement, PWB trace size and thickness, airflow and other cooling provisions all affect the part temperature. Part temperature should be verified in the end application.

APPROVED	CHECKED	PREPARED
曾凡强	卢嘉良	邹声平

CUSTOMER:		REV. NO.	A0
PART NO:	MWI0603IF系列	PAGE NO:	5/7
CUST. PART NO:		DATE:	2025/5/1

6. SOLDERING CONDITIONS

Figure 1. Re-flow Soldering (Lead Free)



Note:


Preheat circuit and products to 150°C

260°C tip temperature (Max)

Reflow times: no more than 2 times

Solder paste thickness: the best 0.08mm is ,but max is 0.1mm

Figure 2. Hand Soldering



Note:


Use a 20 watt soldering iron with tip diameter of 1.0mm

Limit soldering time to 3 sec.


APPROVED	CHECKED	PREPARED
曾凡强	卢嘉良	邹声平

CUSTOMER:		REV NO:	A0
PART NO:	MWI0603IF系列	PAGE NO:	6/7
CUST. PART NO:		DATE:	2025/5/1


7. PACKAGE SPECIFICATION



胶带 POLYSTYRENE TAPE



Peeling off force
Pull strength
0402~1210: 20g~80g
Speed of peeling off:
300mm/min±10%






	A	B	T
胶带	1.15Typ.	1.83Typ.	0.95Typ.

ΦA	ΦB	ΦC	ΦD	E	W	t
178Typ.	60Typ.	13Typ.	21Typ.	2Typ.	8.4Typ.	2Typ.

包装数量(PACKAGING QUANTITY): 4000Pcs/盘

APPROVED	CHECKED	PREPARED
曾凡强	卢嘉良	邹声平

CUSTOMER:		REV NO:	A0
PART NO:	MWI0603IF系列	PAGE NO:	7/7
CUST. PART NO:		DATE:	2025/5/1

8.Package Specifications
Inside Box And Outside Carton


卷轴数量	→	内盒包装数量	→	外箱包装数量
每卷:4000PCS		每盒四盘，共16000 PCS		小箱6盒，共96000 PCS
				中箱8盒，共128000 PCS
				大箱10盒，共160000 PCS

内盒包装尺寸	→	外箱包装尺寸
20.3*19.3*5.5cm		小箱，40.6*23*19.7cm
		中箱，41*22*26cm
		大箱，41*22*33cm

APPROVED	CHECKED	PREPARED
曾凡强	卢嘉良	邹声平