

[illegible]

NOTES1:

UL Standard

1

2.Torque value: M4, 10.53Lb.in

3.Wire range: 20~6AWG

IEC Standard

1

2. Torque value: M4, 1.2Nm

3.wire range: 2.5~10mm<sup>2</sup>

NOTES2:

- 1.Housing: PA66(UL94V-0)
- 2.Solder Pin: Copper alloy(Sn Plated)
- 3.Cage: Brass(Ni Plated)
- 4.Screw: Steel(M4,Zn Plated)

NOTES3:

- 1.Pitch: 10.16mm Poles: 02-24P  
2.Stripping length: 11-12mm  
3.Operating temperature: -40℃~+105℃  
4.RoHS Compliance

## How to order

MX135T - 10.16 - XXP - XXXX - XX - X - X

产品型号 间距 颜色: 极数 01:常规颜色 02-99:定制颜色 A-Z其他定制

灰色:GY 橙色:OE 0:Y一字螺丝 1:S十字螺丝 2:PS平头十字螺丝

蓝色:BU 红色:RD 定制颜色

黑色:BK 透明色:TT

绿色:GN 黄色:YW

白色:WE

Cu:铜方块 Fe:铁方块

| ITEM                                                                                                                                            | NAME OF PART |      | NO. OF PART | Q"TY   | MATERIAL         |          | NOTE                                                                                  |   |
|-------------------------------------------------------------------------------------------------------------------------------------------------|--------------|------|-------------|--------|------------------|----------|---------------------------------------------------------------------------------------|---|
| DWG.                                                                                                                                            | CKK          | DATE | 23.10.20    | UNITS  | MM               | SHEET/OF | 1 / 1                                                                                 | A |
| CHK.                                                                                                                                            |              | DATE |             | SCALE  | 1 : 1            | A4       |  |   |
| APP.                                                                                                                                            |              | DATE |             | NAME   | MX135T-10.16-XXP |          |                                                                                       |   |
| <div>CIXI MAIXU ELECTRONICS CO.,LTD.<br/>慈溪市迈旭电子有限公司</div> |              |      |             |        |                  |          |                                                                                       |   |
|                                                                                                                                                 |              |      |             | DWGN0. |                  |          |                                                                                       |   |