






REV.	ECN NO.	REVISED	DATE



技术要求:

- 1、截剪断面毛刺高度 $\leq 0.03\text{mm}$;
- 2、部件要求平整,无变形、裂纹、损伤等外观缺陷;

UNLESS OTHERWISE SPECIFIED TOLERANCES		MYOUNG 美阳 www.meiyangdz.com			
DECIMALS:	ANGLES:	DSND	YangFeng	DATE	2020-08-25
X :±0.30	X :±1°	CHKD	ZhouRuicai	DATE	2020-08-25
X.X :±0.25	X.X :±0.5°	APVD	XueShunyong	DATE	2020-08-25
X.XX :±0.20					
X.XXX :±0.10					
WEIGHT:		SCALE:	SIZE: A4	VIEW:	⊕ ⊞
SHEET 1 OF 1		UNIT: mm	REV.: A/0	OBJECT: MY	

1	TERMINAL(+)	1	STEEL T=0.3MM	Ni-Plating
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR