



承認書

SPECIFICATION FOR APPROVAL

CUSTOMER:

DESCRIPTION:

WIRE WOUND CHIP INDUCTOR

PART NO:

MWI0805LD-C系列

CUST. PART NO:

REV. NO.

A0

DRAWING		
PREPARED	CHECKED	APPROVED
邹声平	卢嘉良	曾凡强
DATE:	2025/5/1	

CUSTOMER APPROVE



东莞市铭易轩电子科技有限公司

DongGuan Ming Yixuan Electronic Technology Co., LTD


地址: 广东省东莞市大朗镇景泰路20号VV大厦

电话: 15970768093 , 13640935893

网址: <http://www.dgmingyixuan.com>


[illegible]

CUSTOMER:		REV. NO.	A0
PART NO:	MWI0805LD-C系列	PAGE NO:	2/7
CUST. PART NO:		DATE:	2025/5/1

1. SHAPE & DIMENSION (UNIT:mm)


Recommended patterns

L	W	T	E	F	D
2.4 Max.	1.73 Max.	1.52 Max.	1.02 Typ.	1.78 Typ.	0.76 Typ.

2. SCHEMATIC

3. PART NUMBERING SYSTEM

MWI	0805	LD	220	K	S	T	-	C	-	HF
1	2	3	4	5	6	7		8		9

- 1 PRODUCT SYMBOL (产品代号)
- 2 DIMENSIONS (规格尺寸)
- 3 MATERIAL (芯片类型)
- 4 INDUCTANCE (电感量)
- 5 TOLERANCE (公差) : J±5%; K±10%; M±20%
- 6 TERMINAL (端电极材料): S-锡端头
- 7 PACKAGING (包装方式): T-编带盘装; B-散装
- 8 Color (颜色): C-点色
- 9 E.P. (环保): LF—Lead Free HF—Halogen Free FP—Red Phosphor Free

APPROVED	CHECKED	PREPARED
曾凡强	卢嘉良	邹声平

CUSTOMER:		REV. NO.	A0
PART NO:	MWI0805LD-C系列	PAGE NO:	3/7
CUST. PART NO:		DATE:	2025/5/1

4. ELECTRICAL CHARACTERISTICS

No.	Part Number	L	Freq	Q	SRF	Rdc	Irms	Tolerance	Color
		(uH)	(MHz)	(Typ.)	(MHz)Typ.	(Ω)Max.	(mA)Typ.		
1	MWI0805LDR68□ST-C-HF	0.68	7.9	14	765	0.19	1200	K,M	Grey
2	MWI0805LD1R0□ST-HF	1	7.9	14	208	0.17	1100	K,M	\
3	MWI0805LD1R2□ST-C-HF	1.2	7.9	14	208	0.17	960	K,M	Red
4	MWI0805LD1R5□ST-C-HF	1.5	7.9	14	130	0.22	880	K,M	Brown
5	MWI0805LD1R8□ST-C-HF	1.8	7.9	14	112	0.26	860	K,M	Orange
6	MWI0805LD2R2□ST-C-HF	2.2	7.9	12	80	0.31	740	K,M	Red
7	MWI0805LD3R3□ST-C-HF	3.3	7.9	12	50	0.36	620	K,M	Orange
8	MWI0805LD4R7□ST-C-HF	4.7	7.9	14	51	0.56	520	K,M	Yellow
9	MWI0805LD5R6□ST-C-HF	5.6	7.9	12	42	0.65	480	K,M	Blue
10	MWI0805LD6R8□ST-C-HF	6.8	7.9	14	35	0.88	420	K,M	Green
11	MWI0805LD8R2□ST-C-HF	8.2	7.9	13	33	0.94	400	K,M	Purple
12	MWI0805LD100□ST-C-HF	10	2.5	14	25	1.17	300	J,K,M	Blue
13	MWI0805LD120□ST-C-HF	12	2.5	14	30	1.50	290	J,K,M	Grey
14	MWI0805LD150□ST-C-HF	15	2.5	15	28	1.82	280	J,K,M	Purple
15	MWI0805LD180□ST-C-HF	18	2.5	15	27	2.01	260	J,K,M	White
16	MWI0805LD220□ST-C-HF	22	2.5	15	20	2.29	240	J,K,M	Grey
17	MWI0805LD470□ST-HF	47	2.5	14	15	4.42	160	J,K,M	\
18	MWI0805LD560□ST-C-HF	56	2.5	14	10	5.75	150	J,K,M	Yellow
19	MWI0805LD680□ST-C-HF	68	2.5	14	10	5.90	140	J,K,M	Brown
20	MWI0805LD820□ST-C-HF	82	2.5	14	10	9.75	100	J,K,M	Orange
21	MWI0805LD101□ST-C-HF	100	1.0	10	5	9.75	100	J,K,M	Red

□:表示产品公差

Test remarks

- (1). All test data is referenced to 25 °C ambient.
- (2). Irms: DC current that causes the temperature rise ($\Delta T \cong 40^{\circ}\text{C}$) from 25°C ambient.

5. GENERAL SPECIFICATION


- (1). Operating temp.: -40°C ~ +85°C (Including self-generated heat).
- (2). Storage temp.: -10°C ~ +40°C R.H.:60% Max.
- (3). Moisture sensitivity level (MSL) 1
- (4). Recommended products should be used within 12 months from the date of delivery
- (5). The part temperature (ambient + temp rise) should not exceed 85 °C under worst case operating conditions. Circuit design, component placement, PWB trace size and thickness, airflow and other cooling provisions all affect the part temperature. Part temperature should be verified in the end application.

APPROVED	CHECKED	PREPARED
曾凡强	卢嘉良	邹声平

CUSTOMER:		REV. NO.	A0
PART NO:	MWI0805LD-C系列	PAGE NO:	5/7
CUST. PART NO:		DATE:	2025/5/1

6. SOLDERING CONDITIONS

Figure 1. Re-flow Soldering (Lead Free)



Note:


Preheat circuit and products to 150°C

260°C tip temperature (Max)

Reflow times: no more than 2 times

Solder paste thickness: the best 0.08mm is ,but max is 0.1mm

Figure 2. Hand Soldering





Note:

Use a 20 watt soldering iron with tip diameter of 1.0mm


Limit soldering time to 3 sec.

APPROVED	CHECKED	PREPARED
曾凡强	卢嘉良	邹声平

CUSTOMER:		REV NO:	A0
PART NO:	MWI0805LD-C系列	PAGE NO:	6/7
CUST. PART NO:		DATE:	2025/5/1

7. PACKAGE SPECIFICATION

胶带 POLYSTYRENE TAPE


Peeling off force
 Pull strength
 0402~1210:20g~80g
 Speed of peeling off:
 300mm/min $\pm$ 10%



胶带		A	B	T
	0805	1.9	2.4	1.45

Type	ΦA	ΦB	ΦC	ΦD	E	W	t
0805	178	60	13	21	2	8.4	2


包装数量(PACKAGING QUANTITY): 2000Pcs/盘

APPROVED	CHECKED	PREPARED
曾凡强	卢嘉良	邹声平

CUSTOMER:		REV NO:	A0
PART NO:	MWI0805LD-C系列	PAGE NO:	7/7
CUST. PART NO:		DATE:	2025/5/1

8. Package Specifications

Inside Box And Outside Carton



卷轴数量
每卷:2000PCS



内盒包装数量
每盒四盘，共8000 PCS



外箱包装数量
小箱6盒，共48000 PCS
中箱8盒，共64000 PCS
大箱10盒，共80000 PCS

内盒包装尺寸
20.3*19.3*5.5cm



外箱包装尺寸
小箱，40.6*23*19.7cm
中箱，41*22*26cm
大箱，41*22*33cm

APPROVED	CHECKED	PREPARED
曾凡强	卢嘉良	邹声平