



承認書

SPECIFICATION FOR APPROVAL

CUSTOMER:

DESCRIPTION:

WIRE WOUND CHIP INDUCTOR

PART NO:

MWI0805QD系列

CUST. PART NO:

REV. NO.

A0

DRAWING		
PREPARED	CHECKED	APPROVED
邹声平	卢嘉良	曾凡强
DATE:	2025/5/1	

CUSTOMER APPROVE



东莞市铭易轩电子科技有限公司

DongGuan Ming Yixuan Electronic Technology Co., LTD

地址: 广东省东莞市大朗镇景泰路20号VV大厦

电话: 15970768093 , 13640935893

网址: <http://www.dgmingyixuan.com>




CUSTOMER:		REV. NO.	A0
PART NO:	MWI0805QD系列	PAGE NO:	1/6
CUST. PART NO:		DATE:	2025/5/1


MODIFY RECORD 变更履历

[illegible]

CUSTOMER:		REV. NO.	A0
PART NO:	MWI0805QD系列	PAGE NO:	2/6
CUST. PART NO:		DATE:	2025/5/1

1. SHAPE & DIMENSION (UNIT:mm)


L	W	T	E	F	D
2.4 Max.	1.73 Max.	1.52 Max.	1.02 Typ.	1.78 Typ.	0.76 Typ.

2. SCHEMATIC

3. PART NUMBERING SYSTEM

MWI	0805	QD	2R2	M	S	T	-	HF
1	2	3	4	5	6	7		8

- PRODUCT SYMBOL (产品代号)
- DIMENSIONS (规格尺寸)
- MATERIAL (芯片类型)
- INDUCTANCE (电感量)
- TOLERANCE (公差) : K $\pm$ 10%; M $\pm$ 20%
- TERMINAL (端电极材料) : S-锡端头
- PACKAGING (包装方式) : T-编带盘装; B-散装
- E.P. (环保) : LF—Lead Free HF—Halogen Free FP—Red Phosphor Free

APPROVED	CHECKED	PREPARED
曾凡强	卢嘉良	邹声平

CUSTOMER:		REV. NO.	A0
PART NO:	MWI0805QD系列	PAGE NO:	3/6
CUST. PART NO:		DATE:	2025/5/1

4. ELECTRICAL CHARACTERISTICS

No.	Part Number	L	Freq	Q	SRF	Rdc±30%	Isat	Irms
		(uH)	(MHz)	(Typ.)	(MHz)Typ.	(Ω)	(mA)Typ.	(mA)Typ.
1	MWI0805QD1R0MST-HF	1	1	10	550	0.12	1200	1000
2	MWI0805QD1R5MST-HF	1.5	1	10	450	0.13	900	900
3	MWI0805QD2R2MST-HF	2.2	1	10	400	0.18	780	750
4	MWI0805QD4R7MST-HF	4.7	1	10	150	0.33	510	470
5	MWI0805QD6R8MST-HF	6.8	1	10	50	0.35	470	450
6	MWI0805QD100MST-HF	10	1	10	35	0.53	410	450
7	MWI0805QD150MST-HF	15	1	10	25	0.65	270	350
8	MWI0805QD220MST-HF	22	1	9	10	0.95	270	300

产品公差: K±10%; M±20%

Test remarks

- (1).All test data is referenced to 25 °C ambient.
- (2). Isat: DC current at which inductance drops approximate 30% from its value without current,
- Irms: DC current that causes the temperature rise ($\Delta T \leq 40^{\circ}\text{C}$) from 25°C ambient.

5. GENERAL SPECIFICATION


- (1). Operating temp.: -40°C ~ +85°C (Including self-generated heat).
- (2). Storage temp.: -10°C ~ +40°C R.H.:60% Max.
- (3). Moisture sensitivity level (MSL) 1
- (4). Recommended products should be used within 12 months from the date of delivery
- (5). The part temperature (ambient + temp rise) should not exceed 85 °C under worst case operating conditions. Circuit design, component placement, PWB trace size and thickness, airflow and other cooling provisions all affect the part temperature. Part temperature should be verified in the end application.

APPROVED	CHECKED	PREPARED
曾凡强	卢嘉良	邹声平

CUSTOMER:		REV. NO.	A0
PART NO:	MWI0805QD系列	PAGE NO:	4/6
CUST. PART NO:		DATE:	2025/5/1

6. SOLDERING CONDITIONS

Figure 1. Re-flow Soldering (Lead Free)



Note:


Preheat circuit and products to 150°C

260°C tip temperature (Max)

Reflow times: no more than 2 times

Solder paste thickness: the best 0.08mm is ,but max is 0.1mm

Figure 2. Hand Soldering



Note:


Use a 20 watt soldering iron with tip diameter of 1.0mm

Limit soldering time to 3 sec.


Appearance Defect	Graphic	Judging Standard
Copper wire exposed		Area of copper wire exposed in magnetic shield area less than 0.06 square millimeter is OK.
APPROVED	CHECKED	PREPARED
曾凡强	卢嘉良	邹声平

CUSTOMER:		REV NO:	A0
PART NO:	MWI0805QD系列	PAGE NO:	5/6
CUST. PART NO:		DATE:	2025/5/1

7. PACKAGE SPECIFICATION




胶带 POLYSTYRENE TAPE



Peeling off force

Full strength
0402~1210:20g~80g

Speed of peeling off:
300mm/min±10%






胶带		A	B	T	Type	ΦA	ΦB	ΦC	ΦD	E	W	t	R
	0805	1.85	2.4	1.45	0805	178	60	13	21	2	8.4	2	1

包装数量(PACKAGING QUANTITY): 2000Pcs/盘

APPROVED	CHECKED	PREPARED
曾凡强	卢嘉良	邹声平

CUSTOMER:		REV NO:	A0
PART NO:	MWI0805QD系列	PAGE NO:	6/6
CUST. PART NO:		DATE:	2025/5/1

8. Package Specifications
Inside Box And Outside Carton


卷轴数量
每卷:2000PCS



内盒包装数量
每盒四盘，共8000 PCS



外箱包装数量
小箱6盒，共48000 PCS
中箱8盒，共64000 PCS
大箱10盒，共80000 PCS

内盒包装尺寸
20.3*19.3*5.5cm



外箱包装尺寸
小箱，40.6*23*19.7cm
中箱，41*22*26cm
大箱，41*22*33cm

APPROVED	CHECKED	PREPARED
曾凡强	卢嘉良	邹声平