



REV.	ECN NO.	LOCATION	REVISIONS		
			DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A	(A1)X4	产品外观及尺寸变更, 图面升级整理图面	2025.04.29	阿树







■SPECIFICATIONS

- Voltage rating:125V AC/DC
- Current rating:1A AC/DC
- Withstanding Voltage:250V AC/minute
- Temperature range:-45°C+125°C
- Insulation resistance:100MΩ
- Contact resistance:20mΩ MAX

PART NO.:

X9821 W V S-XX-9T SN
① ② ③ ④ ⑤ ⑥ ⑦

- ①Series No
②Category:W-Wafer
③Welding Board Angle:V-Stright 180°
④Welding Way: S-SMT
⑤Row No.Pin No:XX-02~16Pin
⑥Material:9T-PA9T UL94V-0
⑦Planting: SN-Bright tin plating



Poles	Dimensions(mm)		
	A	B	C
02	1.25	4.25	7.55
03	2.50	5.50	8.80
04	3.75	6.75	10.05
05	5.00	8.00	11.30
06	6.25	9.25	12.55
07	7.50	10.50	13.80
08	8.75	11.75	15.05
09	10.00	13.00	16.30
10	11.25	14.25	17.55
11	12.50	15.50	18.80
12	13.75	16.75	20.05
13	15.00	18.00	21.30
14	16.25	19.25	22.55
15	17.50	20.50	23.80
16	18.75	21.75	25.05

X9821WVS-XX-9TSN	PA9T UL 94V-0	Brass	Tin-Plated	X9821H
PART NO	Material	Material(pin)	Finish(pin)	Suitable XKB Terminal

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:	MODEL TYPE: 1.25mm Crimp Style Connectors
CHECKED		UNIT: mm/in	PART NO.: X9821WVS-XX-9TSN
APPROVED		SIZE: A4	DWG NO.: