


30V N-Channel and P-Channel MOSFET

Features

- Trench Power LV MOSFET technology
- High density cell design for Low $R_{DS(ON)}$
- High Speed switching

Application


- Battery protection
- Power management
- Load switch




Marking and pin assignment

Product Summary

V_{DS}	$R_{DS(ON)}$ MAX	I_D MAX
30V	20m Ω @10V	8A
	28m Ω @4.5V	
-30V	22m Ω @-10V	-7A
	40m Ω @-4.5V	



SOP-8 top view



Schematic diagram



Halogen-Free

Absolute Maximum Ratings ($T_A=25^{\circ}\text{C}$ unless otherwise noted)

Symbol	Parameter	N-Channel	P-Channel	Unit
--------	-----------	-----------	-----------	------

Common Ratings ($T_C=25^{\circ}\text{C}$ Unless Otherwise Noted)

V _{DS}	Drain-Source Breakdown Voltage		30	-30	V
V _{GS}	Gate-Source Voltage		±20	±20	V
T _J	Maximum Junction Temperature		150	150	°C
T _{STG}	Storage Temperature Range		-55 to 150	-55 to 150	°C
I _S	Diode Continuous Forward Current	Tc=25°C	8	-7	A







Mounted on Large Heat Sink

I_{DM}	Pulse Drain Current Tested	$T_C=25^{\circ}\text{C}$	40	-40	A
I_D	Continuous Drain Current	$T_C=25^{\circ}\text{C}$	8	-7	A
P_D	Maximum Power Dissipation	$T_C=25^{\circ}\text{C}$	2	2	W
$R_{\theta JA}$	Thermal Resistance Junction-Ambient		62.5	62.5	$^{\circ}\text{C/W}$







N-Ch Electrical Characteristics (TJ=25°C unless otherwise noted)						
Symbol	Parameter	Condition	Min	Typ	Max	Unit
Static Electrical Characteristics @ TJ = 25°C (unless otherwise stated)						
BV _{(BR)DSS}	Drain-Source Breakdown Voltage	V _{GS} =0V, I _D =250μA	30	--	--	V
I _{DSS}	Zero Gate Voltage Drain Current	V _{DS} =30V, V _{GS} =0V	--	--	1	μA
I _{GSS}	Gate-Body Leakage Current	V _{GS} =±20V, V _{DS} =0V	--	--	±100	nA
V _{GS(th)}	Gate Threshold Voltage	V _{DS} =V _{GS} , I _D =250μA	1.2	1.5	2.4	V
R _{DS(on)}	Drain-Source On-State Resistance	V _{GS} =10V, I _D =8A	--	13	20	mΩ
		V _{GS} =4.5V, I _D =6A	--	17	28	mΩ
Dynamic Electrical Characteristics @ TJ = 25°C (unless otherwise stated)						
C _{ISS}	Input Capacitance	V _{DS} =15V, V _{GS} =0V, f=1MHz	--	740	--	pF
C _{OSS}	Output Capacitance		--	110	--	pF
C _{RSS}	Reverse Transfer Capacitance		--	82	--	pF
Switching Characteristics						
Qg	Total Gate Charge	V _{DS} =15V, I _D =8A, V _{GS} =10V	--	15	--	nC
Qgs	Gate Source Charge		--	2.5	--	nC
Qgd	Gate Drain Charge		--	3	--	nC
td(on)	Turn-on Delay Time	V _{DS} =15V, R _L =1.8Ω, V _{GS} =10V, R _G =3Ω	--	5	--	nS
tr	Turn-on Rise Time		--	3.5	--	nS
td(off)	Turn-Off Delay Time		--	19	--	nS
tf	Turn-Off Fall Time		--	3.5	--	nS
Source- Drain Diode Characteristics						
V _{SD}	Forward on voltage	Tj=25°C, Is=8A	--	--	1.2	V


P-Ch Electrical Characteristics (TJ=25°C unless otherwise noted)						
Symbol	Parameter	Condition	Min	Typ	Max	Unit
Static Electrical Characteristics @ TJ = 25°C (unless otherwise stated)						
BV _{(BR)DSS}	Drain-Source Breakdown Voltage	V _{GS} =0V, I _D =-250μA	-30	--	--	V
I _{DSS}	Zero Gate Voltage Drain Current	V _{DS} =-30V, V _{GS} =0V	--	--	-1	μA
I _{GSS}	Gate-Body Leakage Current	V _{GS} =±20V, V _{DS} =0V	--	--	±100	nA
V _{GS(th)}	Gate Threshold Voltage	V _{DS} =V _{GS} , I _D =-250μA	-1.4	-1.6	-2.5	V
R _{DS(on)}	Drain-Source On-State Resistance	V _{GS} =-10V, I _D =-7.0A	--	19	22	mΩ
		V _{GS} =-4.5V, I _D =-3.5A	--	30	40	mΩ
Dynamic Electrical Characteristics @ TJ = 25°C (unless otherwise stated)						
C _{ISS}	Input Capacitance	V _{DS} =-15V, V _{GS} =0V, f=1MHz	--	1040	--	pF
C _{OSS}	Output Capacitance		--	179	--	pF
C _{RSS}	Reverse Transfer Capacitance		--	134	--	pF
Switching Characteristics						
Q _g	Total Gate Charge	V _{DS} =-15V, I _D =-7A, V _{GS} =-10V	--	19	--	nC
Q _{gs}	Gate Source Charge		--	3.6	--	nC
Q _{gd}	Gate Drain Charge		--	4.6	--	nC
t _{d(on)}	Turn-on Delay Time	V _{DD} =-15V, I _D =-7A, V _{GS} =-10V, R _G =3Ω	--	10	--	nS
t _r	Turn-on Rise Time		--	5.5	--	nS
t _{d(off)}	Turn-Off Delay Time		--	26	--	nS
t _f	Turn-Off Fall Time		--	9	--	nS
Source- Drain Diode Characteristics						
V _{SD}	Forward on voltage	Tj=25°C, Is=-7A	--	--	-1.2	V

N-Channel Typical Operating Characteristics



P-Channel Typical Operating Characteristics



SOP-8 Package information


Symbol	Dimensions in Millimeters(mm)		Dimensions In Inches	
	Min	Max	Min	Max
A	1.450	1.750	0.057	0.068
A1	0.100	0.250	0.003	0.009
A2	1.350	1.550	0.053	0.061
b	0.330	0.510	0.012	0.020
c	0.170	0.250	0.006	0.009
D	4.700	5.100	0.185	0.200
e	1.270(BSC)		0.050(BSC)	
E	3.800	4.000	0.149	0.157
E1	5.800	6.200	0.228	0.244
L	0.400	1.270	0.015	0.050
θ	0°	8°	0°	8°