

**Harvatek 4.8x2.5x4.5mm SIDE LOOK PT LED****HV-1302559B-H2-L2**

Official Product	HV-1302559B-H2-L2	Customer Part No.		Data Sheet No.
	*****	*****		CDAE-040-051
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Nov. 11 2019	Version of 1.1	Page 1/11

## DISCLAIMER

HARVATEK reserves the right to make changes without further notice to any products herein to improve reliability, function or design. HARVATEK does not assume any liability arising out of the application or use of any product or circuit described herein; neither does it convey any license under its patent rights, nor the rights of others.

## LIFE SUPPORT POLICY

HARVATEK's products are not authorized for use as critical components in life support devices or systems without the express written approval of the President of HARVATEK or HARVATEK INTERNATIONAL. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
2. A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

Official Product	HV-1302559B-H2-L2	Customer Part No.		Data Sheet No.
	*****	*****		CDAE-040-051
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Nov. 11 2019	Version of 1.1	Page 2/11

## Compliance and Certification

ISO9002, QS9000 and ISO14001 Certified

RoHS Compliant



## Orderable Information

H V - 1 3 0 2 5 5 9 B - H 2 - L 2


Series Name	Color Code	Remark
HV : HARVATEK	130 : 940 nm Silicon PT Chip 2559: 4.8x2.5x4.5mm Side Look LED. B : Black Transparent. H2-L2:HARVATEK Part No.	

## Features:

- Stable Color
- Popular 4.8x2.5x4.5mm through hole package.
- Black Transparent Lens.

Official Product	HV-1302559B-H2-L2	Customer Part No.	Data Sheet No.
	*****	*****	CDAE-040-051
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Nov. 11 2019	Version of 1.1
			Page 3/11

## Package Dimensions



### Notes:

- 1.All dimensions are millimeters.
- 2.Tolerance is +/-0.25mm unless otherwise noted.
- 3.Specifications are subject to change without notice.

Official Product	HV-1302559B-H2-L2	Customer Part No.	Data Sheet No.
	*****	*****	CDAE-040-051
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Nov. 11 2019	Version of 1.1
		Page 4/11	

**Absolute Maximum Ratings at Ta=25°C**

Parameter	Symbol	Rating	Unit
Collector Current	Ic	20	mA
Operating Temperature	Topr	-40to+85	°C
Storage Temperature	Tstg	-40to+100	°C
Soldering Temperature*1	Tsol	260±5	°C
Power Dissipation	Pd	75	mW
Collector-Emitter Voltage	Vceo	30	V
Emitter-Collector Voltage	Veco	5	V

\*1: Soldering time  $\leq$  5 seconds.

Official Product	HV-1302559B-H2-L2	Customer Part No.		Data Sheet No.
	*****	*****		CDAE-040-051
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Nov. 11 2019	Version of 1.1	Page 5/11

## Electrical and Optical Characteristic

Parameter	Symbol	Condition	Min.	Typ.	Max.	Unit
On State Collector Current	$I_{C(on)}$	$V_{ce}=5V$ $E_e=0.555mW/cm^2$	129	/	1085	$\mu A$
Collector Dark Current	$I_d$	$V_{ce}=20V$	/	/	100	nA
Collector – Emitter Breakdown Voltage	$BV_{ceo}$	$I_c=100\mu A$	30	/	/	V
Emitter-Collector Breakdown Voltage	$B V_{eco}$	$I_e=100\mu A$	5	/	/	V
Collector-Emitter Saturation Voltage	$V_{ce(sat)}$	$I_c=0.5mA$ $I_F=20 mA$	/	/	0.4	V
Peak Wavelength	$\lambda_p$	/	/	940	/	nm
Rang of Spectral Bandwidth	$\Delta\lambda$	/	760	940	1100	nm
Rise Time	$t_r$	$V_{CE}=5V$ $I_C=1mA$ $R_L=1000\Omega$	/	15	/	$\mu S$
Fall Time	$t_f$		/	15	/	$\mu S$




Official Product	HV-1302559B-H2-L2	Customer Part No.		Data Sheet No.
	*****	*****		CDAE-040-051
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Nov. 11 2019	Version of 1.1	Page 6/11

**Specifications for Bin Grading:**

Ic(mA)		
Grade	Min.	Max.
A1	0.129	0.25
A2	0.17	0.322
A3	0.242	0.384
A4	0.304	0.458
A5	0.378	0.532
A6	0.452	0.607
A7	0.527	0.682
A8	0.602	0.767
A9	0.767	0.843
A10	0.763	0.916
A11	0.836	0.987
A12	0.907	1.085

Official Product	HV-1302559B-H2-L2	Customer Part No.		Data Sheet No.
	*****	*****		CDAE-040-051
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Nov. 11 2019	Version of 1.1	Page 7/11

## Typical Electro-Optical Characteristics Curves



Official Product	HV-1302559B-H2-L2	Customer Part No.	Data Sheet No.
	*****	*****	CDAE-040-051
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Nov. 11 2019	Page 8/11
		Version of 1.1	



### Reliability test items and conditions:

The reliability of products shall be satisfied with items listed below.

Confidence level: 97%

LTPD:3%

No	Item	Test Conditions	Test Hours/Cycle	Sample Size	Failure Judgment Criteria	Ac/Er
1	Solder Heat	TEMP:260°C±5°C	10 SEC	76 PCS	$I_v \leq I_{vt} * 0.5$ or $V_f \geq U$ or $V_f \leq L$	0/1
2	Temperature Cycle	H:+100°C 15min ∫ 5min L:-40°C 15min	300 CYCLES	76 PCS		0/1
3	Thermal Shock	H:+100°C 5min ∫ 10sec L:-10°C 5min	300 CYCLES	76 PCS		0/1
4	High Temperature Storage	TEMP:100°C	1000 HRS	76 PCS		0/1
5	Low Temperature Storage	TEMP:-40°C	1000 HRS	76 PCS		0/1
6	DC Operating Life	TEMP:25°C IF=20mA	1000 HRS	76 PCS		0/1
7	High Temperature / High Humidity	85°C/85%RH	1000 HRS	76 PCS		0/1

Note: I<sub>vt</sub>: To test I<sub>v</sub> value of the chip before the reliability test.


I<sub>v</sub>: The test value of the chip that has completed the reliability test

U: Upper Specification Limit

L: Lower Specification Limit

Official Product	HV-1302559B-H2-L2	Customer Part No.		Data Sheet No.
	*****	*****		CDAE-040-051
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Nov. 11 2019	Version of 1.1	Page 9/11

## Packing Specification:



	<b>HARVATEK</b>	
CPN:		<b>RoHs</b>
P/N:		
	HV-1302559B-H2-L2	
QTY:		CAT:
		HUE:
LOT NO:		REF:

Official Product	HV-1302559B-H2-L2	Customer Part No.	Data Sheet No.
	*****	*****	CDAE-040-051
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Nov. 11 2019	Page 10/11

**Revision History**

Revision	Page	Version No.	Revision Date
Initial Release		1.0	09-19-2018
Modifies Electrical and Optical Characteristic	6	1.1	11-11-2019

Official Product	HV-1302559B-H2-L2	Customer Part No.		Data Sheet No.
	*****	*****		CDAE-040-051
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Nov. 11 2019	Version of 1.1	Page 11/11