



Technical drawing of a mechanical part showing dimensions: 1.4, 1.2, 5.5, 2.54, 0.6, and DIM.B.



Contact Rating:	25mA,24V DC
Contact Resistance:	50mΩ max
Insulation Resistance:	100mΩ min.500V DC
Dielectric Strength:	500V AC/1minute
Operating Force:	1000gf max
Travel:	2mm
Operating Life:	3000cycles
Operating Temp:	-20℃~+70℃
Storage Temp:	-40℃~+80℃

PART NO.	NO.OF POS	DIM.A	DIM.B
DS-01	1	4.06	
DS-02	2	6.6	2.54
DS-03	3	9.14	5.08
DS-04	4	11.68	7.62
DS-05	5	14.22	10.16
DS-06	6	16.76	12.7
DS-07	7	19.3	15.24
DS-08	8	21.84	17.78
DS-09	9	24.38	20.32
DS-10	10	26.92	22.86
DS-12	12	32	27.94

4	Terminal		Copper Alloy	T: Tin plated G: Plating Gold ≥ 15M
3	Base	1	PBT	Black
2	Keystone	1	PBT	white
1	Cover	1	PBT	Black Blue Red
ITEM	PART NAME	QTY	MATERIAL	FINISHING

		new		2015/5/3		A		瀚源	
ECN BO.		DESCRIPTION.		DATE.		REV.			
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER			SCALT: 1/2		SCALE: 3:1	
Mikey	Tom	Jerry	PART NAME	DS-XXR	UNLESS OTHERWISE SPECIFIED,TOLERANCE:		X.	±0.25	
			MODEL NAME	DS-XXR			X.x	±0.20	
			3RD ANGLE PROJ	HanElectricity Co.,LTD					X.xx
							ANGULAR	±3°	
							FILE.NO.		