




JIANGSU CHANGJING ELECTRONICS TECHNOLOGY CO., LTD.

SOT-323 Plastic-Encapsulate MOSFETS

CJ3144KW N-channel MOSFET

$V_{(BR)DSS}$	$R_{DS(on)MAX}$	I_D
30 V	500mΩ@4V	0.6A
	600mΩ@2.5V	

SOT-323




Feature

- Surface Mount Package
- N-Channel Switch with Low $R_{DS(on)}$
- Operated at Low Logic Level Gate Drive

Application

- Load/Power Switching
- Interfacing Switching
- Battery Management for Ultra Small Portable Electronics
- Logic Level Shift


MARKING



KM=Device code

Solid dot = Greenmolding compound device.

Equivalent Circuit



MOSFET MAXIMUM RATINGS ($T_a = 25^\circ\text{C}$ unless otherwise noted)

Symbol	Parameter	Value	Unit
V_{DS}	Drain-Source voltage	30	V
V_{GS}	Gate-Source Voltage	± 12	V
I_D	Continuous Drain Current	0.6	A
P_D	Power Dissipation	0.2	W
T_J, T_{stg}	Operation Junction and Storage Temperature Range	-55-150	$^\circ\text{C}$
$R_{\theta JA}$	Thermal Resistance from Junction to Ambient	625	$^\circ\text{C/W}$

MOSFET ELECTRICAL CHARACTERISTICS







$T_a=25\text{ }^{\circ}\text{C}$ unless otherwise specified

Parameter	Symbol	Test Condition	Min	Type	Max	Unit
Static Characteristics ⁽²⁾						
Drain-source breakdown voltage	V _{(BR)DSS}	V _{GS} = 0V, I _D =250μA	30			V
Zero gate voltage drain current	I _{DSS}	V _{DS} =30V,V _{GS} = 0V			1	μA
Gate-body leakage current	I _{GSS}	V _{GS} =±10V, V _{DS} = 0V			±3	μA
Gate threshold voltage ⁽³⁾	V _{GS(th)}	V _{DS} =V _{GS} , I _D =250μA	0.5	1.0	1.5	V
Drain-source on-resistance ⁽³⁾	R _{DS(on)}	V _{GS} =4.5V, I _D =0.6A		320	500	mΩ
		V _{GS} =2.5V, I _D =0.3A		410	600	
Forward tranconductance	g _{FS}	V _{DS} =5V, I _D =0.5A	0.1			S
Dynamic characteristics ⁽⁴⁾						
Input Capacitance	C _{iss}	V _{DS} =10V,V _{GS} =0V,f=1MHz		44		pF
Output Capacitance	C _{oss}			15		
Reverse Transfer Capacitance	C _{rss}			8		
Total gate charge	Q _g	V _{DS} =15V,V _{GS} =4.5V,I _D =0.8A		1.2		nC
Gate-source charge	Q _{gs}			0.28		
Gate-drain charge	Q _{gd}			0.3		
Switching Characteristics ⁽⁴⁾						
Turn-on delay time	t _{d(on)}	V _{DS} =15V,I _D =0.7A, V _{GS} =4.5V,R _G =51Ω		5.0		ns
Turn-on rise time	t _r			8.2		
Turn-off delay time	t _{d(off)}			23		
Turn-off fall time	t _f			41		
Source-Drain Diode characteristics						
Diode Forward voltage ⁽³⁾	V _{DS}	I _S =0.6A, V _{GS} = 0V		0.87	1.2	V


Notes:

1. Repetitive Rating: Pulse width limited by maximum junction temperature.
2. These tests are performed with no heat sink at $T_a=25^{\circ}\text{C}$.
3. Pulse Test : Pulse Width $\leq 300\mu s$, Duty Cycle $\leq 0.5\%$.
4. These parameters have no way to verify.

Typical Characteristics




SOT-323 Package Outline Dimensions



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
A	0.900	1.100	0.035	0.043
A1	0.000	0.100	0.000	0.004
A2	0.900	1.000	0.035	0.039
b	0.200	0.400	0.008	0.016
c	0.080	0.150	0.003	0.006
D	2.000	2.200	0.079	0.087
E	1.150	1.350	0.045	0.053
E1	2.150	2.450	0.085	0.096
e	0.650 TYP		0.026 TYP	
e1	1.200	1.400	0.047	0.055
L	0.525 REF		0.021 REF	
L1	0.260	0.460	0.010	0.018
K	0°	8°	0°	8°

SOT-323 Suggested Pad Layout



Note:


1. Controlling dimension: in millimeters.
2. General tolerance: ± 0.05 mm.
3. The pad layout is for reference purposes only.

NOTICE

JSCJ reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to any product herein. JSCJ does not assume any liability arising out of the application or use of any product described herein.

SOT-323 Tape and reel


SOT-323 Embossed Carrier Tape




Packaging Description:
SOT-323 parts are shipped in tape. The carrier tape is made from a dissipative (carbon filled) polycarbonate resin. The cover tape is a multilayer film (Heat Activated Adhesive in nature) primarily composed of polyester film, adhesive layer, sealant, and anti-static sprayed agent. These reeled parts in standard option are shipped with 3,000 units per 7" or 17.8cm diameter reel. The reels are clear in color and is made of polystyrene plastic (anti-static coated).

Dimensions are in millimeter										
Pkg type	A	B	C	d	E	F	P0	P	P1	W
SOT-323	2.25	2.55	1.19	Ø1.55	1.75	3.50	4.00	4.00	2.00	8.00

SOT-323 Tape Leader and Trailer



SOT-323 Reel



Dimensions are in millimeter								
Reel Option	D	D1	D2	G	H	I	W1	W2
7"Dia	Ø178.00	54.40	13.00	R78.00	R25.60	R6.50	9.50	12.30

REEL	Reel Size	Box	Box Size(mm)	Carton	Carton Size(mm)	G.W.(kg)
3000 pcs	7 inch	30,000 pcs	203×203×195	120,000 pcs	438×438×220	