



21	3.5mm Housing	Thermoplastics	Black UL 94—V0
20	4.4mm Separator		
19	4.4mm Housing		
18	4.4mm Sleeve	Copper Alloy	G/F Plated Overall.
17	3.5mm Sleeve		
16	3.5mm Switch		
15	3.5mm Left		
14	3.5mm Right		
13	3.5mm GND	Stainless Steel	Au3u''On Contact Area G/F on Solder Tails Ni Plated Overall.
12	4.4mm Switch—B		
11	4.4mm Switch—A		
5&10	4.4mm Left+		
4&9	4.4mm Left—		
3&8	4.4mm Right+	Copper Alloy	
2&7	4.4mm Right—		
1&6	4.4mm GND		
Item	Name	Material	Description



DRAWING:	林生财	DATE:	2025.02.15	SCALE	1:1
CHECK:	李宏鑫	DATE:	2025.02.15	MATERIAL	*
APPROVAL:	杨进宝	DATE:	2025.02.15	DWG. NO.	
DRAWING NO.	ZB44003-16DBAP-A			SHEET	1/1

PART NAME	Slime #4.4mm 5Pole & #3.5mm Audio Jack Combo Conn.(Leg0.8mm)	TOLERANCE UNLESS	0.0±0.30	0.°±2°	UNIT: mm
PART NO.	ZB44003-16DBAP-A	OTHERWISE SPECIFIED:	0.00±0.20 0.000±0.10	0.0°±1° 0.00°±0.5°	