



连云港美华电子科技有限公司  
Lianyungang MEIHUA Electronics Technology Co., Ltd

# 产品规格书

## DATA SHEET

Part No: MHP3838IR138CT  
REV.6

本产品符合 ROHS 指令有关限制有害物质的环保要求.

| 日期<br>DATE               | 拟制<br>PREPARED | 审核<br>VERIFIED | 批准<br>APPROVED |
|--------------------------|----------------|----------------|----------------|
| 2025-05-20               | Liu            |                | Leo            |
| 客户签回 CUSTOMER'S APPROVAL |                |                |                |
|                          |                |                |                |

电 话 Tel: 0518-83286000

传 真 Fax: 0518-83696699

邮件 E-mail: sales@lygmh.com.cn

网 址 Web: <http://www.lygmh.com.cn>

地址 ADD: 中国·江苏省连云港市灌南经济开发区北环路

North Around Road, Guannan EDA, Lianyungang City, Jiangsu Province China.




连云港美华电子科技有限公司



P/N: MHP3838IR138CT

LED PLCC


## 产品外观尺寸 PACKAGE DIMENSIONS




Side View



Polarity



Recommended Solder Pad



### 注意 Notes :

1. 所有尺寸均为 mm(英寸)。All dimensions are in millimeters. (inches)
2. 如无特殊说明, 公差为 0.10mm(0.004")。Tolerance is  $\pm 0.10\text{mm}$  (0.004") unless otherwise specified.




连云港美华电子科技有限公司

P/N: MHP3838IR138CT

LED PLCC

## 产品特性 Features

- 高可靠性和高稳定性  
High intensity and reliability
- 高品质、和低功耗、低成本  
High quality, Low power requirement and low cost
- IC 易兼容、易装配  
IC compatible, Easy assembly
- 符合 RoHS 指令要求  
ROHS COMPLIANT
- 无铅产品  
Pb FREE PRODUCTS
- 窄视角---90  
Narrow viewing angle --- 90
- 与红外、气相回流焊工艺兼容  
Compatible with infrared and vapor phase reflow solder process



## 产品特征 Descriptions

- 3838 规格封装  
3838 package
- 顶部发光  
Top view LED
- 胶体颜色：透明  
Lens Color: Water Clear
- 发光颜色 Emitted color:
  1. 红外线: Infrared
  - 2.
  - 3.
  - 4.
  - 5.
- 晶片材质 Chips materials:
  1. 硅基片 Si-substrate
  - 2.
  - 3.
  - 4.



连云港美华电子科技有限公司

P/N: MHP3838IR138CT

LED PLCC

### 极限参数 Absolute Maximum Ratings(Ta=25℃)

| 参数<br>Parameter                                                                    | 符号<br>Symbol     | 极限值<br>Rating | 单位<br>Unit |
|------------------------------------------------------------------------------------|------------------|---------------|------------|
| 单字节功耗<br>Power Dissipation Per Segment                                             | Pd               | 2.3           | W          |
| 最大峰值电流<br>Peak Forward Current Per Segment<br>(1/10 duty cycle, 0.1ms pulse width) | IPF              | 1200          | mA         |
| 最大使用电流<br>Continuous Forward Current Per segment                                   | IAF              | 1000          | mA         |
| 反向电压<br>Reverse Voltage                                                            | VR               | 5             | V          |
| 静电承受能力<br>Electrostatic Discharge Threshold (HBM)                                  | ESD              | 2000          | V          |
| 热阻<br>Thermal Resistance(junction to case)                                         | Rs               | 18            | ℃/W        |
| 工作温度<br>Operating Temperature Range                                                | T <sub>OPR</sub> | -40℃ to +85℃  |            |
| 储藏温度<br>Storage Temperature Range                                                  | T <sub>STG</sub> | -40℃ to +100℃ |            |
| 回流焊温度<br>Soldering Temperature                                                     | T <sub>SOL</sub> | 240℃          |            |

#### 注意 Notes:

- 1.脉冲宽度≤0.1ms。Pulse Width≤0.1ms
- 2.占空比≤1/10。Duty≤1/10



连云港美华电子科技有限公司

P/N: MHP3838IR138CT

LED PLCC

### 光电特性 Optical-Electrical Characteristic(Ta=25℃)

| 符号<br>Symbol          | 参数<br>Parameter                            | 测试条件<br>Test Condition | 最小<br>Min | 标准<br>Typ   | 最大<br>Max | 单位<br>Unit |
|-----------------------|--------------------------------------------|------------------------|-----------|-------------|-----------|------------|
| I <sub>e</sub>        | 辐射强度<br>Radiant Intensity                  | IF=1A tP=10ms          | 285       | 350         | 450       | mW/sr      |
| V <sub>F</sub>        | 正向压降<br>Forward Voltage                    | IF=1A tP=10ms          | 1.7       | 1.95        | 2.3       | V          |
| I <sub>R</sub>        | 反向漏电流<br>Reverse Current                   | VR=10V                 | -         | -           | 5         | uA         |
| λ <sub>p</sub>        | 峰值波长<br>Peak Wavelength                    | IF=1A tP=10ms          | -         | 855         | -         | nm         |
| λ <sub>centroid</sub> | 重心波长<br>Centroid Wavelength                | IF=1A tP=10ms          | -         | 850         | -         | nm         |
| Δλ                    | 光谱半宽<br>Spectral Half-width                | IF=1A tP=10ms          | -         | 25          | -         | nm         |
| 2θ <sub>1/2</sub>     | 发光角度<br>Viewing Angle                      | IF=1A, tP=10ms         |           | 90          |           | deg        |
| L x W (Typ.)          | 芯片有效面积尺寸<br>Dimensions of active chip area | -                      | -         | 889<br>x889 | -         | um x<br>um |

#### 注意 Notes :

1. 发光强度公差为±10%。 Tolerance of Luminous Intensity ±10%.
2. 正向压降公差为±0.1V。 Tolerance of Forward Voltage: ±0.1V.
3. 波长公差: ±1nm。 Tolerance of Dominant Wavelength: ±1nm
4. 使用产品时需做防静电措施。 The products are sensitive to static electricity and must be carefully taken when handling products.



连云港美华电子科技有限公司

P/N: MHP3838IR138CT

LED PLCC

### 辐射强度等级 Bin Range of Radiant Intensity(Ie)

| 等级<br>Bin Code | 最小值<br>Min | 最大值<br>Max | 单位<br>Unit | 条件<br>Condition |
|----------------|------------|------------|------------|-----------------|
| A26            | 285        | 360        | mW/sr      | IF=1A, tP=10ms  |
| A27            | 360        | 450        | mW/sr      | IF=1A, tP=10ms  |

#### 注意 Note:

辐射强度公差范围:  $\pm 10\%$ 。 Tolerance of Radiant Intensity:  $\pm 10\%$ .

### 电压等级 Bin Range of Forward Voltage(VF)

| 等级<br>Bin Code | 最小值<br>Min | 最大值<br>Max | 单位<br>Unit | 条件<br>Condition |
|----------------|------------|------------|------------|-----------------|
| C1             | 1.7        | 1.9        | V          | IF=1A, tP=10ms  |
| C2             | 1.9        | 2.1        | V          | IF=1A, tP=10ms  |
| C3             | 2.1        | 2.3        | V          | IF=1A, tP=10ms  |









#### 注意 Note:

电压公差范围:  $\pm 0.1V$ 。 Tolerance of Forward Voltage:  $\pm 0.1V$ .



典型电光特性曲线（芯片代码：IR）

Typical Electro-Optical Characteristics Curve(Chip code: IR)



注意 Notes :

1. 发光强度取平均值。Luminous Intensity is an average value.
2. 发光强度公差：±10%。Tolerance of Luminous Intensity: ±10%.
3. 正向电压公差：±0.1V。Tolerance of Forward Voltage: ±0.1V.



连云港美华电子科技有限公司

P/N: MHP3838IR138CT

LED PLCC

## 标签 Label

连云港美华电子科技有限公司

P/N: MHP3838IR138CT

L/N: xxxxxxxxxxxx

QTY: xxxx pcs

DATA: xxxxx

|         |                                        |
|---------|----------------------------------------|
| P/N:    | 型号 Part Number                         |
| LOT No: | 生产单号 Lot Number                        |
| QTY:    | 数量 Packing Quantity                    |
| DATA:   | 生产日期 Data Code                         |
| IV:     | 亮度 Luminous Intensity ( 参考 Reference ) |
| VF:     | 电压 Forward Voltage ( 参考 Reference )    |



连云港美华电子科技有限公司


P/N: MHP3838IR138CT

LED PLCC

## 焊接条件 Soldering Condition

| 方法<br>Method            | 焊接条件<br>Soldering Conditions | 备注<br>Remark                                       |
|-------------------------|------------------------------|----------------------------------------------------|
| 回流焊<br>Reflow Soldering | 240°C for 10 sec.            | -                                                  |
| 烙铁焊<br>Soldering Iron   | 315°C for 3 sec.             | 使用 25W 以下功率的电烙铁<br>the soldering iron capacity 25W |

## 无铅制程炉温曲线 Pb-Free Solder Temperature Profile



### 注意 Notes:

- 过回流焊次数不可超过 2 次; Reflow soldering should not be done more than two times.
- 焊接加热过程中不要挤压 LED; When soldering, do not put stress on the LEDs during heating.
- 焊接完成后, 不要用力弯曲线路板; After soldering, do not warp the circuit board.
- 客户在设计使用时需串联保护电阻, 避免电压波动烧毁发光二极管。Customer must apply resistors for protection; otherwise, slight voltage shift will cause big current change (Burn out will happen).



连云港美华电子科技有限公司

P/N: MHP3838IR138CT

LED PLCC

## 可靠性试验项目和条件 Reliability Test Items and Conditions

产品的可靠性应满足以下项目 The reliability of products shall be satisfied with items listed below.

置信水平 Confidence level: 90%

批量容许次品率 LTPD: 10%

| 编号<br>No. | 项目<br>Items                                         | 测试条件<br>Test Condition                         | 测试时间<br>Test Hours/Cycles | 样品数量<br>Sample Size | 判定标准<br>Ac/Re |
|-----------|-----------------------------------------------------|------------------------------------------------|---------------------------|---------------------|---------------|
| 1         | 回流焊<br>Reflow Soldering                             | 240+/-5°C/10sec.                               | 3 Cycles                  | 22pcs               | 0/1           |
| 2         | 热冲击<br>Thermal Shock                                | H : +150°C 5min<br>J 10 sec<br>L : -65°C 5min  | 300 Cycles                | 22pcs               | 0/1           |
| 3         | 温度循环<br>Temperature Cycle                           | H : +100°C 15min<br>J 5 min<br>L : -40°C 15min | 300 Cycles                | 22pcs               | 0/1           |
| 4         | 高温高湿测试 High<br>Temperature/Humidity<br>Reverse Bias | Ta=85°C,85%RH                                  | 1000 Hrs.                 | 22pcs               | 0/1           |
| 5         | 低温贮藏<br>Low Temperature Storage                     | Ta= - 40°C                                     | 1000 Hrs.                 | 22pcs               | 0/1           |
| 6         | 高温贮藏<br>High Temperature Storage                    | Ta=100°C                                       | 1000 Hrs.                 | 22pcs               | 0/1           |
| 7         | 寿命测试<br>DC Operation Life                           | Ta=25°C                                        | 1000 Hrs.                 | 22pcs               | 0/1           |
| 8         | 红墨水<br>Red ink                                      | Red ink: alcohol=1:1 soak                      | 24H                       | 50pcs               | 0/1           |




连云港美华电子科技有限公司

P/N: MHP3838IR138CT


LED PLCC

## 包装 Packing


### 1. 卷轴尺寸 Reel Dimensions



### Moisture Resistant Packaging (防潮包装)



### 2. 载带尺寸 Carrier Tape Dimensions



### 注意 Notes:

1. 量测公差为 $\pm 0.1\text{mm}$ ，单位是毫米。Tolerances unless mentioned  $\pm 0.1\text{mm}$ , Unit = mm.
2. 最小包装数量为每卷 1000 个。Minimum packing amount is 1000 pcs per reel.



连云港美华电子科技有限公司

P/N: MHP3838IR138CT

LED PLCC

## 储藏 Storage

1. 发光二极管在出厂后可在温度 30 度以下,湿度 60% 以下的环境内保存 1 年。The LED should be stored at 30°C or less and 60% RH or less after being shipped from MH and the storage life limits are 1 year.

2. 在产品准备使用前请不要打开防潮袋。Do not open moisture proof bag before the products are ready to use.

3. 贮存环境:产品需贮存在温度 10°C~30°C,湿度 $\leq$  60%RH 环境中, 要求所有产品上线前均需按照要求进行烘烤除湿, 烘烤条件如下: Storage environment: All the products should be stored in the environment of temperature 10°C~30°C and humidity $\leq$ 60% RH before foiled bags open and need to be baked before SMT, Baking conditions are as follows:

| 项目        | 烘烤温度         | 烘烤时间 |
|-----------|--------------|------|
| 小于等于 2 个月 | 70 $\pm$ 5°C | 12H  |
| 2 至 6 个月  | 70 $\pm$ 5°C | 18H  |
| 大于 6 个月   | 70 $\pm$ 5°C | 24H  |

4. 如果吸湿性材料(硅胶)已用完或发光二极管已超过存储时间, 应使用以下条件进行烘烤处理, 处理: 60 $\pm$ 5°C 烘烤 5 小时。If the moisture absorbent material (silica gel) has faded away or the LEDs have exceeded the storage time, baking treatment should be performed using the following conditions. Baking treatment: 60 $\pm$ 5°C for 5 hours.

3. 请避免保存在温度变化明显, 尤其是高湿度的地方 Please avoid rapid transitions in ambient temperature, especially, in high humidity environments where condensation can occur.

## 使用注意事项 Application Restrictions

1. 生产环境: 建议在 20°C~30°C & 30%~60%RH 下作业。

Production environment: it is recommended to operate at 20 DEG ~30 DEG & 30%~60%RH

2. 维修温度建议控制在 280°C 以下, 持续加热时间不超过 30S。

The service temperature shall be controlled below 280 degrees, and the continuous heating time shall not exceed 30S.

3. 维修时避免尖锐物体直接戳到胶体, 取料时建议夹取板材两端。

When repairing, the sharp object should be directly punched into the colloid, and when picking



连云港美华电子科技有限公司

P/N: MHP3838IR138CT

LED PLCC

the material, it is recommended to clamp both ends of the PCB.

#### 其他注意事项 Others

1. 本文档中所描述的规范，上述规格可变更不通知。美华将对上述规格的材料更改的保留权。  
Specification described in this document, Above specification may be changed without notice.  
MEIHUA will reserve authority on material change for above specification.

2. 使用本产品时请遵守规格书绝对最大额定值。否则美华将不承担因此引起的损失。  
When using this product, please observe the absolute maximum ratings and the instructions for using outlined in these specification sheets. MEIHUA assumes no responsibility for any damage resulting from use of the product which does not comply with the absolute maximum ratings and the instructions included in these specification sheets.

3. 这些数据包括美华版权保护的材料。未经授权请不要复制。  
These specification sheets include materials protected under copyright of MEIHUA Corporation. Please don't reproduce or cause anyone to reproduce them without MEIHUA's consent.

4. 静电放电（静电放电）ESD (Electrostatic Discharge)  
产品敏感的静电或冲击电压。当使用产品时静电放电会损坏模具及其可靠性。对静电放电的措施  
强烈推荐消除电荷接地的手环，防静电鞋，衣服和地板等 The products are sensitive to static  
electricity or surge voltage. ESD can damage a die and its reliability. When handling the  
products, the following measures against electrostatic discharge are strongly recommended:  
Eliminating the charge Grounded wrist strap, ESD footwear, clothes, and floors

5. 发光二极管正向电流方向使用，驱动电路的设计必须使 LED 在关闭的状态下不经受正向或逆向电压，如果反向电压不断应用于发光二极管，它可以导致 LED 损坏。  
The LEDs should be operated with forward bias. The driving circuit must be designed so that the LEDs are not subjected to forward or reverse voltage while it is off. If reverse voltage is continuously applied to the LEDs, it may cause migration resulting in LED damage.