

# SPTECH Silicon NPN Power Transistors

**BD751/751A**

## DESCRIPTION

- Collector-Emitter Sustaining Voltage-  
:  $V_{CEO(SUS)} = 90V(\text{Min})$ - BD751  
=  $120V(\text{Min})$ - BD751A
- High Power Dissipation
- Complement to Type BD750/750A

## APPLICATIONS



- Designed for high voltage and high power amplifier applications.

## ABSOLUTE MAXIMUM RATINGS( $T_a=25^\circ\text{C}$ )

| SYMBOL         | PARAMETER                                           |        | VALUE   | UNIT             |
|----------------|-----------------------------------------------------|--------|---------|------------------|
| $V_{CEV}$      | Collector-Emitter Voltage                           | BD751  | 100     | V                |
|                |                                                     | BD751A | 130     |                  |
| $V_{CEO(SUS)}$ | Collector-Emitter Voltage                           | BD751  | 90      | V                |
|                |                                                     | BD751A | 120     |                  |
| $V_{EBO}$      | Emitter-Base Voltage                                |        | 7       | V                |
| $I_C$          | Collector Current-Continuous                        |        | 20      | A                |
| $I_B$          | Base Current-Continuous                             |        | 5       | A                |
| $P_C$          | Collector Power Dissipation@ $T_c=25^\circ\text{C}$ |        | 200     | W                |
| $T_J$          | Junction Temperature                                |        | 200     | $^\circ\text{C}$ |
| $T_{stg}$      | Storage Temperature                                 |        | -65~200 | $^\circ\text{C}$ |

## THERMAL CHARACTERISTICS

| SYMBOL        | PARAMETER                            | MAX   | UNIT               |
|---------------|--------------------------------------|-------|--------------------|
| $R_{th\ j-c}$ | Thermal Resistance, Junction to Case | 0.875 | $^\circ\text{C/W}$ |



## SPTECH Silicon NPN Power Transistors

## BD751/751A

## ELECTRICAL CHARACTERISTICS

 $T_C=25^{\circ}\text{C}$  unless otherwise specified

| SYMBOL         | PARAMETER                            |        | CONDITIONS                                                       | MIN | TYP. | MAX | UNIT |
|----------------|--------------------------------------|--------|------------------------------------------------------------------|-----|------|-----|------|
| $V_{CEQ(SUS)}$ | Collector-Emitter Sustaining Voltage | BD751  | $I_C=30\text{mA}$ ; $I_B=0$                                      | 90  |      |     | V    |
|                |                                      | BD751A |                                                                  | 120 |      |     |      |
| $V_{CE(sat)}$  | Collector-Emitter Saturation Voltage | BD751  | $I_C=7.5\text{A}$ ; $I_B=0.75\text{A}$                           |     |      | 1.5 | V    |
|                |                                      | BD751A | $I_C=5\text{A}$ ; $I_B=0.5\text{A}$                              |     |      | 1.0 |      |
| $V_{BE(sat)}$  | Base-Emitter Saturation Voltage      | BD751  | $I_C=7.5\text{A}$ ; $I_B=0.75\text{A}$                           |     |      | 1.8 | V    |
|                |                                      | BD751A | $I_C=5\text{A}$ ; $I_B=0.5\text{A}$                              |     |      | 1.8 |      |
| $I_{CEV}$      | Collector Cutoff Current             | BD751  | $V_{CEV}=100\text{V}$ ; $V_{BE(off)}=1.5\text{V}$                |     |      | 0.5 | mA   |
|                |                                      | BD751A | $V_{CEV}=130\text{V}$ ; $V_{BE(off)}=1.5\text{V}$                |     |      | 0.5 |      |
| $I_{EBO}$      | Emitter Cutoff Current               |        | $V_{EB}=7\text{V}$ ; $I_C=0$                                     |     |      | 1.0 | mA   |
| $h_{FE}$       | DC Current Gain                      | BD751  | $I_C=7.5\text{A}$ ; $V_{CE}=2\text{V}$                           | 15  |      | 60  |      |
|                |                                      | BD751A | $I_C=5\text{A}$ ; $V_{CE}=2\text{V}$                             | 25  |      | 100 |      |
| $f_T$          | Current-Gain—Bandwidth Product       |        | $I_C=0.5\text{A}$ ; $V_{CE}=10\text{V}$ ; $f_{test}=1\text{MHz}$ | 4   |      |     | MHz  |