

SPTECH Silicon NPN Power Transistors

TIP47

DESCRIPTION

- DC Current Gain $-h_{FE} = 30 \sim 150 @ I_C = 0.3A$
- Collector-Emitter Sustaining Voltage-
: $V_{CEO(SUS)} = 250V(\text{Min})$

APPLICATIONS



- Designed for line operated audio output amplifier, switchmode power supply drivers and other switching applications

ABSOLUTE MAXIMUM RATINGS($T_a = 25^\circ\text{C}$)

SYMBOL	PARAMETER	VALUE	UNIT
V_{CBO}	Collector-Base Voltage	350	V
V_{CEO}	Collector-Emitter Voltage	250	V
V_{EBO}	Emitter-Base Voltage	5	V
I_C	Collector Current-Continuous	1.0	A
I_{CM}	Collector Current-Peak	2.0	A
I_B	Base Current	0.6	A
P_D	Collector Power Dissipation $T_C = 25^\circ\text{C}$	40	W
	Collector Power Dissipation $T_a = 25^\circ\text{C}$	2	
T_j	Junction Temperature	150	$^\circ\text{C}$
T_{stg}	Storage Temperature Range	-65~150	$^\circ\text{C}$

THERMAL CHARACTERISTICS

SYMBOL	PARAMETER	MAX	UNIT
$R_{th\ j-c}$	Thermal Resistance, Junction to Case	3.125	$^\circ\text{C/W}$
$R_{th\ j-a}$	Thermal Resistance, Junction to Ambient	62.5	$^\circ\text{C/W}$



SPTECH Silicon NPN Power Transistors

TIP47

ELECTRICAL CHARACTERISTICS

 $T_C=25^{\circ}\text{C}$ unless otherwise specified

SYMBOL	PARAMETER	CONDITIONS	MIN	MAX	UNIT
$V_{CEQ(SUS)}$	Collector-Emitter Sustaining Voltage	$I_C=30\text{mA}; I_B=0$	250		V
$V_{CE(sat)}$	Collector-Emitter Saturation Voltage	$I_C=1\text{A}; I_B=0.2\text{A}$		1.0	V
$V_{BE(on)}$	Base-Emitter On Voltage	$I_C=1\text{A}; V_{CE}=10\text{V}$		1.5	V
I_{CBO}	Collector Cutoff Current	$V_{CB}=350\text{V}; I_E=0$		1.0	mA
I_{CEO}	Collector Cutoff Current	$V_{CE}=150\text{V}; I_B=0$		1.0	mA
I_{EBO}	Emitter Cutoff Current	$V_{EB}=5\text{V}; I_C=0$		1.0	mA
h_{FE-1}	DC Current Gain	$I_C=0.3\text{A}; V_{CE}=10\text{V}$	30	150	
h_{FE-2}	DC Current Gain	$I_C=1\text{A}; V_{CE}=10\text{V}$	10		
f_T	Current-Gain—Bandwidth Product	$I_C=0.1\text{A}; V_{CE}=10\text{V}$	10		MHz