









RoHS
Compliant


ZONE	ECN.NO.	DESCRIPTION	DRAWING	DATE
A		INITIAL	姓名	2020.02.18




1. CONTACT CURRENT RATING: 1A.
2. CONTACT RESISTANCE: 100 mΩ MAX.;
3. INSULATION RESISTANCE: 100MΩ MIN.;
4. DIELECTRIC WITHSTANDING: 500V AC MIN.;
5. DURABILITY: 5,000 CYCLES MIN.;
6. CONNECTOR MATING FORCES: 30N MAX.;
7. CONNECTOR UNMATING FORCES: 3N MIN.;
8. TERPROOF LEVEL: IP67;




P.C.B LAYOUT T=1.00mm
TOP VIEW




(ø3.50mm 4 POLE PLUG)




面板开孔建议尺寸(ø6.35)



WATERPROOF RING



(ø1.50mm 4 POLE PLUG SCHEMATIC)



SCHEMATIC

Not to install the waterproof ring shipment

9	COVER	1	HIGH TEMPERATURE PLASTIC MATERIALE; COLOR BLACK	
8	WATERPROOF RING	1	SILICA GEL	
7	HOUSING	1	HIGH TEMPERATURE PLASTIC MATERIALE; COLOR BLACK	
6	TERMINAL 6#	1	COPPER ALLOY; NICKEL UNDER PLATING OVERALL;GOLD FLASH PLATING ON SOLDER AREA ; GOLD FLASH PLATING ON CONTACT AREA	T=0.20mm
5	TERMINAL 5#	1	COPPER ALLOY; NICKEL UNDER PLATING OVERALL;GOLD FLASH PLATING ON SOLDER AREA ; GOLD FLASH PLATING ON CONTACT AREA	T=0.20mm
4	TERMINAL 4#	1	COPPER ALLOY; NICKEL UNDER PLATING OVERALL;GOLD FLASH PLATING ON SOLDER AREA ; GOLD FLASH PLATING ON CONTACT AREA	T=0.20mm
3	TERMINAL 3#	1	COPPER ALLOY; NICKEL UNDER PLATING OVERALL;GOLD FLASH PLATING ON SOLDER AREA ; GOLD FLASH PLATING ON CONTACT AREA	T=0.20mm
2	TERMINAL 2#	1	COPPER ALLOY; NICKEL UNDER PLATING OVERALL;GOLD FLASH PLATING ON SOLDER AREA ; GOLD FLASH PLATING ON CONTACT AREA	T=0.20mm
1	TERMINAL 1#	1	STAINLESS STEEL; NICKEL UNDER PLATING OVERALL;GOLD FLASH PLATING ON SOLDER AREA ; GOLD FLASH PLATING ON CONTACT AREA	T=0.20mm
ITEM	NAME	QTY	DESCRIPTION	NOTE

LZG®

LZG INDUSTRIAL CO. LTD

DRAWING:	姓名	DATE:	2020.02.18	SCALE	1:1
CHECK:	姓名	DATE:	2020.02.18	MATERIAL	*
APPROVAL:	姓名	DATE:	2020.02.18	DWG. NO.	
DRAWING NO.	ZB23003-06DBAP-A			SHEET	1/1

PART NAME	WATERPROOF ø3.5 PHONE JACK	TOLERANCE UNLESS OTHERWISE SPECIFIED:	0.0±0.3 0.00±0.2 0.000±0.1	0.1±2° 0.0°±1° 0.00°±0.5°	UNIT: mm	
PART NO.	ZB23003-06DBAP-A					