









RoHS
Compliant



RECOMMEND PCB LAYOUT
TOL=±0.05

A1	GND	B12	GND	7	RING	SILICON	-----	1 PCS
A2	SSTXP1	B11	SSRXP1	6	MID-PLANT	STAINLESS STEEL	-----	1 PCS
A3	SSTXN1	B10	SSRXN1	5	GND-PLANT	STAINLESS STEEL	NI/SN PLATING	1 PCS
A4	VBUS	B9	VBUS	4	SHELL	STAINLESS STEEL	-----	1 PCS
A5	CC1	B8	SBU2	3	INNER SHELL	STAINLESS STEEL	NI PLATING	1 PCS
A6	DP1	B7	DN2	2	CONTACT	COPPER ALLOY	Au/Ni PLATING	2 SET
A7	DN1	B6	DP2	1	HOUSING	HIGH TEMPERATURE PLASTIC	COLOR BLACK	1 PCS
A8	SBU1	B5	CC2					
A9	VBUS	B4	VBUS					
A10	SSRXN2	B3	SSTXN2					
A11	SSRXP2	B2	SSTXP2					
A12	GND	B1	GND					
PIN	SIGNAL NAME	PIN	SIGNAL NAME	NO.	DESCRIPTION	MATERIAL	REMARKS	QTY

LZG

LZG INDUSTRIAL CO. LTD

DRAWING:	林生財	DATE:	2020.02.18	SCALE	1:1
CHECK:	李宏鑫	DATE:	2020.02.18	MATERIAL	*
APPROVAL:	楊進宝	DATE:	2020.02.18	DWG. NO.	
DRAWING NO.	ZB48031-24FBAP-A			SHEET	1/1

PART NAME	WATERPROFF TYPE C 24PIN	TOLERANCE UNLESS	0.0±0.3	0.°±2°	UNIT:	
PART NO.	ZB48031-24FBAP-A	OTHERWISE SPECIFIED:	0.00±0.2	0.0°±1°	mm	
			0.000±0.05	0.00°±0.5°		