






满足时序要求

- 1.Current Rating: 12V&1A max.
- 2.Contact Resistance: 50mOhms Max.(initial)
Switch Resistance: 100mOhms Max.(initial)
- 3.Insulation Resistance: 100M Ohms Min./500V DC
- 4.Dielectric Withstanding Voltage: 500V AC/1Minute
- 5.4mm Mating Force: 50N Max, Withdrawal Force: 5N Min.
- 6.Durability: 5,000 Cycles
- 7.Operating Temperature: -25°C to +85°C
- 8.Mate Audio Plug with "JEITA RC-8141C" Standard(Length19.5mm)

RECOMMEND PCB LAYOUT
TOLERANCE: ± 0.05



15	4.4mm Separator	Thermoplastics	Black UL 94-V0
14	4.4mm Housing		
13	4.4mm Sleeve	Copper Alloy	G/F On Contact Area &Solder Tails
12	4.4mm Switch-B	Stainless Steel	
11	4.4mm Switch-A	Copper Alloy	Au3u''On Contact Area G/F on Solder Tails Ni Plated Overall.
5&10	4.4mm Left+		
4&9	4.4mm Left-		
3&8	4.4mm Right+		
2&7	4.4mm Right-		
1&6	4.4mm GND		
Item	Name	Material	Description



LZG INDUSTRIAL CO. LTD

DRAWING:	林生财	DATE:	2025.02.15	SCALE	1:1
CHECK:	李宏鑫	DATE:	2025.02.15	MATERIAL	*
APPROVAL:	杨进宝	DATE:	2025.02.15	DWG. NO.	
DRAWING NO.	ZB44002-12DBAP-A			SHEET	1/1

TOLERANCE UNLESS	0.0±0.30
OTHERWISE SPECIFIED:	0.00±0.20
	0.000±0.10

F

F

D

C

B

A