




RoHS
Compliant



3D VIEW






ZONE	E C N . N O .	DESCRIPTION	DRAWING	DATE
A		INITIAL	林生财	2020.02.18

NOTES:

SPECIFICATION:

1. CURRENT RATING: 3.0A MAX
2. DIELECTRIC WITHSTAND VOLTAGE: 100VAC
3. TEMPERATURE RANGE: -30 °C ~ 85 °C
4. CONTACT RESISTANCE: 40 MILLIONHM MAX
5. INSULATION RESISTANCE: 100 MEGOHMS MIN.
6. INSERTION FORCE :10N~30N
7. UNMATING FORCE: 8N~30N
8. DURABILITY:1500 CYCLES





RECOMMENDED PCB LAYOUT(TOP VIEW)


THICKNESS T=1.0mm
DEFAULT TOLERANCE+/-0.05

结构设计注意:

1. 成品使用时, 如有洗面奶泡沫、牙膏、洗手液、脏污液体, 请在TYPE-C口外面再设计一层外壳, 保护TYPE-C表面金手指不会被脏污覆盖。



注: 防水圈是圆形圈, 直径为1.0mm的橡胶圈, 防水圈的压力, 由1.0mm的橡胶圈0.4mm~0.5mm, 防水效果良好



组装示意图

PIN ASSIGNMENT

PIN NO.	1	2	3	4
SIGNAL NAME	VBUS	D-	D+	GND

4	INNER SHELL	SUS 301	WASH	1
3	PLASTIC SHELL	PA10T	COLOR BLACK	1
2	CONTACT	BRASS	Au/Ni Plating T=0.25mm	4
1	HOUSING	PA10T	COLOR BLACK	1
NO.	DESCRIPTION	MATERIAL	REMARKS	QTY

LZG

LZG INDUSTRIAL CO. LTD

DRAWING:	林生财	DATE:	2020.02.18	SCALE	1/1
CHECK:	李宏鑫	DATE:	2020.02.18	MATERIAL	*
APPROVAL:	杨进宝	DATE:	2020.02.18	DWG. NO.	
DRAWING NO.	ZB40004-06DBAP-A			SHEET	1/1

PART NAME	WATERPROFF USB 2.0 A TYPE	TOLERANCE UNLESS	0.0±0.3	0.°±2°	UNIT:	
PART NO.	ZB40004-06DBAP-A	OTHERWISE SPECIFIED:	0.00±0.1	0.0°±1°	mm	
			0.000±0.05	0.00°±0.5°		