

SPTECH Silicon NPN Power Transistor

2SD2155

DESCRIPTION



- High Current Capability
- High Power Dissipation
- High Collector-Emitter Breakdown Voltage-
: $V_{(BR)CEO} = 180V(\text{Min})$
- Complement to Type 2SB1429

APPLICATIONS

- Power amplifier applications
- Recommend for 100W high fidelity audio frequency amplifier output stage applications

ABSOLUTE MAXIMUM RATINGS($T_a=25^\circ\text{C}$)

SYMBOL	PARAMETER	VALUE	UNIT
V_{CBO}	Collector-Base Voltage	180	V
V_{CEO}	Collector-Emitter Voltage	180	V
V_{EBO}	Emitter-Base Voltage	5	V
I_C	Collector Current-Continuous	15	A
I_B	Base Current-Continuous	1.5	A
P_C	Collector Power Dissipation @ $T_C=25^\circ\text{C}$	150	W
T_J	Junction Temperature	150	$^\circ\text{C}$
T_{stg}	Storage Temperature Range	-55~150	$^\circ\text{C}$



SPTECH Silicon NPN Power Transistor

2SD2155

ELECTRICAL CHARACTERISTICS

 $T_C=25^{\circ}\text{C}$ unless otherwise specified

SYMBOL	PARAMETER	CONDITIONS	MIN	TYP.	MAX	UNIT
$V_{(BR)CEO}$	Collector-Emitter Breakdown Voltage	$I_C = 30\text{mA}$; $I_B = 0$	180			V
$V_{CE(sat)}$	Collector-Emitter Saturation Voltage	$I_C = 8.0\text{A}$; $I_B = 0.8\text{A}$			2.0	V
$V_{BE(on)}$	Base-Emitter On Voltage	$I_C = 6\text{A}$; $V_{CE} = 5\text{V}$			1.5	V
I_{CBO}	Collector Cutoff Current	$V_{CB} = 180\text{V}$; $I_E = 0$			5	μA
I_{EBO}	Emitter Cutoff Current	$V_{EB} = 5\text{V}$; $I_C = 0$			5	μA
h_{FE-1}	DC Current Gain	$I_C = 1\text{A}$; $V_{CE} = 5\text{V}$	55		160	
h_{FE-2}	DC Current Gain	$I_C = 6\text{A}$; $V_{CE} = 5\text{V}$	30			
C_{OB}	Output Capacitance	$I_E = 0$; $V_{CB} = 10\text{V}$; $f_{test} = 1.0\text{MHz}$		160		pF
f_T	Current-Gain—Bandwidth Product	$I_C = 1\text{A}$; $V_{CE} = 5\text{V}$		10		MHz

◆ h_{FE-1} Classifications

R	O
55-110	80-160