

Harvatek 6.4*4.9*6.5mm Reflective Type Sensor**HV-22S064065/242B/T210-F35**

Official Product	HV-22S064065/242B/T210-F35	Customer Part No.		Data Sheet No.
	*****	*****		HV-22S064065/242B/T210-F35
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Nov.17 2022	Version of 1.2	Page 1/14

DISCLAIMER

HARVATEK reserves the right to make changes without further notice to any products herein to improve reliability, function or design. HARVATEK does not assume any liability arising out of the application or use of any product or circuit described herein; neither does it convey any license under its patent rights, nor the rights of others.

LIFE SUPPORT POLICY

HARVATEK's products are not authorized for use as critical components in life support devices or systems without the express written approval of the President of HARVATEK or HARVATEK INTERNATIONAL. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
2. A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

Official Product	HV-22S064065/242B/T210-F35	Customer Part No.		Data Sheet No.
	*****	*****		HV-22S064065/242B/T210-F35
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Nov.17 2022	Version of 1.2	Page 2/14

Compliance and Certification

ISO9002, QS9000 and ISO14001 Certified

RoHS Compliant



Orderable Information

H V - 2 2 S 0 6 4 0 6 5 / 2 4 2 B / T 2 1 0 - F 3 5


Series Name	Color Code	Remark
HV : HARVATEK	22S: HARVATEK Part No. 064065 :6.4*4.9*6.5mm Reflective Type Sensor. With AlGaAs Infrared emitter & Silicon Photo transistor. 242 : Lamp Model. B : PT Lens Color is Black T210:HARVATEK Part No. F35:HARVATEK Part No.	

Features:

- Low power consumption.
- High analytic.
- Fast response.
- Good lock and easy to assembly.

Official Product	HV-22S064065/242B/T210-F35	Customer Part No.	Data Sheet No.
	*****	*****	HV-22S064065/242B/T210-F35
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Nov.17 2022	Version of 1.2
			Page 3/14

Package Dimensions:



Notes:

- 1.All dimensions are millimeters.
- 2.Tolerance is +/-0.25mm unless otherwise noted.
- 3.Specifications are subject to change without notice.

Official Product	HV-22S064065/242B/T210-F35	Customer Part No.	Data Sheet No.
	*****	*****	HV-22S064065/242B/T210-F35
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Nov.17 2022	Version of 1.2
			Page 4/14

Absolute Maximum Ratings at Ta=25°C

Parameter		Symbol	Rating	Unit
Emitter	Forward Current	I _F	50	mA
	Power Dissipation	P _d	75	mW
	Reverse Voltage	V _R	5	V
	Peak Forward Current *1	I _{FP}	1	A
Receiver	Collector Current	I _c	20	mA
	Power Dissipation	P _d	75	mW
	Collector-Emitter Voltage	V _{ceo}	30	V
	Emitter-Collector Voltage	V _{eco}	5	V
Operating Temperature		Topr	-40to+85	°C
Storage Temperature		Tstg	-40to+100	°C
Soldering Temperature *2		Tsol	260±5	°C

*1: Pulse Width ≤ 100μs and Duty ≤ 1% *2: Soldering time ≤ 5 seconds.

Official Product	HV-22S064065/242B/T210-F35	Customer Part No.		Data Sheet No.
	*****	*****		HV-22S064065/242B/T210-F35
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Nov.17 2022	Version of 1.2	Page 5/14

Electrical and Optical Characteristic

Parameter		Symbol	Condition	Min.	Typ.	Max.	Unit
Emitter	Forward Voltage	V_F	$I_F=20\text{ mA}$	/	1.2	1.5	V
	Reverse Current	I_R	$V_R=5\text{ V}$	/	/	10	μA
	Peak Wavelength	λ_p	$I_F=20\text{ mA}$	930	940	/	nm
Receiver	Dark Current	I_d	$V_{ce}=20\text{V}$	/	/	100	nA
	C-E Saturation	$V_{ce(sat)}$	$I_c=0.5\text{mA}$ $I_F=20\text{ mA}$	/	/	0.4	V
Transfer Characteristics	Collect Current	$I_{C(ON)}$	$V_{CE}=2\text{V}$ $I_F=10\text{mA}$	0.4	/	9.98	mA
	Rise time	T_r	$V_{CE}=5\text{V}$ $I_C=1\text{mA}$ $R_L=1\text{K}\Omega$	/	25	/	μsec
	Fall time	T_f		/	25	/	μsec


Official Product	HV-22S064065/242B/T210-F35	Customer Part No.		Data Sheet No.
	*****	*****		HV-22S064065/242B/T210-F35
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Nov.17 2022	Version of 1.2	Page 6/14

Specifications for Bin Grading:

Ic(mA) VCE=2V IF=10mA		
Grade	Min.	Max.
F	0.4	1.35
G	0.7	1.9
H	1.14	2.6
J	1.77	3.61
K	2.67	5.07
L	4.18	7.07
M	5.68	8.48
N	7.18	9.98


Official Product	HV-22S064065/242B/T210-F35	Customer Part No.		Data Sheet No.
	*****	*****		HV-22S064065/242B/T210-F35
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Nov.17 2022	Version of 1.2	Page 7/14

Typical Electro-Optical Characteristics Curves For IR





Official Product	HV-22S064065/242B/T210-F35	Customer Part No.	Data Sheet No.
	*****	*****	HV-22S064065/242B/T210-F35
Specifications are subject to change without notice. Data and drawings herein are copyrighted.	Nov.17 2022	Version of 1.2	Page 8/14

Typical Electro-Optical Characteristics Curves For PT



Official Product	HV-22S064065/242B/T210-F35	Customer Part No.	Data Sheet No.
	*****	*****	HV-22S064065/242B/T210-F35
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Nov.17 2022	Version of 1.2
			Page 9/14




Official Product	HV-22S064065/242B/T210-F35	Customer Part No.	Data Sheet No.
	*****	*****	HV-22S064065/242B/T210-F35
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Nov.17 2022	Version of 1.2
			Page 10/14

Soldering condition

- Careful attention should be paid during soldering. When soldering, leave more than 2mm from solder joint to Led, and soldering beyond the base of the tie bar is recommended.
- Avoiding applying any stress to the lead frame while the LED are at high temperature particularly when soldering.
- Dip and hand soldering should not be done more than one time.
- After soldering the LED, the epoxy bulb should be protected from mechanical shock or vibration until the LED return to room temperature.
- A rapid-rate process is not recommended for cooling the LED down from the peak temperature.
- Although the recommended soldering conditions are specified in the above table, dip or hand soldering at the lowest possible temperature is desirable for the LED.
- Wave soldering parameter must be set and maintain according to recommended temperature and dwell time in the solder wave.

• Recommended soldering conditions

Hand Soldering		Wave Soldering	
Temp. at tip of iron	300°C Max. (30W Max.)	Preheat temp.	160°C Max. (120 sec Max.)
Soldering time	3 sec Max.	Bath temp. & time	260 Max., 5 sec Max
Distance	2mm Min.(From solder joint to Led)	Distance	2mm Min. (From solder joint to Led)



Official Product	HV-22S064065/242B/T210-F35	Customer Part No.	Data Sheet No.
	*****	*****	HV-22S064065/242B/T210-F35
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Nov.17 2022	Version of 1.2
			Page 11/14

Reliability test items and conditions:

The reliability of products shall be satisfied with items listed below.

Confidence level: 97%.

LTPD:3%.

No	Item	Test Conditions	Test Hours/Cycle	Sample Size	Failure Judgment Criteria	Ac/Er
1	Solder Heat	TEMP:260℃±5℃	10 SEC	76 PCS	$IL \leq IL_t * 0.5$ or $V_f \geq U$ or $V_f \leq L$	0/1
2	Temperature Cycle	H:+100℃ 15min ∫ 5min L:-40℃ 15min	300 CYCLES	76 PCS		0/1
3	Thermal Shock	H:+100℃ 5min ∫ 10sec L:-10℃ 5min	300 CYCLES	76 PCS		0/1
4	High Temperature Storage	TEMP:100℃	1000 HRS	76 PCS		0/1
5	Low Temperature Storage	TEMP:-40℃	1000 HRS	76 PCS		0/1
6	DC Operating Life	TEMP:25℃ IF=20mA	1000 HRS	76 PCS		0/1
7	High Temperature / High Humidity	85℃/85%RH	1000 HRS	76 PCS		0/1

Note: IL_t: To test IL value of the chip before the reliability test.


IL: The test value of the chip that has completed the reliability test.






U: Upper Specification Limit.

L: Lower Specification Limit.

Official Product	HV-22S064065/242B/T210-F35	Customer Part No.		Data Sheet No.
	*****	*****		HV-22S064065/242B/T210-F35
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Nov.17 2022	Version of 1.2	Page 12/14

Packing Specification:



 HARVATEK 	
CPN:	
P/N:	RoHs
 HV-22S064065/242B/T210-F35	
QTY:	CAT:
 HUE:	
LOT NO:	REF:
	

Official Product	HV-22S064065/242B/T210-F35	Customer Part No.	Data Sheet No.
	*****	*****	HV-22S064065/242B/T210-F35
Specifications are subject to change without notice. Data and drawings herein are copyrighted.		Nov.17 2022	Version of 1.2
			Page 13/14

Revision History

Revision	Page	Version No.	Revision Date
Initial Release		1.0	10-17-2020
Increase the photoelectric characteristic curve diagram and over the furnace conditions And the amount of packaging	10/11/13	1.1	12-21-2021
Modify parameters	6/7	1.2	11-17-2022

Official Product	HV-22S064065/242B/T210-F35	Customer Part No.	Data Sheet No.
	*****	*****	HV-22S064065/242B/T210-F35
Specifications are subject to change without notice. Data and drawings herein are copyrighted.	Nov.17 2022	Version of 1.2	Page 14/14