



产品承认书

SPECIFICATION FOR APPROVAL

客户名称:

CUSTOMER

我司料号:

OUR PART NO.

XRAL0510-6R8K

我司品名:

OUR PART NAME

Color ring inductance

送样日期:

DATE SAMPLES

数量:

QUANTITY

制造确认 MANUFACTURER APPROVE

拟制 DRAWN	审核 CHECKED	确认 APPROVED
ZhangJiaoru	RaoPin	Zhongcuilan

客户确认 CUSTOMER APPROVE

客户名称 CUSTOMER NAME:

客户料号 CUSTOMER P/N:

规格型号 DESCRIPTION:

XRAL0510 6.8uH $\pm 10\%$ 850mA

检查结果: ☐ 合格 ☐ 不合格

签名及盖章:

INSPECT RESULT ACCEPT REJECT

SIGNATURE AND STAMP

说明 REMARK:

如对本承认书内容有异议请提出或标记发送至我司, 本承认书在未收到异议回复时于本承认书提供一周后生效。

If you have any objection to the contents of this acknowledgement, please put forward or mark it and send it to our company. This acknowledgement will take effect one week after it is provided if you do not receive an objection reply.

东莞市祥如电子有限公司

Dongguan xiangru electronics co., ltd

Tel: 0769-86346548 Fax: 0769-86346358

Email: dgxiangru@126.com



修订记录 Revision record

[illegible]


产品承认书

SPECIFICATION FOR APPROVAL

客户名称 CUSTOMER		日期 DATE	2025-05-06
客户物料编号 CUSTOMER P/N		客户规格型号 DESCRIPTION	XRAL0510 6.8uH ±10% 850mA
我司物料编号 OUR PART NO	XRAL0510-6R8K	我司品名 OUR PART NAME	Color ring inductance

外观尺寸 Appearance of size

单位 Unit: mm



ΦA	5.0 MAX	B	12.0 MAX	C	26 ±2.0	ΦD	0.65 ±0.05
E	63 ±2.0						
标识Identification		依据具体规格 号According to the specific specification number					

原理图Schematic Diagram:



注意事项 Matters needing attention:

1、由于油漆调配比例略有差异，烘烤时间及烘烤温度存有差异，不同批次或同一批次存有色差属正常现象：Due to the slight difference in paint blending ratio, there are differences in baking time and baking temperature, and it is normal for different batches or the same batch to have color difference:

2、不要使产品遭受温度和湿度的快速变化，易造成电感涂层开裂，建议使用温度范：-20~+125℃；Don't subject the product to rapid changes in temperature and humidity, which may easily lead to cracking of the inductor coating. It is recommended to use the temperature norm of -20 ~+125℃;

3、色环电感成品外观检查事项及标准详见以下附件：See the following attachments for the appearance inspection items and standards of finished products of color ring inductors:



产品承认书
SPECIFICATION FOR APPROVAL

客户名称 CUSTOMER				日期 DATE		2025-05-08	
客户物料编号 CUSTOMER P/N				客户规格型号 DESCRIPTION		XRAL0510 6.8uH ±10% 850mA	
我司物料编号 OUR PART NO		XRAL0510-6R8K		我司品名 OUR PART NAME		Color ring inductance	
电性参数Electrical parameters:							
品名规格Commodity specification		XRAL0510-6R8K		磁芯规格Magnetic core specification		DRWW4*7	
漆包线enamelled wire				合数composite number		色环标识Color ring identification 1. 蓝 2. 灰 3. 金 4. 银 1. Blue 2. Gray 3. metals 4. Silver	
类型 Type	电感量 Inductance (uH)	误差 Tolerance	Q值 (min)	直流电阻 RDC (Ω) max	测试频率 Test frequency (MHz)	自谐频率 SRF (MHz) min	额定电流 Rated current IDC (mA) max
XRAL0510-6R8K	6.8	±10%	15	0.45	7.96	45	850
测试仪器Test equipment	HP4285A (HP4286A, HP4287A)			HP4338B		HM9461	HP42841A
环境温度Ambient temperature		18~25℃					
环境湿度Ambient humidity		45%~75%					
物料清单 BOM							
物料 MATERIAL	规格型号 SPECIFICATIONS			制造厂商 MANUFACTURERS		UL证书号 UL FILE NO	
CORE	Ferrite core 4*7			JIACHENG			
				OR Equivalent supplier			
WIRE	2UEW-F(QA)			CHENGWE		E227475	
				OR Equivalent supplier			
PIN	Tinned copper clad steel wire (CP)			BAICHUAN			
				OR Equivalent supplier			
EPOXY PAINT	DGT-1(green)			QIFU			
				OR Equivalent supplier			
EPOXY RESIN	DZ-6			JINGDINGSHENG			
				OR Equivalent supplier			
SOLDER	Sn:99.3%/Cu:0.7%			SONGBEN			
				OR Equivalent supplier			

注意事项 Matters needing attention

1、 本承认书保证我司产品作为一个单体时的质量情况， 当我司产品被安装到贵司产品上时， 请保证我司的产品已根据贵司的规范进行了有效评价和确认。

Specification for approval that guarantee the quality of our products as a monomer, when our products were installed on your products, please make sure that our products are according to your specification for the effective evaluation and confirmation.

2、 本承认书的更改需经双方确认， 任何一方单独修改无效。

The recognition of the need to change the book recognized by both parties, either party to amend a separate as null and void.

3、 本承认书在客户收到的七个工作日内， 必须签章返回， 逾期视为默认。

Admit in the book the customer received within seven working days, must return signature, late regarded as the default.

4、 该电感器磁芯的中部缠绕有漆包线并连接于两端引脚， 引脚成型过程中可能造成开路或损伤本体。当您执行引脚成型过程时， 请遵守以下指示：

The middle part of the core of the inductor is wound with enameled wires and is connected with the pins at both ends, Pin forming process may cause open circuit or damage the body. When you perform the pin forming process, Please comply with the following instruction: Please apply supporting jigs as below

包装说明及示意图 Packing instructions and schematic diagram:

