

NOTES:

1. MATERIAL:

1.1 HOUSING: THERMOPLASTIC, HIGH TEMP, UL94V-0, COLOR: BLACK.

1.2 LATCH: THERMOPLASTIC, HIGH TEMP, UL94V-0, COLOR: SEE PART NO.

1.3 CONTACTS: COPPER ALLOY.

1.4 HOLDDOWN: COPPER ALLOY.
2. FINISH:

2.1 CONTACT:

SELECTIVE GOLD PLATING ON THE CONTACT AREA.

100u" MIN. MATTE-TIN PLATING ON THE SOLDERING AREA.

50u" MIN. NICKEL UNDERPLATING OVERALL.

2.2 HOLDDOWN:

100u" MIN. MATTE-TIN PLATING ON THE SOLDERING AREA.

50u" MIN. NICKEL UNDERPLATING OVERALL.
4. PRODUCT SPEC: PS-GEN4-01
5. PACKAGING SPEC: 311304001 FOR TRAY

PART NO.

PCIE-G406 X X X 3 M XX

Housing Color Options
1: Black Hsg + Natural Latch
2: Black Hsg + Black Latch


Contact Plating Options
0: 30u" Gold
1: 15u" Gold

Dim.L
0 - 3.05
1 - 2.20

Halogen Options
Blank: Halogen
HF: Halogen Free

Packaging Options
M: Tray Packaging With Mylar

No. of Pins
3: 164P



	See Sheet 1		
REV	ECN NO.	NAME	DATE

TOLERANCE		UMax conn 东莞市友贸实业有限公司 DONGGUAN UMAX ENTERPRISE LIMITED	
LINEAR	ANGLES		
X.±	X'±		
.X±	.X'±	APPD: Jason	MAT'L:
.XX±	.XX'±	CHKD: Schumi	FINISH:
.XXX±	.XXX'±	DRWN: Lei Songping	Q'TY:

TITLE: PCI EXPRESS Gen4 SMT WITH TAB & LATCH TYPE			
PART NO. PCIE-G406XXX3MXX			
DWG NO. C-PCIE-G406			
	UNITS	SCALE	SHEET
	MM	1 : 1	3 OF 3
REV A0			

CUSTOMER