

SPTECH Silicon PNP Power Transistor

TIP2955

DESCRIPTION

- Excellent Safe Operating Area
- DC Current Gain-
: $h_{FE}=20-70@I_C = -4A$
- Collector-Emitter Saturation Voltage-
: $V_{CE(sat)} = -1.1 V(Max)@ I_C = -4A$
- Complement to Type TIP3055

APPLICATIONS



- Designed for general-purpose switching and amplifier applications.

ABSOLUTE MAXIMUM RATINGS($T_a=25^{\circ}C$)

SYMBOL	PARAMETER	VALUE	UNIT
V_{CBO}	Collector-Base Voltage	-100	V
V_{CEO}	Collector-Emitter Voltage	-60	V
V_{EBO}	Emitter-Base Voltage	-7	V
I_C	Collector Current-Continuous	-15	A
I_B	Base Current	-7	A
P_C	Collector Power Dissipation $T_C=25^{\circ}C$	90	W
T_j	Junction Temperature	150	$^{\circ}C$
T_{stg}	Storage Temperature Range	-65~150	$^{\circ}C$

THERMAL CHARACTERISTICS

SYMBOL	PARAMETER	VALUE	UNIT
$R_{th j-c}$	Thermal Resistance, Junction to Case	1.39	$^{\circ}C/W$
$R_{th j-a}$	Thermal Resistance, Junction to Ambient	35.7	$^{\circ}C/W$



SPTECH Silicon PNP Power Transistors

TIP2955

ELECTRICAL CHARACTERISTICS

 $T_C=25^{\circ}\text{C}$ unless otherwise specified

SYMBOL	PARAMETER	CONDITIONS	MIN	MAX	UNIT
$V_{CEQ(SUS)}$	Collector-Emitter Sustaining Voltage	$I_C = -30\text{mA}$; $I_B = 0$	-60		V
$V_{CE(sat)-1}$	Collector-Emitter Saturation Voltage	$I_C = -4\text{A}$; $I_B = -0.4\text{A}$		-1.0	V
$V_{CE(sat)-2}$	Collector-Emitter Saturation Voltage	$I_C = -10\text{A}$; $I_B = -3.3\text{A}$		-3.0	V
$V_{BE(on)}$	Base-Emitter On Voltage	$I_C = -4\text{A}$; $V_{CE} = -4\text{V}$		-1.8	V
I_{CEO}	Collector Cutoff Current	$V_{CE} = -30\text{V}$; $I_B = 0$		-0.7	mA
I_{CBO}	Collector Cutoff Current	$V_{CB} = -100\text{V}$; $I_E = 0$		-1.0	mA
I_{EBO}	Emitter Cutoff Current	$V_{EB} = -7\text{V}$; $I_C = 0$		-5.0	mA
h_{FE-1}	DC Current Gain	$I_C = -4\text{A}$; $V_{CE} = -4\text{V}$	20	70	
h_{FE-2}	DC Current Gain	$I_C = -10\text{A}$; $V_{CE} = -4\text{V}$	5		
$I_{s/b}$	Second Breakdown Collector Current with Base Forward Biased	$V_{CE} = -30\text{V}$, $t = 1.0\text{s}$, Nonrepetitive	3.0		A
f_T	Current-Gain—Bandwidth Product	$I_C = -0.5\text{A}$; $V_{CE} = -10\text{V}$; $f_{test} = 1.0\text{MHz}$	2.5		MHz