



安装视图



TEL: 0769-82310511-867

1. Rating : DC36V 3A.
2. Contact resistance: $\leq 50\text{m}\Omega$.
3. Insulation resistance: $\geq 1000\text{M}\Omega$ (DC500V).
4. Withstanding voltage: 2000VAC.
5. Operating Force: $\leq 4\text{N}$
6. life test: 50000 cycles.
7. Operation temperature range: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$.
8. Sign "*" is importance dimension.

发光类型: E环形

发光颜色: L蓝

额定电压: AC/DC: 3V/6V/12V/24V/36V/48V/AC: 60V/110V/220V

10	C/NO/NC TERMINAL	BRASS	3	Ag-PLATED
9	LED TERMINAL	BRASS	2	Ag-PLATED
8	CONTACT	SILVER ALLOY	2	
7	C/NO/NC HOUSING	PA46	1	
6	LED HOUSING	PC	1	
5	NUT	BRASS	1	Ni-PLATED
4	O-RING	SILICA GEL	1	BLACK
3	SHELL	SUS/BRASS	1	Ni-PLATED
2	BUTTON	SUS	1	
1	LUMINOUS REGION	PC	1	
NO.	PART NAME	MATERIAL	QTY	FINISHING

TOLERANCE UNLESS SPECIFIED							
< 1.5: ±0.1mm	ANGULAR ±1°						
> 1.5~5.0:±0.25mm							
> 5.0:±0.3mm		NO	DATE	REVISIONS		BY	APPD
TITLE: PUSH SWITCH			UNIT : MM	ROHS	DWN		
MODEL: HY-22A-P11-S-E-L12V-CU-008			SCALE: 1:1	COMPLIANT	CHK'D		
东莞市六钧电子五金有限公司					APPD		
					PRO.AGL:  		REV :A0