




NOTES:

1. MATERIAL:
 - 1.1. HOUSING: PBT ,COLOR IS BLACK;
 - 1.2. CONTACT: PHOSPHOR BRONZE, $\phi 0.46 \pm 0.02 \text{mm}$;
 - 1.3. SHELL: BRASS ;
2. FINISH:
 - 2.1 CONTACT: PLATED GOLD OVER NI;
 - 2.2 SHELL: NI OVER ALL;
3. RECINNEBDED PCB THICKNESS: 1.60mm;
4. ELECTRICAL:
 - 4.1. VOLTAGE RATING: 125 VAC RMS;
 - 4.2. CURRENT RATING: 1.5 AMP;
 - 4.3. CONTACT RESISTANCE: 35MILLIOHMS MAX.;
 - 4.4. WITHSTAND VOLTAGE: 1000 VAC RMS 50(60)Hz,1MIN.;
 - 4.5. INSULATION RESISTANCE: 1000MEGOHMS MIN @500V DC;
5. MECHANICAL:
 - 5.1. MATING/UNMATING FORCE: 25N MAX.;
 - 5.2. RETENTIION STRENGTH: 50N MIN.;
 - 5.3. OPERATING LIFE: 750 CYCLES MIN.;
6. SALT SPRAY TEST: 12H (Excluding riveted bends);
7. SOLDERABILITY: $245 \pm 5^{\circ}\text{C}$, $5 \pm 0.5\text{S}$;
8. RESISTANCE TO SOLDER: $260 \pm 5^{\circ}\text{C}$, $10 \pm 1\text{S}$;
9. ENVIRONMENTAL:
 - 9.1. STORAGE TEMPERATURE RANGE: $-40^{\circ}\text{C} \sim +85^{\circ}\text{C}$;
 - 9.2. OPERATION TEMPERATURE RANGE: $-25^{\circ}\text{C} \sim +70^{\circ}\text{C}$;
10. MATES WITH: MODULAR PLUGS THAT CONFORM TO FCC REGULATION PART 68.500;

	深圳市虹成电子有限公司		品 名 TITLE	网 口	
			料 号 PART NO	HC-WK88-H16-K	
GENERAL TOLERANCES (UNLESS SPECIFIED)		比 例 SCALE	1 : 1		
X.xxx ±0.10 X.xx ±0.20 X.x ±0.30 X.xx° ±1° X.x° ±3° X.° ±5°		单 位 UNIT	MM	制 图 DRAW	AhYe
		张 数 PART NO	1 OF 1	审 核 CHECKED	夏操云
		版 本 REV	A	批 准 APPROVE	赵亮亮
					



RECOMMENDER P. C. B. LAYOUT TOP VIEW
(COMPONENT SIDE TOLERANCE ± 0.05)



DETAIL "X"

SCALE 2:1