

Low power consumption,high performance 150mA LDO RC75XX

General Description

The RC75XX is low power consumption very low 2.5uA ground current, high performance 150mA LDO . The family uses an advanced CMOS process and a PMOSFET pass device to achieve fast start-up, with high output voltage accuracy . The RC75XX is stable with a 1.0μF ceramic output capacitor, and uses a precision voltage reference and feedback loop to achieve a worst-case accuracy of 1% over all load, line, process, and temperature variations. It is fully specified from $T_J = -40^{\circ}\text{C}$ to $+125^{\circ}\text{C}$ and is offered in a SOT89-3 , SOT23-3L package

Features


- Wide Input Voltage Range: 2V to 40V
- Up to 150mA Load Current
- Very Low I_Q : 2.5μA@Typ
- Ultra Low Dropout: 650mV at 150mA Load @ $V_{OUT}=5\text{V}$
- Short current protection:60mA
- Excellent Load/Line Transient Response
- Line Regulation: 0.05% typical
- Package: SOT89-3, SOT23-3L

Mark Specification Label

Part No.	Package	V_{OUT}
RC7530D	SOT89-3	3.0V
RC7533D	SOT89-3	3.3V
RC7550D	SOT89-3	5.0V
RC7530	SOT23-3L	3.0V
RC7533	SOT23-3L	3.3V
RC7550	SOT23-3L	5.0V

Low power consumption,high performance 150mA LDO RC75XX

Pin Configuration




Pin Function

Pin No.		Pin Name	Pin Function
SOT89-3	SOT23-3L		
1	1	GND	Ground.
2	3	IN	Supply input pin. Must be closely decoupled to GND with a 1 μ F or greater ceramic capacitor.
3	2	OUT	Output pin. Bypass a 1 μ F ceramic capacitor from this pin to ground.

Low power consumption, high performance 150mA LDO RC75XX

Block Diagram



Input Capacitor

A $1\mu\text{F}$ - $10\mu\text{F}$ ceramic capacitor is recommended to connect between V_{IN} and GND pins to decouple input power supply glitch and noise. The amount of the capacitance may be increased without limit. This input capacitor must be located as close as possible to the device to assure input stability and less noise. For PCB layout, a wide copper trace is required for both V_{IN} and GND.

Output Capacitor

An output capacitor is required for the stability of the LDO. The recommended output capacitance is from $1\mu\text{F}$ to $10\mu\text{F}$, Equivalent Series Resistance (ESR) is from $5\text{m}\Omega$ to $100\text{m}\Omega$, and temperature characteristics are X7R or X5R. Higher capacitance values help to improve load/line transient response. The output capacitance may be increased to keep low undershoot/overshoot. Place output capacitor as close as possible to OUT and GND pins.

Low Quiescent Current

The RC75XX, consuming only around $2.5\mu\text{A}$ for all input range and output loading, provides great power saving in portable and low power applications.

Short Current Limit Protection

When output current at the OUT pin is higher than current limit threshold or the OUT pin is short-circuit to GND, the short current limit protection will be triggered and clamp the output current to approximately 100mA to prevent over-current and to protect the regulator from damage due to overheating.

Low power consumption, high performance 150mA LDO RC75XX

Absolute Maximum Ratings

Parameter	Rating		Unit
IN Voltage	-0.3 to 49		V
Maximum Power Dissipation	SOT89-3	700	mw
	SOT23-3L	500	
Operating Junction Temperature	-40 to 125		°C
Storage Temperature	-65 to 150		°C
Lead Temperature (Soldering, 10 sec)	300		°C


Electrical Characteristics

($V_{IN} = V_{EN} = 7V$, $T_A = 27^\circ C$ unless otherwise noted)

PARAMETER	SYMBOL	TEST CONDITIONS	MIN	TYP	MAX	UNIT
Input Voltage Operation Range	V_{IN}		2		40	V
Dropout Voltage	V_{drop}	$V_{OUT} = 5V$, $I_{OUT} = 150mA$		650	780	mV
		$V_{OUT} = 5V$, $I_{OUT} = 100mA$		400	530	
DC Supply Quiescent Current	I_Q			2.5		μA
Regulated Output Voltage	V_{OUT}	$I_{OUT} = 1mA$, $-40^\circ C \leq T_A \leq 85^\circ C$	-1		1	%
Output Voltage Line Regulation		$V_{IN} = V_{OUT} + 1V$ to $30V$, $I_{OUT} = 10mA$		0.05		%
Output Voltage Load Regulation		I_{OUT} from $0mA$ to $150mA$		0.2		%
Maximum Output Current		$V_{IN} = V_{OUT} + 1V$	150			mA
Short Current Protection		V_{OUT} short to GND		60		mA


Note: Production test at $+25^\circ C$. Specifications over the temperature range are guaranteed by design and characterization.

Application Circuits



Low power consumption,high performance 150mA LDO RC75XX


3-pin SOT89 Outline Dimensions



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	1.400	1.600	0.055	0.063
b	0.320	0.520	0.013	0.020
b1	0.400	0.580	0.016	0.023
c	0.350	0.440	0.014	0.017
D	4.400	4.600	0.173	0.181
D1	1.550 REF.		0.061 REF.	
E	2.300	2.600	0.091	0.102
E1	3.940	4.250	0.155	0.167
e	1.500 TYP.		0.060 TYP.	
e1	3.000 TYP.		0.118 TYP.	
L	0.900	1.200	0.035	0.047

Low power consumption, high performance 150mA LDO RC75XX

3-pin SOT23-3 Outline Dimensions



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
A	1.050	1.250	0.041	0.049
A1	0.000	0.100	0.000	0.004
A2	1.050	1.150	0.041	0.045
b	0.300	0.500	0.012	0.020
c	0.100	0.200	0.004	0.008
D	2.820	3.020	0.111	0.119
E	1.500	1.700	0.059	0.067
E1	2.650	2.950	0.104	0.116
e	0.950(BSC)		0.037(BSC)	
e1	1.800	2.000	0.071	0.079
L	0.300	0.600	0.012	0.024
θ	0°	8°	0°	8°