


合金电阻规格书-0805 Alloy resistance specification

适用范围Scope

- 合金电阻0805系列 Metal Alloy Resistance 0805 Series.
- 符合RoHS 要求 Complies With RoHS Requirements
- 符合车规AEC-Q200 测试 Conforms To Vehicle-specific AEC-200Q Tests



型号规格Type Designation :

电阻尺寸 Product Type	产品类型 Resistor Size	功率 Power	阻值精度 Resistance tolerance	阻值范围 Resistance
0805	SE(小电极)	3 W	D: 0.5% F: 1% G: 2% J: 5%	R000
		1W		R003
		0.75W		R005-R010
		0.5W		R011-R040


编码原则Coding principle:

制造商/产品 manufacturer	尺寸 size	类型 type	功率 power	阻值 resistance	精度 accuracy	包装数量 quantity
YHR	0805	小电极 SE	0.5W(1D)	R003 R010	0.5%=D 1%=F 2%=G 5%=J	0805(5)

文件编码 Document No	版本 REV	日期 Date	编写 Drawn	审核 Checked	批准 Approved
YH-WG03	A8	2025/04/22	盛广洋	李振超	李俊

示例/ Example: YHR0805SE1DR003F5


结构尺寸Construction and Dimension :

产品尺寸 Product	类型 type	图示 Illustration	尺寸 Size	图例 legend
0805	SE	L	2.0 ± 0.2	
		W	1.25 ± 0.2	
		E	0.35 ± 0.2	
		H	0.5 ± 0.1	

电气规格Electrical Specifications :

类型 type	功率 power	阻值范围 Resistance range	材料 Material	温度系数 TCR	工作温度范围 Operating temperature range	阻值精度 Resistance tolerance	绝缘阻抗 Insulation resistance	最大工作电压 Maximum operating voltage (V)
SE (0805)	3.0 W	R000	紫铜	/	-55℃~+170℃	/	Over 100MΩ	(P*R) ^½
	0.5 W	≦0.2mΩ						
	1W	R003	MnCu	±50 ppm/℃		0.5% 1% 2% 5%		
	0.5 W	4mΩ≦R ≦40mΩ						

功率衰减曲线图 / Derating Curve




文件编码 Document No	版本 REV	日期 Date	编写 Drawn	审核 Checked	批准 Approved
YH-WG03	A8	2025/04/22	盛广洋	李振超	李俊

可靠性验证 Reliability Tests

项目 Project	检测方法 Test Method (依据标准 Refer to IEC 60115, 60068; JIS-C 5201-1)	规格和要求 Specifications and Requirements
温度系数 Temperature coefficient (TCR)	25°C (T1、R1)、125°C(T2、R2)条件下分别测量阻值, 计算 TCR=(R2-R1)/(R1 (T2-T1)) *10 ⁶ Resistance values were measured at 25°C(T1, R1) and 125°C(T2, R2), and TCR was calculated as (R2-R1)/(R1 (T2-T1)) *10 ⁶	参考物理特性TCR规格 Refer to TCR specifications for physical features
短时间过载 Short Time Overload	5倍额定功率, 保持5s, 0Ω最大电流50A 5 times rated power, maintain 5s	$\Delta R \leq \pm (1\% + 0.05\text{m}\Omega)$
绝缘电阻 Insulation resistance	在电极与基片间施加100V±15V直流电压, 保持60s, 然后测绝缘电阻 Apply 100V±15V DC voltage between electrode and substrate, hold for 60 seconds, then measure insulation resistance	> 100 MΩ
耐电压 Withstand voltage	在电极与基片之间以大约100V/S的速率施加有效值为最大过负荷电压的交流电, 保持60±5s An alternating current with an effective value of the maximum overload voltage is applied between the electrode and the substrate at a rate of approximately 100V/S, maintaining 60±5s	无击穿或飞弧 No breakdown or arc
焊锡性 solderability	245°C±5°C 锡槽, 保持2s±0.5s 245°C±5°C tin tank, hold 2s±0.5s	电极上锡面积>95% At least 95% of surface area of electrode shall be covered with new solder
耐热性 Resistance to Soldering Heat	270°C±5°C 锡槽, 保持10s±1s 270°C±5°C tin tank, hold for 10s±1s	$\Delta R \leq \pm (0.5\% + 0.05\text{m}\Omega)$, 无可见损伤 no visible damage
弯曲测试 Bending test	弯曲距离2mm, 保持时间60s±5s Bending distance 2mm, hold time 60s±5s	$\Delta R \leq \pm (0.5\% + 0.05\text{m}\Omega)$ 无机械损伤 no mechanical damage
耐溶测试 Solvent resistance	异丙醇(IPA), 23°C±5°C, 浸10小时 Isopropanol (IPA) at 23°C±5°C for 10 hours	外观无明显损伤 No obvious damage to appearance
长期高温 High Temperature Exposure	高温170°C放置1000H 170°C±2°C, 1000H, stand for 1H, test the resistance value	$\Delta R \leq \pm (1.0\% + 0.05\text{m}\Omega)$
长期低温 Low Temperature Exposure	低温-55°C放置1000H -55°C±2°C, 1000H, stand for 1H, test the resistance value	$\Delta R \leq \pm (0.5\% + 0.05\text{m}\Omega)$
温度循环 Rapid change of Temperature	-55°C 30分钟~常温 5分钟~155°C 30分钟, 1000个循环 -55°C 30 minutes ~ normal temperature 5 minutes ~155°C 30 minutes, 1000 cycles	$\Delta R \leq \pm (0.5\% + 0.05\text{m}\Omega)$
长期耐久 Load Life	70°C±2°C, 1000小时, 额定功率, 通1.5小时/断0.5小时 70°C±2°C, 1000 hours, rated power 1.5 hours on / 0.5 hours off	$\Delta R \leq \pm (1.0\% + 0.05\text{m}\Omega)$
长期耐湿 Moisture with Load	85°C±2°C, 85%±3%RH, 持续 1000 小时, 额定功率, 通1.5小时/断0.5小时 85°C±2°C, 85%±3%RH, 1000 hours, rated power, 1.5 hours on / 0.5 hours off	$\Delta R \leq \pm (1.0\% + 0.05\text{m}\Omega)$


文件编码 Document No	版本 REV	日期 Date	编写 Drawn	审核 Checked	批准 Approved
YH-WG03	A8	2025/04/22	盛广洋	李振超	李俊

载带尺寸Tape Packaging Dimensions:



A	B	W	F	E	P ₁	P ₂	P ₀	D ₀	t
1.65±0.05	2.4±0.1	8.0±0.2	3.5±0.05	1.75±0.1	4.0±0.1	2.0±0.05	4.0±0.05	1.5~1.6	0.8±0.1

卷盘尺寸Reel Dimensions:




型号 Type	A	B	C	D	E	T	W
Reel	178±2.0	60±1.0	13±1.0	2.0±0.5	>22	11.4±0.5	9.0±0.3


文件编码 Document No	版本 REV	日期 Date	编写 Drawn	审核 Checked	批准 Approved
YH-WG03	A8	2025/04/22	盛广洋	李振超	李俊

焊盘尺寸 : Pad Size

焊盘 Pattern	尺寸Size
	SE(小电极)
A	1.5
B	1.0
L	1.0



载带拉力 : Belt Tension



注意事项 : Matters Needing Attention

- 1, 储存时应注意温度和湿度 (温度 5 ~ 35℃, 相对湿度 45 ~ 75% RH). 湿度尽可能保持在范围内;
Chip resistor shall be stored in a room where temperature and humidity must be controlled.
(temperature 5 to 35℃, humidity 45 to 75% RH)However, a humidity keep it low, as it is possible.
- 2, 不能阳光长时间直接照射产品; Chip resistor shall be stored as direct sunshinedoesn't hit on it.
- 3, 不能存储在潮湿, 灰尘及导致焊接性能变差的有害气体环境中(氯化氢气体、亚硫酸气体、硫化氢气体); Chip resistor shall be stored with no moisture, dust, a materialthat will make solder ability inferior, and a harmful gas (Hydrogen chloride, sulfurous acidgas, and Hydrogen sulfide)
- 4, 保存期限: 1 年; Storage life: 1 year;

文件编码 Document No	版本 REV	日期 Date	编写 Drawn	审核 Checked	批准 Approved
YH-WG03	A8	2025/04/22	盛广洋	李振超	李俊



版本信息 :Version History

版本 Version	日期 Date	修订描述 Description of amendment
A1	2022/12/5	首版发行
A2	2023/01/08	更新阻值段
A3	2023/02/06	更新温漂系数
A4	2023/05/06	更新载带尺寸
A5	2024/04/23	更新阻值功率
A6	2024/11/02	更新阻值精度
A7	2025/01/05	更新可靠性验证
A8	2025/04/22	更新阻值段落区间对应主材料名称说明

文件编码 Document No	版本 REV	日期 Date	编写 Drawn	审核 Checked	批准 Approved
YH-WG03	A8	2025/04/22	盛广洋	李振超	李俊