



Features

- ✧ For surface mounted applications in order to optimize board space
- ✧ Low profile space
- ✧ Glass passivated chip
- ✧ High reliability
- ✧ For use in stabilizing and clipping circuits with high power rating.
- ✧ Component in accordance to RoHS 2002/95/EC and WEEE 2002/96/EC

Mechanical Data

- ✧ Case: JEDEC SOD-123FL molded plastic over passivated chip
- ✧ Terminals: Solder plated, solderable per MIL-STD-750 Method 2026
- ✧ Polarity: types the band by laser denotes the cathode
- ✧ Weight: 0.017gram

Applications




- ✧ Voltage stabilization

Maximum Ratings & Thermal Characteristics

(T_A = 25 °C unless otherwise noted)

	Symbol	VALUE	UNIT
power dissipation	P	1.0	W
Typical thermal resistance, junction to ambient	R _{θJA}	180	°C / W
Typical thermal resistance, junction to lead	R _{θJL}	40	°C / W
Junction temperature	T _J	150	°C
storage temperature range	T _{STG}	-55 to +150	°C

SOD-123FL



Dimensions in inches and (millimeters)



Electrical Characteristics $T_A = 25^\circ\text{C}$ unless otherwise noted.

DEVICE House No.	Zener Voltage				Zener Impedance			Leakage Current	
	$V_Z(\text{Volts})$			$@I_{ZT}$	$Z_{ZT}@I_{ZT}$	$Z_{ZK}@I_{ZK}$		$I_R@V_R$	
	Min	Nom	Max	mA	Ω	Ω	mA	μA	Volts
DZL4728A	3.13	3.3	3.47	76	10	400	1.0	100	1.0
DZL4729A	3.42	3.6	3.78	69	10	400	1.0	100	1.0
DZL4730A	3.70	3.9	4.10	64	9	400	1.0	50	1.0
DZL4731A	4.08	4.3	4.52	58	9	400	1.0	50	1.0
DZL4732A	4.46	4.7	4.94	53	8	500	1.0	10	1.0
DZL4733A	4.84	5.1	5.36	49	7	550	1.0	10	1.0
DZL4734A	5.32	5.6	5.88	45	5	600	1.0	10	2.0
DZL4735A	5.89	6.2	6.51	41	2	700	1.0	10	3.0
DZL4736A	6.46	6.8	7.14	37	3.5	700	1.0	10	4.0
DZL4737A	7.12	7.5	7.88	34	4	700	0.5	10	5.0
DZL4738A	7.79	8.2	8.61	31	4.5	700	0.5	10	6.0
DZL4739A	8.64	9.1	9.56	28	5	700	0.5	10	7.0
DZL4740A	9.50	10	10.50	25	7	700	0.25	10	7.6
DZL4741A	10.45	11	11.55	23	8	700	0.25	5	8.4
DZL4742A	11.40	12	12.60	21	9	700	0.25	5	9.1
DZL4743A	12.35	13	13.65	19	10	700	0.25	5	9.9
DZL4744A	14.25	15	15.75	17	14	700	0.25	5	11.4
DZL4745A	15.20	16	16.80	15.5	16	700	0.25	5	12.2
DZL4746A	17.10	18	18.90	14	20	750	0.25	5	13.7
DZL4747A	19.00	20	21.00	12.5	22	750	0.25	5	15.2
DZL4748A	20.90	22	23.10	11.5	23	750	0.25	5	16.7
DZL4749A	22.80	24	25.20	10.5	25	750	0.25	5	18.2
DZL4750A	25.65	27	28.35	9.5	35	750	0.25	5	20.6
DZL4751A	28.50	30	31.50	8.5	40	1000	0.25	5	22.8
DZL4752A	31.35	33	34.65	7.5	45	1000	0.25	5	25.1
DZL4753A	34.20	36	37.80	7	50	1000	0.25	5	27.4
DZL4754A	37.05	39	40.95	6.5	60	1500	0.25	5	29.7
DZL4755A	40.85	43	45.15	6	70	1500	0.25	5	32.7
DZL4756A	44.65	47	49.35	5.5	80	1500	0.25	5	35.8
DZL4757A	48.45	51	53.55	5	95	1500	0.25	5	38.8
DZL4758A	53.20	56	58.80	4.5	110	2000	0.25	5	42.6
DZL4759A	58.90	62	65.10	4	125	2000	0.25	5	47.1
DZL4760A	64.60	68	71.40	3.7	150	2000	0.25	5	51.7
DZL4761A	71.25	75	78.75	3.3	175	2000	0.25	5	56.0
DZL4762A	77.90	82	86.10	3	200	3000	0.25	5	62.2
DZL4763A	86.45	91	95.55	2.8	250	3000	0.25	5	69.2
DZL4764A	95.00	100	105.00	2.5	350	3000	0.25	5	76.0
DZL4765A	104.50	110	115.50	2.3	450	4000	0.25	5	83.6
DZL4766A	114.00	120	126.00	2.0	550	4500	0.25	5	91.2
DZL4767A	123.50	130	136.50	1.9	700	5000	0.25	5	98.8
DZL4768A	142.50	150	157.50	1.7	1000	6000	0.25	5	114.0
DZL4769A	152.00	160	168.00	1.6	1100	6500	0.25	5	121.6
DZL4770A	171.00	180	189.00	1.4	1200	7000	0.25	5	136.8
DZL4771A	190.00	200	210.00	1.2	1500	8000	0.25	5	152.0

PACKAGE	SPQ/PCS	CARTON SPQ/PCS	CARTON SIZE/CM	CARTON GW/KG	CARTON NW/KG
SOD-123FL	3000/REEL	90000	40X20X22	5.00	4.00

Ratings and Characteristic Curves

FIG1: Maximum Continuous Power Dissipation




FIG2: Typical Zener Impedance




FIG3: Typical Temperature Coefficients




FIG4: Typical Instantaneous Forward Characteristics for SMA4763A




FIG5: Typical Reverse Characteristics

