



承認書

SPECIFICATION FOR APPROVAL

CUSTOMER:

DESCRIPTION:

WIRE WOUND CHIP INDUCTOR

PART NO:

MWI0805UC系列

CUST. PART NO:

REV. NO.

A0

DRAWING		
PREPARED	CHECKED	APPROVED
邹声平	卢嘉良	曾凡强
DATE:	2025/5/1	

CUSTOMER APPROVE



东莞市铭易轩电子科技有限公司

DongGuan Ming Yixuan Electronic Technology Co., LTD

地址: 广东省东莞市大朗镇景泰路20号VV大厦

电话: 15970768093 , 13640935893


网址: <http://www.dgmingyixuan.com>



MODIFY RECORD 变更履历


[illegible]

CUSTOMER:		REV. NO.	A0
PART NO:	MWI0805UC系列	PAGE NO:	2/9
CUST. PART NO:		DATE:	2025/5/1

1. SHAPE & DIMENSION (UNIT:mm)


Recommended patterns

L	W	T	E	F	D
2.29 Max.	1.73 Max.	1.52 Max.	1.02 Typ.	1.78 Typ.	0.76 Typ.

2. SCHEMATIC

3. PART NUMBERING SYSTEM

MWI	0805	UC	2R2	J	S	T	-	HF
1	2	3	4	5	6	7		8

- 1 PRODUCT SYMBOL (产品代号)
- 2 DIMENSIONS (规格尺寸)
- 3 MATERIAL (芯片类型)
- 4 INDUCTANCE (电感量)
- 5 TOLERANCE (公差) : S±0.3; G±2%; J±5%; K±10%; M±20%
- 6 TERMINAL (端电极材料) : S-锡端头
- 7 PACKAGING (包装方式) : T-编带盘装; B-散装
- 8 E.P. (环保) : LF—Lead Free HF—Halogen Free FP—Red Phosphor Free

APPROVED	CHECKED	PREPARED
曾凡强	卢嘉良	邹声平

CUSTOMER:		REV. NO:	A0
PART NO:	MWI0805UC系列	PAGE NO:	3/9
CUST. PART NO:		DATE:	2025/5/1

4. ELECTRICAL CHARACTERISTICS

No.	Part Number	L	Freq	Q	SRF	Rdc	Irms	Tolerance
		(nH)	(MHz)	Min.	(MHz)Min.	(Ω)Max.	(mA) Max.	
1	MWI0805UC2N2□ST-HF	2.2	250	50@1GHz	7900	0.06	800	S,J,K,M
2	MWI0805UC2N7□ST-HF	2.7	250	50@1GHz	7900	0.06	800	S,J,K,M
3	MWI0805UC3N0□ST-HF	3	250	40@1.5GHz	7900	0.06	800	S,J,K,M
4	MWI0805UC3N3□ST-HF	3.3	250	40@1.5GHz	7900	0.08	600	S,J,K,M
5	MWI0805UC3N6□ST-HF	3.6	250	20@1GHz	7900	0.2	200	S,J,K,M
6	MWI0805UC3N9□ST-HF	3.9	250	20@1GHz	7900	0.2	150	S,J,K,M
7	MWI0805UC4N7□ST-HF	4.7	250	35@1GHz	6200	0.08	600	S,J,K,M
8	MWI0805UC5N1□ST-HF	5.1	250	50@1GHz	6200	0.08	600	S,J,K,M
9	MWI0805UC5N6□ST-HF	5.6	250	65@1GHz	5900	0.08	600	J,K,M
10	MWI0805UC6N2□ST-HF	6.2	250	65@1GHz	5900	0.08	600	J,K,M
11	MWI0805UC6N8□ST-HF	6.8	250	50@1GHz	5600	0.11	600	J,K,M
12	MWI0805UC7N5□ST-HF	7.5	250	50@1GHz	4800	0.14	600	J,K,M
13	MWI0805UC8N2□ST-HF	8.2	250	50@1GHz	4400	0.12	600	J,K,M
14	MWI0805UC9N1□ST-HF	9.1	250	60@500MHz	4300	0.1	600	J,K,M
15	MWI0805UC10N□ST-HF	10	250	60@500MHz	4300	0.1	600	J,K,M
16	MWI0805UC12N□ST-HF	12	250	50@500MHz	4000	0.15	600	J,K,M
17	MWI0805UC15N□ST-HF	15	250	50@500MHz	3200	0.17	600	J,K,M
18	MWI0805UC16N□ST-HF	16	250	50@500MHz	3200	0.17	600	J,K,M
19	MWI0805UC18N□ST-HF	18	250	50@500MHz	3100	0.2	600	J,K,M
20	MWI0805UC20N□ST-HF	20	250	55@500MHz	2600	0.22	500	J,K,M
21	MWI0805UC22N□ST-HF	22	250	55@500MHz	2600	0.22	500	G,J,K,M
22	MWI0805UC23N□ST-HF	23	250	50@500MHz	2400	0.22	500	G,J,K,M
23	MWI0805UC24N□ST-HF	24	250	50@500MHz	2400	0.22	500	G,J,K,M
24	MWI0805UC25N□ST-HF	25	250	50@500MHz	2450	0.22	500	G,J,K,M

□:表示产品公差

APPROVED	CHECKED	PREPARED
曾凡强	卢嘉良	邹声平

CUSTOMER:		REV. NO.	A0
PART NO:	MWI0805UC系列	PAGE NO:	4/9
CUST. PART NO:		DATE:	2025/5/1

4. ELECTRICAL CHARACTERISTICS

No.	Part Number	L	Freq	Q	SRF	Rdc	Irms	Tolerance
		(nH)	(MHz)	Min.	(MHz)Min.	(Ω)Max.	(mA) Max.	
25	MWI0805UC27N□ST-HF	27	250	55@500MHz	2580	0.250	500	G,J,K,M
26	MWI0805UC30N□ST-HF	30	250	55@500MHz	2400	0.250	500	G,J,K,M
27	MWI0805UC33N□ST-HF	33	250	60@500MHz	2150	0.270	500	G,J,K,M
28	MWI0805UC36N□ST-HF	36	250	55@500MHz	1900	0.270	500	G,J,K,M
29	MWI0805UC39N□ST-HF	39	250	60@500MHz	1850	0.290	500	G,J,K,M
30	MWI0805UC43N□ST-HF	43	200	60@500MHz	1800	0.340	500	G,J,K,M
31	MWI0805UC47N□ST-HF	47	200	60@500MHz	1700	0.310	500	G,J,K,M
32	MWI0805UC50N□ST-HF	50	200	60@500MHz	1650	0.340	500	G,J,K,M
33	MWI0805UC56N□ST-HF	56	200	60@500MHz	1600	0.340	500	G,J,K,M
34	MWI0805UC62N□ST-HF	62	200	60@500MHz	1450	0.360	500	G,J,K,M
35	MWI0805UC64N□ST-HF	64	200	60@500MHz	1500	0.380	500	G,J,K,M
36	MWI0805UC68N□ST-HF	68	200	60@500MHz	1500	0.380	500	G,J,K,M
37	MWI0805UC72N□ST-HF	72	150	60@500MHz	1400	0.380	500	G,J,K,M
38	MWI0805UC75N□ST-HF	75	150	60@500MHz	1400	0.400	450	G,J,K,M
39	MWI0805UC78N□ST-HF	78	150	60@500MHz	1400	0.400	450	G,J,K,M
40	MWI0805UC82N□ST-HF	82	150	65@500MHz	1330	0.420	400	G,J,K,M
41	MWI0805UC91N□ST-HF	91	150	65@500MHz	1330	0.480	400	G,J,K,M
42	MWI0805UCR10□ST-HF	100	150	65@500MHz	1250	0.460	400	G,J,K,M
43	MWI0805UCR11□ST-HF	110	150	50@250MHz	1100	0.480	400	G,J,K,M
44	MWI0805UCR12□ST-HF	120	150	50@250MHz	1100	0.510	400	G,J,K,M
45	MWI0805UCR13□ST-HF	130	100	50@250MHz	920	0.560	400	G,J,K,M
46	MWI0805UCR14□ST-HF	140	100	50@250MHz	920	0.560	400	G,J,K,M
47	MWI0805UCR15□ST-HF	150	100	50@250MHz	920	0.560	400	G,J,K,M
48	MWI0805UCR16□ST-HF	160	100	50@250MHz	920	0.600	400	G,J,K,M

□:表示产品公差

APPROVED	CHECKED	PREPARED
曾凡强	卢嘉良	邹声平

CUSTOMER:		REV. NO.	A0
PART NO:	MWI0805UC系列	PAGE NO:	5/9
CUST. PART NO:		DATE:	2025/5/1

4. ELECTRICAL CHARACTERISTICS

No.	Part Number	L	Freq	Q	SRF	Rdc	Irms	Tolerance
		(nH)	(MHz)	Min.	(MHz)Min.	(Ω)Max.	(mA) Max.	
49	MWI0805UCR18□ST-HF	270	100	50@250MHz	920	0.640	400	G,J,K,M
50	MWI0805UCR20□ST-HF	280	100	50@250MHz	860	0.680	400	G,J,K,M
51	MWI0805UCR21□ST-HF	290	100	50@250MHz	820	0.700	400	G,J,K,M
52	MWI0805UCR22□ST-HF	300	100	50@250MHz	820	0.700	400	G,J,K,M
53	MWI0805UCR24□ST-HF	330	100	44@250MHz	770	1.000	350	G,J,K,M
54	MWI0805UCR25□ST-HF	360	100	45@250MHz	750	1.200	350	G,J,K,M
55	MWI0805UCR27□ST-HF	390	100	48@250MHz	730	1.000	350	G,J,K,M
56	MWI0805UCR28□ST-HF	420	100	48@250MHz	550	1.350	350	G,J,K,M
57	MWI0805UCR29□ST-HF	430	150	48@250MHz	450	1.400	310	G,J,K,M
58	MWI0805UCR30□ST-HF	470	150	48@250MHz	450	1.400	310	G,J,K,M
59	MWI0805UCR33□ST-HF	560	100	48@250MHz	650	1.400	310	G,J,K,M
60	MWI0805UCR36□ST-HF	620	100	48@250MHz	630	1.450	300	G,J,K,M
61	MWI0805UCR39□ST-HF	680	100	48@250MHz	600	1.500	290	G,J,K,M
62	MWI0805UCR42□ST-HF	750	50	33@100MHz	425	1.700	250	G,J,K,M
63	MWI0805UCR43□ST-HF	820	50	33@100MHz	425	1.700	250	G,J,K,M
64	MWI0805UCR47□ST-HF	880	50	33@100MHz	375	1.760	250	G,J,K,M
65	MWI0805UCR56□ST-HF	910	25	23@50MHz	330	1.900	230	G,J,K,M
66	MWI0805UCR62□ST-HF	1000	25	23@50MHz	320	2.200	210	G,J,K,M
67	MWI0805UCR68□ST-HF	1200	25	23@50MHz	310	2.200	190	G,J,K,M
68	MWI0805UCR75□ST-HF	1500	25	23@50MHz	310	2.300	180	G,J,K,M
69	MWI0805UCR82□ST-HF	1600	25	23@50MHz	310	2.350	180	G,J,K,M
70	MWI0805UCR88□ST-HF	1800	25	23@50MHz	310	2.350	180	G,J,K,M
71	MWI0805UCR91□ST-HF	2200	25	22@50MHz	250	2.450	170	G,J,K,M
72	MWI0805UC1R0□ST-HF	2700	25	20@50MHz	220	2.500	170	J,K,M

□:表示产品公差

APPROVED	CHECKED	PREPARED
曾凡强	卢嘉良	邹声平

CUSTOMER:		REV. NO.	A0
PART NO:	MWI0805UC系列	PAGE NO:	6/9
CUST. PART NO:		DATE:	2025/5/1

4. ELECTRICAL CHARACTERISTICS

No.	Part Number	L	Freq	Q	SRF	Rdc	Irms	Tolerance
		(nH)	(MHz)	Min.	(MHz)Min.	(Ω)Max.	(mA) Max.	
73	MWI0805UC1R2□ST-HF	1200	25	20@25MHz	180	2.900	150	J,K,M
74	MWI0805UC1R5□ST-HF	1500	25	20@25MHz	160	3.300	150	J,K,M
75	MWI0805UC1R6□ST-HF	1600	25	20@25MHz	140	3.400	150	J,K,M
76	MWI0805UC1R8□ST-HF	1800	25	20@25MHz	130	3.500	120	J,K,M
77	MWI0805UC2R2□ST-HF	2200	25	20@25MHz	100	4.500	120	J,K,M
78	MWI0805UC2R7□ST-HF	2700	25	18@25MHz	80	4.800	100	J,K,M
79	MWI0805UC3R3□ST-HF	3300	25	18@25MHz	50	6.800	50	J,K,M
80	MWI0805UC4R7□ST-HF	4700	25	18@25MHz	40	7.000	30	J,K,M

□:表示产品公差

Test remarks

- (1).All test data is referenced to 25 °C ambient.
- (2). Irms: DC current that causes the temperature rise ($\Delta T \leq 40^{\circ}\text{C}$) from 25°C ambient.

5. GENERAL SPECIFICATION


- (1). Operating temp.: -40°C ~ +125°C (Including self-generated heat).
- (2). Storage temp.: -10°C ~ +40°C R.H.:60% Max.
- (3). Moisture sensitivity level (MSL) 1
- (4). Recommended products should be used within 12 months from the date of delivery
- (5). The part temperature (ambient + temp rise) should not exceed 125 °C under worst case operating conditions. Circuit design, component placement, PWB trace size and thickness, airflow and other cooling provisions all affect the part temperature. Part temperature should be verified in the end application.

APPROVED	CHECKED	PREPARED
曾凡强	卢嘉良	邹声平

CUSTOMER:		REV. NO.	A0
PART NO:	MWI0805UC系列	PAGE NO:	7/9
CUST. PART NO:		DATE:	2025/5/1

6. SOLDERING CONDITIONS

Figure 1. Re-flow Soldering (Lead Free)



Note:


Preheat circuit and products to 150°C

260°C tip temperature (Max)

Reflow times: no more than 2 times

Solder paste thickness: the best 0.08mm is ,but max is 0.1mm

Figure 2. Hand Soldering





Note:

Use a 20 watt soldering iron with tip diameter of 1.0mm


Limit soldering time to 3 sec.

APPROVED	CHECKED	PREPARED
曾凡强	卢嘉良	邹声平

CUSTOMER:		REV NO:	A0
PART NO:	MWI0805UC系列	PAGE NO:	8/9
CUST. PART NO:		DATE:	2025/5/1

7. PACKAGING(unit: mm)

胶带 POLYSTYRENE TAPE


Peeling off force
Pull strength
0402~1210:20g~80g
Speed of peeling off:
300mm/min±10%



		A	B	T
胶带	0805	1.85	2.4	1.45

Type	ΦA	ΦB	ΦC	ΦD	E	W	t
0805	178	60	13	21	2	8.4	2


包装数量(PACKAGING QUANTITY): 2000Pcs/盘

APPROVED	CHECKED	PREPARED
曾凡强	卢嘉良	邹声平

CUSTOMER:		REV NO:	A0
PART NO:	MWI0805UC系列	PAGE NO:	9/9
CUST. PART NO:		DATE:	2025/5/1

8. Package Specifications

Inside Box And Outside Carton



卷轴数量 每卷:2000PCS	→	内盒包装数量 每盒四盘，共8000 PCS	→	外箱包装数量 小箱6盒，共48000 PCS 中箱8盒，共64000 PCS 大箱10盒，共80000 PCS
		内盒包装尺寸 20.3*19.3*5.5cm	→	外箱包装尺寸 小箱，40.6*23*19.7cm 中箱，41*22*26cm 大箱，41*22*33cm

APPROVED	CHECKED	PREPARED
曾凡强	卢嘉良	邹声平