



BCH65S30D2

Silicon Carbide Schottky Diode

650V, 30A

Description

BCH65S30D3 utilizes Bestirpower's advanced silicon carbide diode technology. This technology combines the benefits of excellent low forward voltage and robustness. Consequently, the family is suitable for application requiring high power efficiency

Benefits

- High-speed switching
- Low heat dissipation requirements
- Reduce size and cost of the system
- High-reliability
- System efficiency improvement


Applications

- Free Wheeling Diodes in Inverter stages
- Power factor correction
- Data Center
- Switch mode power supply

Features

V_{RRM}	I_F	T_C	Q_C
650 V	30 A	142°C	85 nC

- High surge current capability
- No reverse recovery
- Positive temperature coefficient
- Benchmark switching behavior
- RoHS compliant / Halogen-free



Absolute Maximum Ratings ($T_C = 25^\circ\text{C}$ unless otherwise noted)

Symbol	Parameter	Value	Unit
V_{RRM}	Repetitive Peak Reverse Voltage	650	V
I_F	Forward Current	$T_C = 25^\circ\text{C}$	72 A
		$T_C = 135^\circ\text{C}$	34 A
		$T_C = 142^\circ\text{C}$	30 A
$I_{F,SM}$	Non-Repetitive Forward Surge Current	$T_C = 25^\circ\text{C}, t_p = 10 \text{ ms}$	216 A
		$T_C = 110^\circ\text{C}, t_p = 10 \text{ ms}$	187 A
$I_{F,RM}$	Repetitive Peak Forward Surge Current	$T_C = 25^\circ\text{C}, t_p = 10 \text{ ms}$	186 A
I^2dt value	$\int I^2t$	$T_C = 25^\circ\text{C}, t_p = 10 \text{ ms}$	233 A ² s
		$T_C = 110^\circ\text{C}, t_p = 10 \text{ ms}$	174 A ² s
P_{tot}	Power Dissipation	$T_C = 25^\circ\text{C}$	254 W
		$T_C = 110^\circ\text{C}$	110 W
		$T_C = 150^\circ\text{C}$	42 W
T_J, T_{STG}	Operating Junction and Storage Temperature	-55 to +175	°C

Thermal Characteristics

Symbol	Parameter	Value	Unit
$R_{\theta JC}$	Thermal Resistance, Junction to Case, Typ.	0.59	°C/W

Electrical Characteristics ($T_C = 25^\circ\text{C}$ unless otherwise noted)

Symbol	Parameter	Test Conditions	Min	Typ	Max	Unit
V_{DC}	DC blocking voltage	$I_R = 100\mu\text{A}$	650	-	-	V
V_F	Forward Voltage	$I_F = 30\text{A}, T_J = 25^\circ\text{C}$	-	1.45	1.8	V
		$I_F = 30\text{A}, T_J = 175^\circ\text{C}$	-	1.95	-	
I_R	Reverse Current	$V_R = 650\text{V}, T_J = 25^\circ\text{C}$	-	2	20	μA
		$V_R = 650\text{V}, T_J = 175^\circ\text{C}$	-	40	200	
Q_C	Total Capacitive Charge	$V_R = 400\text{V}, T_J = 25^\circ\text{C}$	-	85	-	nC
C	Total Capacitance	$V_R = 0\text{V}, f = 1\text{MHz}$	-	2050	-	pF
		$V_R = 200\text{V}, f = 1\text{MHz}$	-	162	-	
		$V_R = 400\text{V}, f = 1\text{MHz}$	-	137	-	
E_C	Capacitance Stored Energy	$V_R = 400\text{V}$	-	21	-	μJ

Typical Performance Characteristics

Figure 1. Forward Characteristics




Figure 2. Reverse Characteristics




Figure 3. Peak Forward Current Derating




Figure 4. Power Dissipation




Figure 5. Capacitance vs. Reverse Voltage






Figure 6. Capacitance Charge vs. Reverse Voltage





Typical Performance Characteristics

Figure 7. Transient Thermal Impedance



Package Outlines TO220-2



Package Marking and Ordering Information

Part Number	Top Marking	Package	Packing Method	Quantity
BCH65S30D2	BCH65S30D2	TO220-2	Tube	50 units

Disclaimer

Bestirpower reserve the right to make changes, corrections, enhancements, modifications, and improvements to Bestirpower products and/or to this document at any time without notice.

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics. Bestirpower does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Products or technical information described in this document.

This document is the property of Bestirpower Co., LTD., and not allowed to copy or transformed to other format if not under the authority approval.

© 2024 bestirpower – All rights reserved