



SOT-23 Bipolar Transistor 双极型三极管


■ Features 特点

NPN General Purpose 通用



SOT-23

- 1. BASE
- 2. EMITTER
- 3. COLLECTOR



■ Absolute Maximum Ratings 最大额定值

| Characteristic 特性参数                         | Symbol 符号                     | Rat 额定值                      | Unit 单位                     |
|---------------------------------------------|-------------------------------|------------------------------|-----------------------------|
| Collector-Base Voltage 集电极基极电压              | $V_{CBO}$                     | 60                           | V                           |
| Collector-Emitter Voltage 集电极发射极电压          | $V_{CEO}$                     | 50                           | V                           |
| Emitter-Base Voltage 发射极基极电压                | $V_{EBO}$                     | 5                            | V                           |
| Collector Current 集电极电流                     | $I_C$                         | 150                          | mA                          |
| Power dissipation 耗散功率                      | $P_C(T_a=25^{\circ}\text{C})$ | 200                          | mW                          |
| Thermal Resistance Junction-Ambient 热阻      | $R_{\theta JA}$               | 625                          | $^{\circ}\text{C}/\text{W}$ |
| Junction and Storage Temperature<br>结温和储藏温度 | $T_J, T_{stg}$                | -55to+150 $^{\circ}\text{C}$ |                             |

■ Device Marking 产品打标

S1815-6AF=HF




## ■Electrical Characteristics 电特性


( $T_A=25^{\circ}\text{C}$  unless otherwise noted 如无特殊说明, 温度为  $25^{\circ}\text{C}$ )

| Characteristic<br>特性参数                                                                           | Symbol<br>符号  | Min<br>最小值 | Type<br>典型值 | Max<br>最大值 | Unit<br>单位 |
|--------------------------------------------------------------------------------------------------|---------------|------------|-------------|------------|------------|
| Collector-Base Breakdown Voltage<br>集电极基极击穿电压<br>( $I_C=100\mu\text{A}$ , $I_E=0$ )              | $BV_{CBO}$    | 60         | —           | —          | V          |
| Collector-Emitter Breakdown Voltage<br>集电极发射极击穿电压<br>( $I_C=1\text{mA}$ , $I_B=0$ )              | $BV_{CEO}$    | 50         | —           | —          | V          |
| Emitter-Base Breakdown Voltage<br>发射极基极击穿电压<br>( $I_E=100\mu\text{A}$ , $I_C=0$ )                | $BV_{EBO}$    | 5          | —           | —          | V          |
| Collector-Base Leakage Current<br>集电极基极漏电流<br>( $V_{CB}=60\text{V}$ , $I_E=0$ )                  | $I_{CBO}$     | —          | —           | 100        | nA         |
| Emitter-Base Leakage Current<br>发射极基极漏电流<br>( $V_{EB}=5\text{V}$ , $I_C=0$ )                     | $I_{EBO}$     | —          | —           | 100        | nA         |
| DC Current Gain<br>直流电流增益<br>( $V_{CE}=6\text{V}$ , $I_C=2\text{mA}$ )                           | $H_{FE}$      | 120        | —           | 400        |            |
| Collector-Emitter Saturation Voltage<br>集电极发射极饱和压降<br>( $I_C=100\text{mA}$ , $I_B=10\text{mA}$ ) | $V_{CE(sat)}$ | —          | —           | 0.25       | V          |
| Base-Emitter Saturation Voltage<br>基极发射极饱和压降<br>( $I_C=100\text{mA}$ , $I_B=10\text{mA}$ )       | $V_{BE(sat)}$ | —          | —           | 1          | V          |
| Transition Frequency<br>特征频率<br>( $V_{CE}=10\text{V}$ , $I_C=1\text{mA}$ )                       | $f_T$         | 80         | —           | —          | MHz        |
| Output Capacitance<br>输出电容<br>( $V_{CB}=6\text{V}$ , $I_E=0$ , $f=1\text{MHz}$ )                 | $C_{ob}$      | —          | 3           | —          | pF         |

### ■ Typical Characteristic Curve 典型特性曲线



### ■Dimension 外形封装尺寸



| Symbol | Dimensions In Millimeters |       | Dimensions In Inches |       |
|--------|---------------------------|-------|----------------------|-------|
|        | Min                       | Max   | Min                  | Max   |
| A      | 0.900                     | 1.150 | 0.035                | 0.045 |
| A1     | 0.000                     | 0.100 | 0.000                | 0.004 |
| A2     | 0.900                     | 1.050 | 0.035                | 0.041 |
| b      | 0.300                     | 0.500 | 0.012                | 0.020 |
| c      | 0.080                     | 0.150 | 0.003                | 0.006 |
| D      | 2.800                     | 3.000 | 0.110                | 0.118 |
| E      | 1.200                     | 1.400 | 0.050                | 0.055 |
| E1     | 2.250                     | 2.550 | 0.089                | 0.100 |
| e      | 0.900                     | 1.00  | 0.035                | 0.039 |
| e1     | 1.800                     | 2.000 | 0.071                | 0.079 |
| L      | 0.500                     | 0.600 | 0.020                | 0.024 |
| L1     | 0.300                     | 0.500 | 0.012                | 0.020 |
| θ      | 0°                        | 8°    | 0°                   | 8°    |