

浙江创都电子科技有限公司

ZHE JIANG CHUANG DU ELECTRONICS CO.,LTD

APPROVAL SHEET



CUSTOMER: _____

CUSTOMER P/N: _____ (小批可用管装) (批货推荐卷装)

PART NAME: 1.0mmPitch H=2.5mm SMT 拉拔K型 上接

PART NO. : CAX-A07-**SCB-H2.5

MANUFACTURE SIGNATURE			CUSTOMER SIGNATURE
SALES REP.	R&D DEPT.	QA DEPT	
DAET:	DAET:	DAET:	DAET:



SECTION A-A
SCALE 1:1

Note:

1. Material:

- 1.1 Housing: thermoplastic high temp.UL94V-0; Color: natural.
- 1.2 Latch: thermoplastic high temp.UL94V-0; Color: black.
- 1.3 Terminal: copper alloy.
- 1.4 Fitting Nail: copper alloy.

2. Finish:

- 2.1 Terminal:
Underplating: Au/matt Tin overall.
- 2.2 Fitting Nail:
Underplating: matt Tin overall.

3. Product must comply HF RoHS specification.

4. Product No:

AFA07-S **

CKTS

CONTACTS TYPE

E:Upper

PLATING

1:Gold flash 1u"

2:Gold flash 2u"




3:Gold flash 3u"

B:Bright-Tin 80-150u"


C:Matte-Tin 80-150u"

REMARKS
HF:Halogen free


PACKING
A:Tape&Reel
C:Tube



Product Appearance Description



RECOMMENDED P.C.B. PATTERN LAYOUT



RECOMMENDED FPC/FFC DIMENSION

CUSTOMER DRAWING

Tolerance Unspecified
(未注公差)

0.0 ±0.25 0° ±5°

0.00 ±0.15 0° 0 ±3°

0.000 ±0.10 0° 0.00 ±1°

Project View
(投影视图)

1 OF 1

Rev(版本):
A

Size(图幅):
A4

Unit(单位):
MM

Scale(比例):
1:1

Page(页数):
1 OF 1

Rev(版本):
A

浙江创都电子科技有限公司

ZHE JIANG CHUANG DU ELECTRONICS CO.,LTD

Product Name(产品名称):

1.0Pitch H=2.5 FPC/FFC ZIF R/A TypeK1 Upper SMT CONN

Product No(产品料号):


CAX-A07-**SCB-H2.5

Designer(设计):

Checked(审核):

Approved(核准):

Rev	Change Description	Date	Revisor
A	初版发行	2011/03/23	
版本	变更内容	日期	制/修订人



DETAIL B
SCALE 5:1

-

浙江创都电子科技有限公司

ZHE JIANG CHUANG DU ELECTRONICS CO.,LTD

REV. A

产 品 规 格 书 PRODUCT SPECIFICATION

【1】适用范围 SCOPE

本规格书适用于 1.0mm Pitch H=2.5 FPC/FFC 拉拔卧式 K 型 SMT 型连接器系列。

This specification covers the 1.0mm Pitch H=2.5 FPC/FFC ZIF R/A TypeK SMT Connectors series.

【2】外观尺寸 CONNECTOR DIMENSIONS

请参照图面

See attached drawings.

【3】材质 MATERIAL

绝缘胶体 Housing: LCP

颜色 Color:自然色 Natural.

耐燃等级 (UL94V-0) Flammability Rating (UL94V-0).

后盖 Latch: LCP

颜色 Color:黑色 Black.

耐燃等级 (UL94V-0) Flammability Rating (UL94V-0).

端子 Terminal: 磷青铜 Phosphor Bronze.

焊片 Fitting Nail: 磷青铜 Phosphor Bronze.

【4】建议 P.C.B LAYOUT 图 ACCOMMODATED P.C.B LAYOUT

请参照图面

See attached drawings.

【5】等级 RATING

项 目 ITEM	规 格 SPECIFICATIONS
最大容许电压 Operating Voltage (Max.)	50V AC
最大容许电流 Current Rating (Max.)	0.5A DC
使用温度范围 Operating Temperature range	*-55° C ~ +85° C
使用湿度范围 Operating humidity range	相对湿度90%以下 Relative humidity 90% max.
保存温度范围 Storage temperature range	-40° C ~ +50° C
保存湿度范围 Storage humidity range	相对湿度90%以下 Relative humidity 90% max.

浙江创都电子科技有限公司

ZHE JIANG CHUANG DU ELECTRONICS CO.,LTD

REV. A

※:包含电流通过所产生的上升温度 Including terminal temperature rise.

【6】性能 PERFORMANCE

6.1 电气特性 ELECTRICAL PERFORMANCE

项目 ITEM	测试条件 TEST CONDITION	规格 REQUIRMENT
接触阻抗 Contact Resistance	将样品与适合之FPC/FFC连接,测试电压20mV, 限电流100mA下进行阻抗测试。(EIA-364-23) Mate applicable FPC/FFC and measure by dry circuit, 20mV Max, 100mA. (EIA-364-23)	40 mΩ最大. 40 mΩ Max.
绝缘阻抗 Insulation Resistance	将样品与适合之FPC/FFC连接,提供相邻端子间测试电压500V DC进行绝缘阻抗测试(EIA-364-21) Mate applicable FPC/FFC and apply 500V DC between adjacent terminal or ground. (EIA-364-21)	500 MΩ最小. 500 MΩ Min.
耐电压 Dielectric Strength	将样品与适合之FPC/FFC连接,相邻端子间需可承受250V AC(rms) 1分钟。(EIA-364-20) Mate applicable FPC/FFC ,apply 250V AC(rms) for 1 minute between adjacent terminal or ground. (EIA-364-20)	目视外观无任何损坏异状 No Breakdown

6.2 机械特性 MECHANICAL PERFORMANCE

项目 ITEM	测试条件 TEST CONDITION	规格 REQUIRMENT
FPC保持力 FPC Retention Force	将盖子盖上,与FPC/FFC连接,以操作速度每分钟位移25±3mm进行FPC/FFC保持力测试。(EIA-364-13) Insert the Latch, pull the FPC at a rate of 25±3mm per minute. (EIA-364-13)	Pos. x 0.40N最小 Pos. x 0.40N Min.

浙江创都电子科技有限公司

ZHE JIANG CHUANG DU ELECTRONICS CO.,LTD

REV. A

端子保持力 Terminal Retention Force	端子与Housing组装后,以操作速度每分钟位移 $25\pm 3\text{mm}$ 将端子拔出Housing,进行端子保持力测试。 (EIA-364-29) Apply axial pull out force at the rate of $25\pm 3\text{ mm/minute}$ on the terminal assembled in the housing. (EIA-364-29)	3.0N最小. 3.0N Min.
项目 ITEM	测试条件 TEST CONDITION	规格 REQUIRMENT
焊片保持力 Fitting Nail Retention Force	焊片与Housing组装后,以操作速度每分钟位移 $25\pm 3\text{mm}$ 将焊片拔出Housing,进行焊片保持力测试。 (EIA-364-29) Apply axial pull out force at the rate of $25\pm 3\text{ mm/minute}$ on the Fitting Nail assembled in the housing. (EIA-364-29)	1.0N最小. 1.0N Min

6.3 环境特性及其它性能 ENVIRONMENTAL PERFORMANCE AND OTHERS

项目 ITEM	测试条件 TEST CONDITION	规格 REQUIRMENT	
耐久性 Durability	将盖子与FPC/FFC反复连接,以每分钟小于10 Cycles连续操作20次。 (EIA-364-09) Insert and withdraw actuator up to 20 cycles at the speed rate of less than 10 cycles/minute. (EIA-364-09)	接触阻抗 Contact Resistance	60m Ω 最大. 60m Ω Max.
温度上升 Temperature Rise	量测通过FPC/FFC最大容许电流时,样品接触点之温升。 (EIA-364-70 Method2) Mate applicable FPC/FFC and measure the temperature rise of contact when the maximum AC rated current is passed. (EIA-364-70 Method 2)	温升 Temperature Rise	30° C最大. 30° C Max.

浙江创都电子科技有限公司

ZHE JIANG CHUANG DU ELECTRONICS CO.,LTD

REV. A

耐振性 Vibration	通过DC电流100mA，位移相对距离1.5mm，振动周期10~ 55~ 10 Hz在1分钟内，持续2小时，方向在X, Y, Z轴做测试。(EIA-364-28 Condition I) Mate connectors and subject to the following vibration conditions, for period of 2 hours in each of 3 mutually perpendicular axes, passing DC 100mA during the test. Amplitude : 1.5mm P-P Frequency : 10~ 55~ 10 Hz in 1 minute. Duration : 2 hours in each of X, Y, Z axes. (EIA-364-28 Condition I)	外观 Appearance	目视外观无任何损坏异状 NoDamage
		接触阻抗 Contact Resistance	60mΩ最大. 60mΩ Max.
		瞬间断电 Discontinuity	1 μ sec最大 1 μ sec Max.
项目 ITEM	测试条件 TEST CONDITION	规格 REQUIRMENT	
耐冲击性 Shock	将样品与适合之FPC/FFC连接，通过DC 100 mA测试条件，连续测试3次。在X、Y、Z 3轴6个垂直方向施于重力加速度490m/s2 {50G} 冲击。 (EIA-364-27, Test condition A) Mate applicable FPC/FFC and subject to the following shock conditions. 3 times of shocks shall be applied for each 6 directions along 3 mutually perpendicular axes, passing DC 100 mA current during the test. (Total of 18 shocks) Peak value : 490m/s2 {50G} (EIA-364-27, Test condition A)	外观 Appearance	目视外观无任何损坏异状 NoDamage
		接触阻抗 Contact Resistance	60mΩ 最大. 60mΩ Max.
		瞬间断电 Discontinuity	1 μ sec 最大 1 μ sec Max.
耐热性 Heat Resistance	将样品与适合之FPC/FFC连接，置于环境温度85±2° C测试时间96小时，再置放于室温下1~ 2小时。 (EIA-364-17) Mate applicable FPC/FFC and expose	外观 Appearance	目视外观无任何损坏异状 NoDamage

浙江创都电子科技有限公司

ZHE JIANG CHUANG DU ELECTRONICS CO.,LTD

REV. A

	to $85\pm 2^{\circ}\text{C}$ for 96 hours. Upon completion of the exposure period, the test specimens shall be conditioned at ambient room conditions for 1 to 2 hours, after which the specified measurements shall be performed. (EIA-364-17)	接触阻抗 Contact Resistance	60m Ω 最大. 60m Ω Max.
耐寒性 Cold Resistance	将样品与适合之FPC/FFC连接, 置于环境温度 $-40\pm 2^{\circ}\text{C}$, 测试时间96小时, 再置放于室温下1~ 2小时。 (EIA-364-59) Mate applicable FPC/FFC and expose to $-40\pm 2^{\circ}\text{C}$ for 96 hours. Upon completion of the exposure period, the test specimens shall be conditioned at ambient room conditions for 1 to 2 hours, after which the specified measurements shall be performed. (EIA-364-59)	外观 Appearance	目视外观无任何损坏异状 NoDamage
		接触阻抗 Contact Resistance	60m Ω 最大. 60m Ω Max.

项目 ITEM	测试条件 TEST CONDITION	规格 REQUIRMENT	
耐湿性 Humidity	将样品与适合之FPC/FFC连接, 置于环境温度 $40\pm 2^{\circ}\text{C}$, 相对湿度90~ 95%, 测试时间96小时, 再置放于室温下1~ 2小时。(EIA-364-31) Mate applicable FPC/FFC and expose to $40\pm 2^{\circ}\text{C}$, relative humidity 90 to 95% for 96 hours. Upon completion of the exposure period, the test specimens shall be conditioned at ambient room conditions for 1 to 2 hours, after which the specified measurements shall be performed. (EIA-364-31)	外观 Appearance	目视外观无任何损坏异状 NoDamage
		接触阻抗 Contact Resistance	60m Ω 最大. 60m Ω Max.
		耐电压 Dielectric Strength	需能符合耐电压测试 No Breakdown
		绝缘阻抗 Insulation Resistance	20 M Ω 最小. 20 M Ω Min

浙江创都电子科技有限公司

ZHE JIANG CHUANG DU ELECTRONICS CO.,LTD

REV. A

热冲击 Thermal Shock	将样品与适合之FPC/FFC连接, 承受5 cycles冷热冲击后放置于室温下1~ 2 小时。1 cycle time如下 a) $-55\pm 3^{\circ}\text{C}$ 30分钟 b) $+85\pm 3^{\circ}\text{C}$ 30分钟 (EIA-364-32) Mate applicable FPC/FFC and subject to the following conditions for 5 cycles. Upon completion of the exposure period, the test specimens shall be conditioned at ambient room conditions for 1 to 2 hours, after which the specified measurements shall be performed. 1 cycle a) $-55\pm 3^{\circ}\text{C}$ 30minutes b) $+85\pm 3^{\circ}\text{C}$ 30minutes (EIA-364-32)	外观 Appearance	目视外观无任何损坏异状 NoDamage
		接触阻抗 Contact Resistance	60mΩ 最大. 60mΩ Max.
盐水喷雾 Salt Spray	将样品与适合之FPC/FFC连接, 使用 $5\pm 1\%$ 浓度盐水, 测试温度 $35\pm 2^{\circ}\text{C}$, 镀金: 1~ 2u", 测试时间 24 ± 4 小时, 镀金: 3u" 及以上, 测试时间 48 ± 4 小时, 后于室温下使用清水冲洗后再干燥。(EIA-364-26) Mate applicable FPC/FFC and expose to the following salt mist conditions. Upon completion of the exposure period, salt deposits shall be removed by a gentle wash or dip in running water, after which the specified measurements shall be performed. NaCl solution Concentration : $5 \pm 1\%$ Gold plating: 1~ 2u " Spray time : 24 ± 4 hours Gold plating: 3u "and above Spray time : 48 ± 4 hours Ambient temperature : $35 \pm 2^{\circ}\text{C}$ (EIA-364-26)	外观 Appearance	目视外观无任何损坏异状 NoDamage
		接触阻抗 Contact Resistance	60mΩ 最大. 60mΩ Max.
项目	测试条件	规格	

浙江创都电子科技有限公司

ZHE JIANG CHUANG DU ELECTRONICS CO.,LTD

REV. A


ITEM	TEST CONDITION	REQUIRMENT	
焊锡性 Solderability	锡温 $245\pm5^{\circ}\text{C}$, 将导电端子浸入锡炉液面至Housing距离锡面0.1mm位置, 焊锡时间 3 ± 0.5 秒。(EIA-364-52) Tip of solder tails and fitting nails into the molten solder (held at $245\pm5^{\circ}\text{C}$) up to 0.1mm from the bottom of the housing for 3 ± 0.5 seconds. (EIA-364-52)	润湿性 Solder Wetting	润湿面积95%以上, 并不得有漏焊针孔现象 95% of immersed area must show no voids, pin holes.
焊锡耐热性 Resistance to Soldering Heat	使用红外线回焊时请参考第7 When reflowing Refer to paragraph 7. 使用烙铁手焊时须可符合下述焊锡条件。(EIA-364-56) Soldering iron method 0.2mm from terminal tip and fitting nail tip. Soldering time : 5 seconds Max. Solder temperature : $370\sim 400^{\circ}\text{C}$. (EIA-364-56)	外观 Appearance	目视外观无任何损坏异状 NoDamage

浙江创都电子科技有限公司

ZHE JIANG CHUANG DU ELECTRONICS CO.,LTD

REV. A

【7】 红外线回焊温度曲线 INFRARED REFLOW CONDITION



温度条件TEMPERATURE CONDITION GRAPH
(基板表面温度) (TEMPERATURE ON BOARD PATTERN SIDE)