



General tolerances(mm)													0.1/10 ±2°
0 ~ 3	>3 ~ 6	>6 ~ 10	>10 ~ 18	>18 ~ 30	>30 ~ 50	>50 ~ 80	>80 ~ 120	>120 ~ 180	>180 ~ 250	>250 ~ 315	>315 ~ 400	>400 ~ 500	
±0.12	±0.18	±0.22	±0.26	±0.31	±0.37	±0.57	±0.80	±0.93	±1.05	±1.15	±1.60	±2.20	

UL Standard	B	C	D
Rated Voltage(V)/Current(A)	300/7	/	/
Torque Tightening(N·m/Lb.in)	M3, 0.5/4.43		
Wire Range(rigid and flexible)(mm ² /AWG)	22~14		
Pitch(mm)/Poles	5.08/N=02~24P		
Operating temperature(°C)	-40~+105		
Conform to RoHS	Yes		



Note:The A&Z(H) in the name means: A(H) and Z(H).			
3	Scerw	Steel	M3/Ni Plated
2	Pin Header	Copper alloy	Sn Plated
1	Housing	PA66	UL94V-0
ITEM	NAME OF PART	MATERIAL	NOTES

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERL TOLERANCE		制图 DRAWING	料号 PART NO.	品名 TITLE	客户料号 CUTM.NO.	版本 REV.	页次 SHEET
					Yu	BX-DG10-7.62-NP	DG10-7.62-NP		A	1/1
					HUANG					
					RUAN					
					单位 UNITS	MM	比例 SCALE	1:1		