



SMB Fast Recovery Diode 快恢复二极管



■Features 特点

Built-in strain relief 内应力释放
Fast Recovery time 快恢复时间
Surface mount device 表面贴装器件
Case 封装:SMB(DO-214AA)



■Maximum Rating 最大额定值

($T_A=25^{\circ}\text{C}$ unless otherwise noted 如无特殊说明, 温度为 25°C)

Characteristic 特性参数	Symbol 符号	RS3AB -6AF	RS3BB -6AF	RS3DB -6AF	RS3GB -6AF	RS3JB -6AF	RS3KB -6AF	RS3MB -6AF	Unit 单位
Marking 印字		RS3A	RS3B	RS3D	RS3G	RS3J	RS3K	RS3M	
Repetitive Peak Reverse Voltage 重复峰值反向电压	V_{RRM}	50	100	200	400	600	800	1000	V
DC Reverse Voltage 直流反向电压	V_R	50	100	200	400	600	800	1000	V
RMS Reverse Voltage 反向电压均方根值	$V_{R(RMS)}$	35	70	140	280	420	560	700	V
Forward Rectified Current 正向整流电流	I_F	3							A
Peak Surge Current 峰值浪涌电流	I_{FSM}	100							A
Thermal Resistance J-A 结到环境热阻	$R_{\theta JA}$	20							$^{\circ}\text{C}/\text{W}$
Junction/Storage Temperature 结温/储藏温度	T_J, T_{stg}	$-50\text{to}+150^{\circ}\text{C}$							

■Electrical Characteristics 电特性

($T_A=25^{\circ}\text{C}$ unless otherwise noted 如无特殊说明, 温度为 25°C)

Characteristic 特性参数	Symbol 符号	RS3AB-RS3GB -6AF	RS3JB -6AF	RS3KB-RS3MB -6AF	Unit 单位	Condition 条件
Forward Voltage 正向电压	V_F	1.3			V	$I_F=3\text{A}$
Reverse Current 反向电流	I_R	$5(T_A=25^{\circ}\text{C})$ $200(T_A=125^{\circ}\text{C})$			μA	$V_R=V_{RRM}$
Reverse Recovery Time 反向恢复时间	T_{rr}	150	250	500	nS	$I_F=0.5\text{A}, I_R=1\text{A}$ $I_{rr}=0.25\text{A}$
Junction Capacitance 结电容	C_J	60			pF	$V_R=4\text{V}, f=1\text{MHz}$

■ Typical Characteristic Curve 典型特性曲线

FIG.1-TYPICAL FORWARD

CHARACTERISTICS




FIG.2-TYPICAL FORWARD CURRENT DERATING CURVE




FIG.4-MAXIMUM NON-REPETITIVE FORWARD SURGE CURRENT





FIG.3- TEST CIRCUIT DIAGRAM AND REVERSE

RECOVERY TIME CHARACTERISTICS



NOTES: 1. Rise Time= 7ns max., Input Impedance= 1 megohm, 22pF.

2. Rise Time= 10ns max., Source Impedance= 50 ohms.




FIG.5-TYPICAL JUNCTION CAPACITANCE

