




SOT-89-3L Bipolar Transistor 双极型三极管

■ Features 特点

PNP High Voltage 高压



1. BASE
2. COLLECTOR
3. EMITTER



■ Absolute Maximum Ratings 最大额定值

Characteristic 特性参数	Symbol 符号	Rat 额定值	Unit 单位
Collector-Base Voltage 集电极基极电压	V_{CBO}	-160	V
Collector-Emitter Voltage 集电极发射极电压	V_{CEO}	-160	V
Emitter-Base Voltage 发射极基极电压	V_{EBO}	-6	V
Collector Current 集电极电流	I_C	-1000	mA
Power dissipation 耗散功率	$P_C(T_a=25^{\circ}C)$	500	mW
Thermal Resistance Junction-Ambient 热阻	$R_{\theta JA}$	250	$^{\circ}C/W$
Junction and Storage Temperature 结温和储藏温度	T_J, T_{stg}	-55to+150 $^{\circ}C$	

■ Device Marking 产品打标

H_{FE}	60-120(R)	100-200(O)	160-320(Y)
Mark	1013R	1013O	1013Y









■Electrical Characteristics 电特性


($T_A=25^{\circ}\text{C}$ unless otherwise noted 如无特殊说明, 温度为 25°C)

Characteristic 特性参数	Symbol 符号	Min 最小值	Type 典型值	Max 最大值	Unit 单位
Collector-Base Breakdown Voltage 集电极基极击穿电压($I_C = -100\mu\text{A}$, $I_E = 0$)	BV_{CBO}	-160	—	—	V
Collector-Emitter Breakdown Voltage 集电极发射极击穿电压($I_C = -1\text{mA}$, $I_B = 0$)	BV_{CEO}	-160	—	—	V
Emitter-Base Breakdown Voltage 发射极基极击穿电压($I_E = -10\mu\text{A}$, $I_C = 0$)	BV_{EBO}	-6	—	—	V
Collector-Base Leakage Current 集电极基极漏电流($V_{CB} = -150\text{V}$, $I_E = 0$)	I_{CBO}	—	—	-1	μA
Emitter-Base Leakage Current 发射极基极漏电流($V_{EB} = -6\text{V}$, $I_C = 0$)	I_{EBO}	—	—	1	μA
DC Current Gain 直流电流增益($V_{CE} = -5\text{V}$, $I_C = -200\text{mA}$)	H_{FE}	60	—	320	
Collector-Emitter Saturation Voltage 集电极发射极饱和压降 ($I_C = -500\text{mA}$, $I_B = -50\text{mA}$)	$V_{CE(sat)}$	—	—	-1.5	V
Base-Emitter On Voltage 基极发射极导通电压($V_{CE} = -5\text{V}$, $I_C = -5\text{mA}$)	V_{BE}	—	—	-0.75	V
Transition Frequency 特征频率($V_{CE} = -5\text{V}$, $I_C = -200\text{mA}$)	f_T	15	—	—	MHz
Output Capacitance 输出电容($V_{CB} = -5\text{V}$, $I_E = 0$, $f = 1\text{MHz}$)	C_{ob}	—	12	—	pF

■ Typical Characteristic Curve 典型特性曲线



■Dimension 外形封装尺寸



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
A	1.40	1.60	0.055	0.063
B	0.40	0.56	0.016	0.022
B1	0.35	0.48	0.014	0.019
C	0.35	0.44	0.014	0.017
D	4.40	4.60	0.173	0.181
D1	1.35	1.83	0.053	0.072
e	1.45	1.55	0.057	0.061
e1	2.95	3.05	0.116	0.120
E	2.29	2.60	0.090	0.102
H	3.75	4.25	0.148	0.167
L	0.80	1.20	0.031	0.047