







A-A



推荐插头尺寸



电路示意图

NOTES:

1. VOLTAGE RATING: 20V DC ;
2. CURRENT RATING: 5A ;
3. CONTACT RESISTANCE: $\leq 30m\Omega$;
4. INSULATION RESISTANCE: $\geq 100M\Omega$;
5. WITHSTAND VOLTAGE: 500 VAC ;
6. UNMATING FORCE: 3N~30N ;
7. OPERATING LIFE: 5000 CYCLES MIN ;
8. OPERATION TEMPERATURE: $-20^{\circ}C \sim +80^{\circ}C$;



Ordering Information

HC- DC*** - * - * ** - * - ** - ** - 08

序列号 Nature Foot Type T=Through holes PIN Diameter Material
Male Female 2=2P 3=3P 4=4P DP=DP (有插孔) SM=SM (有插孔) VS=Vertical SM (有插孔) MB=MB Mount (有插孔) DS=DP+SM (有插孔) WB=Wire Bonding (有插孔)
1.3~1.3mm 1.65~1.65mm 2.0~2.0mm 2.5~2.5mm
HT=1.00 MT=1.00

6	外壳	不锈钢 T=0.2mm	1	镀镍
5	面盖	不锈钢 T=0.1mm	1	本色
4	插片	C2680 T=0.4mm	1	镀锡
3	弹片	C5191 T=0.3mm	1	镀银
2	PIN针	ZINC ALLOY	1	镀金
1	主体	PA10T	1	黑色
序号	名称	材料	数量	颜色/电镀

			GENERAL TOLERANCE		制图	深圳市华灿天禄电子有限公司			
					DRAWING	ShenzhenhuacantianluELECTRONICS CO., LTD			
			DIM	TOL	审核	产品名称	电源插座 母座 2P 焊线式	版本	A
			X.X	±0.30	CHECK	TITLE	02.5 半铜	REV.	
			X.XX	±0.20	批准	产品料号	HC-DC0167A-F-2WB-2.5-M-08	单位	mm
			X.XXX	±0.10	APPROVAL	PART NO.		页次	1/1
			Angle	±3.0°	比例	材料		SHEET	
序号	变更内容	日期			投影				
No.	MODIFY CONTENT	MODIFY DATE			Projection				