




RoHS



Technology Request;
1.Outlook;No burr,no hurt.
2.Electronic performance;
a.Insulation resistance;Above DC500V/100MΩ;
b.Endur voiage;AC500V at 1 minute
c.Contact resistance;Under 30mΩ
3.Insertion force & withdrawal force;0.3-3kgf
4.Salt spray test;24H
5.Meet RoHS.
6.Remark * is important specification

4	9.3*8.5*8.3外管	C3601	Ni 40-120u
3	7*8.5*5.4中管	C3604	Ni 40-120u
2	1.2*1.8*8.5针	C3604	Ni 40-120u
1	PLASTIC	PBT	Black
NO	PART	MATERIAL	PLATING

X.±0.50	X.°±
.X±0.25	.X°±
.XX±0.15	.XX°±
.XXX±0.10	.XXX°±
UNITS:	mm
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED, COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN	

PART NO:		XF-931285-3-M		XFCN 兴飞连接器	
TITLE:		9.3*1.2*85 插板式 三级公头		0769-82001899	
				www.xfconn.com	
				DWG NO:	
APPD		Chen ZhiQiang			
CHKD		Liu Wei		VIEW	
DRAW		Chen HongJiang		SCALE	
DATE		2025.05.08		SHEET	
				REV	
				1/1	
				A1	