

## Features

- Ultra small package: 0.6x0.3x0.3mm
- Ultra low capacitance: 30pF typical
- Ultra low leakage: nA level
- Low operating voltage:  $\pm 3.3\text{V}$
- Low clamping voltage
- 2-pin leadless package
- Complies with following standards:
  - - IEC 61000-4-2 (ESD) immunity test
  - Air discharge:  $\pm 30\text{kV}$
  - Contact discharge:  $\pm 30\text{kV}$
  - IEC61000-4-5 (Lightning) 20A (8/20 $\mu\text{s}$ )
- These are Pb-Free Devices
- Response Time is Typically < 1 ns


## Mechanical Characteristics

- Package: DFN0603-2 (0201)
- Lead Finish: Matte Tin
- Case Material: "Green" Molding Compound.
- Moisture Sensitivity: Level 3 per J-STD-020
- Terminal Connections: See Diagram Below
- Shipping Qty :15000pcs Or 10000/7Inch Tape & Reel

## Applications

- Cellular Handsets and Accessories
- Personal Digital Assistants
- Notebooks and Handhelds
- Portable Instrumentation
- Digital Cameras
- Peripherals

## Dimensions and Pin Configuration



**Marking: 3J**

**Absolute Maximum Ratings** (Tamb=25°C unless otherwise specified)

| Parameter                       | Symbol | Value       | Unit |
|---------------------------------|--------|-------------|------|
| Peak Pulse Power (8/20μs)       | Ppk    | 200         | W    |
| Peak Pulse Current (8/20μs)     | Ipp    | 20          | A    |
| ESD per IEC 61000-4-2 (Air)     | VESD   | ±30         | kV   |
| ESD per IEC 61000-4-2 (Contact) |        | ±30         |      |
| Operating Temperature Range     | TJ     | -55 to +125 | °C   |
| Storage Temperature Range       | Tstg   | -55 to +150 | °C   |

**Electrical Characteristics** (TA=25°C unless otherwise specified)

| Parameter               | Symbol | Min | Typ | Max | Unit | Test Condition         |
|-------------------------|--------|-----|-----|-----|------|------------------------|
| Reverse Working Voltage | VRWM   |     |     | 3.3 | V    |                        |
| Breakdown Voltage       | VBR    | 3.8 | 4.2 | 5.6 | V    | IT = 1mA               |
| Reverse Leakage Current | IR     |     |     | 0.1 | uA   | VRWM = 5V              |
| Clamping Voltage        | VC     |     | 7   |     | V    | Ipp=10A(8x 20us pulse) |
| Clamping Voltage        | VC     |     | 10  | 11  | V    | Ipp=20A(8x 20us pulse) |
| Junction Capacitance    | CJ     |     | 30  |     | pF   | VR = 0V, f = 1MHz      |

**Typical Performance Characteristics ( $T_A=25^\circ\text{C}$  unless otherwise Specified)**

Fig1. 8/20 $\mu\text{s}$  Pulse Waveform




Fig2. ESD Pulse Waveform (according to IEC 61000-4-2)






Fig3. Power Derating Curve




**DFN0603-2 Package Outline Drawing (0201)**



| SYM | DIMENSIONS  |       |       |
|-----|-------------|-------|-------|
|     | MILLIMETERS |       |       |
|     | MIN         | NOM   | MAX   |
| A   | 0.230       | 0.300 | 0.330 |
| A1  | 0.000       | 0.020 | 0.050 |
| b   | 0.215       | 0.245 | 0.275 |
| c   | 0.120       | 0.150 | 0.180 |
| D   | 0.550       | 0.600 | 0.650 |
| e   | 0.355 BSC   |       |       |
| E   | 0.250       | 0.300 | 0.350 |
| L   | 0.160       | 0.190 | 0.220 |
| h   | 0.079 BSC   |       |       |

**Suggested Land Pattern**



| SYM | DIMENSIONS  |        |
|-----|-------------|--------|
|     | MILLIMETERS | INCHES |
| X   | 0.30        | 0.012  |
| Y1  | 0.25        | 0.010  |
| Y2  | 0.15        | 0.006  |
| Y3  | 0.40        | 0.016  |
| Z   | 0.65        | 0.026  |