





- 技术指标(Technical Index):
- 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。(The surface of the plastic parts should be smooth,no rough edges,no obvious shrinkage,defects, cracks and other phenomena.)
 - 温度范围(Temperature range): -25° C~+85° C.
 - 额定电压(Rated voltage): 50V, AC/DC(=等效).
 - 接触电阻(Contact resistance): ≤0.03Ω.
 - 绝缘电阻(Insulation resistance): ≥500MΩ.

	2	端子	铜	镀锡	
	1	胶芯	LCP	黑色	
	序号	品名	材质	电镀/颜色	备注
品名 TITLE			FPC座		
料号 PART NO			HC-FPC-0.5-30P-CXH20		
GENERAL TOLERANCES (UNLESS SPECIFIED)		比列 SCALE	1:1		
X. ±.50 .XX ±.10		单位 UNIT	MM	制图 DRAW	AhYe
.X ±.20 .XXX ±.05		张数 PART NO	1 OF 1	审核 CHECKED	夏操云
ANGLES ±1°		版本 REV	A	批准 APPROVE	赵亮亮

