

RVE-LZ

低阻品 片式铝电解电容
Chip Type Aluminum Electrolytic Capacitors



表面安装




小型薄形品



低电阻品



耐清洗品




产品特点 Features

低阻抗；适用-55℃~+105℃温度范围，寿命2,000小时；性能稳定，可靠性高；产品直径：φ 4mm~ φ 10mm
Low impedance; -55℃ ~+105℃ temperature range, life 2000 hours; stable performance, high reliability
product diameter: φ 4mm~ φ 10mm

主要技术性能 Specifications

项目 Items	特 性 Characteristics																																												
工作温度范围 Category Temperature Range	-55℃~+105℃																																												
额定电压范围 Rated Voltage Range	6.3~50V.DC																																												
标称电容量范围 Nominal Capacitance Range	0.1 μ F ~ 1500 μ F																																												
标称电容量允许偏差 Nominal Capacitance Tolerance	± 20%(120Hz,+20 ℃)																																												
泄漏电流范围 Leakage Current(MAX)	I=0.01CV(μ A) or 3 (μ A) after 2 minutes I=Leakage Current(μ A) C=Nominal Capacitance(μ F) V=Roted Voltage(V)																																												
损耗角正切值 Dissipation Factor(MAX) Tan δ (20℃,120Hz)	<table><tr><td>Rated Voltage(V)</td><td>6.3</td><td>10</td><td>16</td><td>25</td><td>35</td><td>50</td></tr><tr><td>Tanδ</td><td>0.26</td><td>0.20</td><td>0.16</td><td>0.14</td><td>0.12</td><td>0.12</td></tr></table>							Rated Voltage(V)	6.3	10	16	25	35	50	Tanδ	0.26	0.20	0.16	0.14	0.12	0.12																								
Rated Voltage(V)	6.3	10	16	25	35	50																																							
Tanδ	0.26	0.20	0.16	0.14	0.12	0.12																																							
耐久性 Load Life	+105℃施加额定工作电压2000H后, 放置16H, 电容器应满足以下要求。 After applying rated voltage with max ripple current for 2000hrs at 105℃,and then resumed 16 hours, the capacitors shall meet the following requirements <table><tr><td>Capacitance Change</td><td>± 30%初始值以内</td><td colspan="5">Within ± 30% of the initial value</td></tr><tr><td>Dissipation Factor</td><td>≤ 300%初始值以内</td><td colspan="5">Not more than 300% of the specified value</td></tr><tr><td>Leakage Current</td><td>≤ 初始规定值</td><td colspan="5">Not more than the specified value</td></tr></table>							Capacitance Change	± 30%初始值以内	Within ± 30% of the initial value					Dissipation Factor	≤ 300%初始值以内	Not more than 300% of the specified value					Leakage Current	≤ 初始规定值	Not more than the specified value																					
Capacitance Change	± 30%初始值以内	Within ± 30% of the initial value																																											
Dissipation Factor	≤ 300%初始值以内	Not more than 300% of the specified value																																											
Leakage Current	≤ 初始规定值	Not more than the specified value																																											
高温贮存 Shelf Life	+105℃, 贮存1000H后, 放置16H, 电容器应满足以下要求。 After storage for 1000hrs at 105℃, then resumed 16 hours, the capacitors shall meet the following requirements <table><tr><td>Capacitance Change</td><td>± 30%初始值以内</td><td colspan="5">Within ± 30% of the initial value</td></tr><tr><td>Dissipation Factor</td><td>≤ 300%初始值以内</td><td colspan="5">Not more than 300% of the specified value</td></tr><tr><td>Leakage Current</td><td>≤ 200%初始值以内</td><td colspan="5">Within 200% of initial specified value</td></tr></table>							Capacitance Change	± 30%初始值以内	Within ± 30% of the initial value					Dissipation Factor	≤ 300%初始值以内	Not more than 300% of the specified value					Leakage Current	≤ 200%初始值以内	Within 200% of initial specified value																					
Capacitance Change	± 30%初始值以内	Within ± 30% of the initial value																																											
Dissipation Factor	≤ 300%初始值以内	Not more than 300% of the specified value																																											
Leakage Current	≤ 200%初始值以内	Within 200% of initial specified value																																											
耐焊接热 Resistance to Soldering Heat	在250℃的条件下, 电容器在热板上保持30秒, 然后从热板上取出电容器,让其在室温下恢复,电容器应满足以下要求。 The capacitors shall be kept on then hot plate maintained at 250℃ for 30 seconds.After removing from the hot plate and restored at room temperature, they meet the following requirement: <table><tr><td>Capacitance Change</td><td>± 10%初始值以内</td><td colspan="5">Within ± 10% of the initial value</td></tr><tr><td>Dissipation Factor</td><td>≤ 初始规定值</td><td colspan="5">Not more than the initial specified value</td></tr><tr><td>Leakage Current</td><td>≤ 初始规定值</td><td colspan="5">Not more than the initial specified value</td></tr></table>							Capacitance Change	± 10%初始值以内	Within ± 10% of the initial value					Dissipation Factor	≤ 初始规定值	Not more than the initial specified value					Leakage Current	≤ 初始规定值	Not more than the initial specified value																					
Capacitance Change	± 10%初始值以内	Within ± 10% of the initial value																																											
Dissipation Factor	≤ 初始规定值	Not more than the initial specified value																																											
Leakage Current	≤ 初始规定值	Not more than the initial specified value																																											
低温特性及阻抗比 Low Temperature Stability Impedance Ratio (MAX) 120Hz	<table><tr><td colspan="2">Roted Voltage (V)</td><td>6.3</td><td>10</td><td>16</td><td>25</td><td>35</td><td>50</td></tr><tr><td rowspan="2">Z-25℃/Z+20℃ (120Hz)</td><td>< Φ8</td><td>4</td><td>3</td><td>2</td><td>2</td><td>2</td><td>2</td></tr><tr><td>≥ Φ8</td><td>5</td><td>4</td><td>3</td><td>2</td><td>2</td><td>2</td></tr><tr><td rowspan="2">Z-55℃/Z+20℃ (120Hz)</td><td>< Φ8</td><td>12</td><td>8</td><td>4</td><td>4</td><td>3</td><td>3</td></tr><tr><td>≥ Φ8</td><td>10</td><td>8</td><td>6</td><td>4</td><td>3</td><td>3</td></tr></table>							Roted Voltage (V)		6.3	10	16	25	35	50	Z-25℃/Z+20℃ (120Hz)	< Φ8	4	3	2	2	2	2	≥ Φ8	5	4	3	2	2	2	Z-55℃/Z+20℃ (120Hz)	< Φ8	12	8	4	4	3	3	≥ Φ8	10	8	6	4	3	3
Roted Voltage (V)		6.3	10	16	25	35	50																																						
Z-25℃/Z+20℃ (120Hz)	< Φ8	4	3	2	2	2	2																																						
	≥ Φ8	5	4	3	2	2	2																																						
Z-55℃/Z+20℃ (120Hz)	< Φ8	12	8	4	4	3	3																																						
	≥ Φ8	10	8	6	4	3	3																																						

■ 尺寸图 Dimensions



(Φ4~Φ10)

单位: mm

ΦD	L	A	B	C	E	H
4	5.4 ± 0.3	5.0	4.3	4.3	1.0	0.5~0.9
5	5.4 ± 0.3	6.0	5.3	5.3	1.5	0.5~0.9
6.3	5.4 ± 0.3	7.2	6.6	6.6	2.1	0.5~0.9
6.3	7.7 ± 0.3	7.2	6.6	6.6	2.1	0.5~0.9
8	10.2 ± 0.5	9.1	8.3	8.3	3.1	0.8~1.1
10	10.2 ± 0.5	11.1	10.3	10.3	4.5	0.8~1.1

■ 标准品一览表 Standard Size

V	6.3			10			16			25			35			50		
μF	D×Lmm	Ω	mA	D×Lmm	Ω	mA	D×Lmm	Ω	mA	D×Lmm	Ω	mA	D×Lmm	Ω	mA	D×Lmm	Ω	mA
1.0																		
2.2																4 × 5.4	7.3	38
3.3																4 × 5.4	7.3	38
4.7							4 × 5.4	4.5	38	4 × 5.4	4.5	50	4 × 5.4	4.5	50	4 × 5.4	7.3	38
10							4 × 5.4	4.5	50	4 × 5.4	4.5	50	4 × 5.4 5 × 5.4	4.5 1.9	50 80	5 × 5.4	3.8	53
22	4 × 5.4	4.5	50	4 × 5.4	4.5	50	5 × 5.4	1.9	80	5 × 5.4	1.9	80	6.3 × 5.4	1.1	115	6.3 × 5.4	2.2	103
33	4 × 5.4	4.5	50	5 × 5.4	1.9	80	5 × 5.4 6.3 × 5.4	1.9 1.1	80 115	6.3 × 5.4	1.1	115	6.3 × 5.4	1.1	115	6.3 × 7.7	1.7	116
47	5 × 5.4	1.9	80	5 × 5.4	1.9	80	5 × 5.4	1.9	80	6.3 × 5.4	1.1	115	6.3 × 5.4	1.1	115	6.3 × 7.7	1.7	116
100	5 × 5.4 6.3 × 5.4	1.9 1.1	80 115	5 × 5.4 6.3 × 5.4	1.9 1.1	80 115	6.3 × 5.4	1.1	115	6.3 × 7.7	0.85	150	6.3 × 7.7 8 × 10.2	0.85 0.43	150 240	8 × 10.2	0.85	185
150	6.3 × 5.4	1.1	115	6.3 × 7.7	0.85	150	6.3 × 7.7	0.85	150	8 × 10.2	0.43	240	10 × 10.2	0.23	360	10 × 10.2	0.45	418
220	6.3 × 5.4 6.3 × 7.7	1.1 0.85	115 150	6.3 × 5.4 6.3 × 7.7	1.1 0.85	115 150	6.3 × 7.7	0.85	150	8 × 10.2	0.43	240	10 × 10.2	0.23	360	10 × 10.2	0.45	418
330	6.3 × 7.7	0.85	150	8 × 10.2	0.43	240	8 × 10.2	0.43	240	8 × 10.2	0.43	240	10 × 10.2	0.23	360			
470	6.3 × 7.7 8 × 10.2	0.85 0.43	150 240	6.3 × 7.7 8 × 10.2	0.85 0.43	150 240	8 × 10.2 10 × 10.2	0.43 0.23	240 360	10 × 10.2	0.23	360	10 × 10.2	0.23	360			
1000	10 × 10.2	0.23	360	10 × 10.2	0.23	360	10 × 10.2	0.17	670									
1500	10 × 10.2	0.23	360															

mA额定纹波电流 Rated ripple current(mA, 105℃, 100kHz)
 Ω阻抗值 Impedance: (Ω, 20℃, 100kHz)

■ 纹波电流修正系数/频率系数 Multiplier For Ripple Current / Frequency coefficient

频率 Frequency	50Hz	120Hz	300Hz	1kHz	≥10kHz
系数 Coefficient	0.64	0.5	0.64	0.83	1.0

注: 以上所提供的设计及特性参数仅供参考, 任何修改不做预先通知, 如在使用上有疑问, 请在采购前与我们联系, 以便提供技术上的协助。
 Note: all designs and specifications are for reference only and are subject to change without prior notice, if any doubt about safety for your application, please contact us immediately for technical assistance before purchase.