

TDS:EMIC

拓電半導體

自主封測 品質把控 售後保障


WEB | WWW.TDSEMIC.COM




電源管理




顯示驅動




二三極管



LDO穩壓器




觸摸芯片



MOS管



運算放大器



存儲芯片



MCU



串口通信

SS16

產品規格說明書

1.0Amp Surface Mounted Schottky Barrier Rectifiers

Features

- The plastic package carries Underwriters Laboratory Flammability Classification 94V-0
- For surface mounted applications
- Built-in strain relief, ideal for automated placement
- Low reverse leakage
- High forward surge current capability
- High temperature soldering guaranteed
260°C/10 seconds at terminals

Mechanical Data


Case : Molded plastic body

Terminals : Solder plated, solderable per MIL-STD-750, Method 2026

Polarity : Polarity symbol marking on body

Mounting Position : Any

Weight : 0.0023 ounce, 0.07 grams



Dimensions in inches and (millimeters)

Maximum Ratings And Electrical Characteristics

Ratings at 25°C ambient temperature unless otherwise specified. Single phase half-wave 60Hz, resistive or inductive load, for capacitive load current derate by 20%.

Parameter	SYMBOLS	SS								UNITS
		12	14	145	16	18	110	115	120	
Maximum repetitive peak reverse voltage	V _{RRM}	20	40	45	60	80	100	150	200	V
Maximum RMS voltage	V _{RMS}	14	28	31.5	42	56	70	105	140	V
Maximum DC blocking voltage	V _{DC}	20	40	45	60	80	100	150	200	V
Maximum average forward rectified current at T _L =100°C	I _(AV)	1.0								A
Peak forward surge current, 8.3ms single half sine-wave superimposed on rated load	I _{FSM}	30.0								A
Maximum instantaneous forward voltage at 1.0A	V _F	0.55			0.70	0.85		0.95		V
Maximum DC reverse current at rated DC blocking voltage	I _R	0.2 10				0.05 5				mA
Typical thermal resistance	R _{QJA}	80.0								°C/W
Operating junction temperature range	T _J	-55 to +125				-55 to +150				°C
Storage temperature range	T _{STG}	-55 to +150								°C

Ratings And Characteristic Curves

FIG. 1- DERATING CURVE OUTPUT RECTIFIED CURRENT




FIG. 2-MAXIMUM NON-REPETITIVE PEAK FORWARD SURGE CURRENT PER LEG




FIG. 3-TYPICAL FORWARD VOLTAGE CHARACTERISTICS






FIG. 4-TYPICAL REVERSE LEAKAGE CHARACTERISTICS




Suggested Pad Layout




Symbol	Unit (mm)	Unit (inch)
A	1.68	0.066
B	1.52	0.060
C	3.90	0.154
D	2.41	0.095
E	5.45	0.215

Marking



Symbol	Explanation
A	Color Band Denotes Cathode
B	Product Name, X : 2.4.....20

Suggested Soldering Temperature Profile




Note

- Recommended reflow methods: IR, vapor phase oven, hot air oven, wave solder.
- The device can be exposed to a maximum temperature of 260°C for 10 seconds.
- Devices can be cleaned using standard industry methods and solvents.
- If reflow temperatures exceed the recommended profile, devices may not meet the performance requirements.

Package Information

Carrier Dimension(mm)



A0	B0	K0	D0	E	F
2.80	5.30	2.36	1.55	1.75	5.50
P0	P1	P2	T	W	Tolerance
4.0	4.0	2.0	0.25	12	0.1

Package Specifications

Package	Reel Size	Reel DIA. (mm)	Q'TY/Reel (Kpcs)	Box Size (mm)	QTY/Box (Kpcs)	Carton Size (mm)	Q'TY/Carton (Kpcs)
SMA	11'	278	5	285	10	355*310*310	80
	13'	330	7.5	340	15	360*360*360	120