


SWITCHING DIODE / DATA SHEET

BAV19W-BAV21W

- ◇ General purpose diodes
- ◇ Fast switching devices
- ◇ **SOD123** Micro SMD package
- ◇ RoHS compliant / Green EMC
- ◇ Matte Tin (Sn) Lead finish
- ◇ Cathode Band / Device marking

Device Marking Code	
BAV19W	A8
BAV20W	T2
BAV21W	T3



Maximum Ratings (Ta = 25 °C)

Symbol	Parameter	BAV19W	BAV20W	BAV21W	Units
V_{RM}	Non-Repetitive Peak Reverse Voltage	120	200	250	V
V_{RRM}	Repetitive Peak Reverse Voltage	100	150	200	V
$V_{R(RMS)}$	RMS Reverse Voltage	71	106	141	V
I_O	Average Rectified Output Current	200			mA
I_{FSM}	Non-Repetitive Peak Forward Surge Current (@t=1.0us)	2.0			A
P_D	Power Dissipation	400			mW
T_J	Junction Temperature	150			°C
T_{STG}	Storage Temperature	-65 to +150			°C

Electrical Characteristics (Ta = 25 °C)


Symbol	Parameter	Test Conditions		Min	Max	Units
V_F	Forward Voltage	$I_F=100mA$ $I_F=200mA$			1 1.25	V
I_R	Reverse current	$V_R=100V$ $V_R=150V$ $V_R=200V$	BAV19W BAV20W BAV21W		0.1 0.1 0.1	uA

Electrical Characteristics (Ta = 25 °C)

Symbol	Parameter	Test Conditions	Min	Max	Units
Ctot	Total capacitance	$V_R=0V, f=1MHz$		5	pF
trr	Reverse recovery time	$I_F=I_R=30mA, I_{rr}=0.1*I_R, R_L=100\Omega$		50	ns

Ordering Information

Device	Package	Shipping	Tape wide	Emboss pitch	Tape specification	Notes
BAV series	SOD123	Tape & Reel 3000pcs /7" Reel	8 mm	4 mm	Conductive	

Package Dimensions


NOTICE

POPPULA'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS COMPONENTS IN ANY LIFE SUPPORT DEVICES OR SYSTEMS.

POPPULA reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to any product herein. POPPULA does not assume any liability arising out of the application or use of any product described herein.